

Wave LED

WAL026135

Old item no.: 18947LG



WAVE LED K2FE 5D L.GRAY/GRIS

Wave LED is an illuminated magnifier for industrial applications. No knobs to tighten, nothing to adjust - a flexible, self-balancing shade and hands-free neck assembly combined with 30" heavy-duty internal-spring parallel, three-pivot K-arm, allows the lamp head to be secured in any position. The fully-enclosed neck design is ideal for environments where FOD is a concern. An automatic shut-off feature and step dimming further ensures energy savings. WAVE LED offers shadow-free 5-diopter (2.25X) magnification with light coming from both sides, as well as three-dimensional magnification lighting from the left or right. The 3D-feature is especially welcome when working with circuit board and similar delicate objects. Weighted base mount. Color: light grey.



Lightsource

Number of lamps	1
Lightsource	LED
CRI and/or Color Temperature	80 CRI, 4000K
Lamp power (W)	12
Lumen/Watt	59
Lumen Out	764

Optic

Primary Lens (D)	5
Working distance (mm)	200
Magnification (X)	2.25

Technical data

Maximum ambient temperature (°C)	25
IP classification	20

Electrical data

Maximum frequency (Hz)	60
Minimum frequency (Hz)	50
Maximum voltage (V)	120
Voltage from (V)	100
Total consumption (W)	13

Dimensions

Net weight (kg)	0
Arm length (in.)	30

Body

Body color	Grey
------------	------

Termination

Mounting	Table/desk base
----------	-----------------

Wave LED
WAL026135



WAVE LED K2FE 5D L.GRAY/GRIS

Wave LED is an illuminated magnifier for industrial applications. No knobs to tighten, nothing to adjust - a flexible, self-balancing shade and hands-free neck assembly combined with 30" heavy-duty internal-spring parallel, three-pivot K-arm, allows the lamp head to be secured in any position. The fully-enclosed neck design is ideal for environments



Drawings

