

Surface Mount Fuse, 7 x 2 mm, Time-Lag T, 125 VAC, 125 VDC



IEC 60127-4 · 125VAC · 125VDC · Time-Lag T



### Description

- Low Breaking Capacity
- Directly solderable on printed circuit boards

### Standards

- IEC 60127-4/2
- UL 248-14
- CSA C22.2 no. 248.14

### Approvals

- Approval Reference Type: MSB
- UL File Number: E42088

### Applications

- Telecom
- Household appliances


### References

[Packaging Details](#)  
Square Footprint Type [MKT](#)  
Corresponding Fuseholder [231786](#); [231787](#)

### Weblinks

[pdf datasheet](#), [html-datasheet](#), [General Product Information](#), [Packaging details](#), [Approvals](#), [CE declaration of conformity](#), [RoHS](#), [CHINA-RoHS](#), [REACH](#), [Distributor-Stock-Check](#), [Detailed request for product](#)


### Technical Data



Rated Voltage	63 - 125VAC, 65 - 125VDC
Rated current	0.75 - 15A
Breaking Capacity	50A - 150A
Characteristic	Time-Lag T
Mounting	PCB,SMT
Admissible Ambient Air Temp.	-55 °C to 85 °C
Climatic Category	55/085/56 acc. to IEC 60068-1
Material: Tube	Ceramic
Material: Endcaps	Tin-Plated Copper Alloy
Unit Weight	0.07 g
Storage Conditions	0 °C to 60 °C, max. 70% r.h.
Product Marking	 , Rated current

Soldering Methods	Reflow, Wave <a href="#">Soldering Profile</a>
Solderability	235 °C / 2 sec acc. to IEC 60068-2-58, Test Td, Fig. 2B (Reflow) // 245 °C / 3 sec (Wave)
Resistance to Soldering Heat	260 °C / 10 sec acc. to IEC 60068-2-58, Test Td

Detailed information on product approvals, code requirements, usage instructions and detailed test conditions can be looked up in [General Product Information](#)

### Dimension

 7 mm




Soldering pads


**Pre-Arcing Time**


Rated Current I <sub>n</sub>	1.1 x I <sub>n</sub> min.	1.25 x I <sub>n</sub> min.	2.0 x I <sub>n</sub> max.	10.0 x I <sub>n</sub> min.	10.0 x I <sub>n</sub> max.
0.75 A - 1.5 A	-	60 min	120 s	5 ms	100 ms
2 A - 8 A	-	60 min	120 s	10 ms	100 ms
10 A - 15 A	60 min	-	120 s	10 ms	100 ms


**Time-Current-Curves**



**All Variants**

Rated Current [A]	Rated Voltage [VAC]	Rated Voltage [VDC]	Breaking Capacity	Voltage Drop 1.0 I <sub>n</sub> typ. [mV]	Power Dissipation 1.1 I <sub>n</sub> typ. [mW]	Power Dissipation 1.25 I <sub>n</sub> typ. [mW]	Melting I <sup>2</sup> t 10.0 Intyp. [A <sup>2</sup> s]		Order Number
0.75	125	125	1)	106	-	145	0.4	●	<a href="#">7010.9960.63</a>
0.75	125	125	1)	106	-	145	0.4	●	<a href="#">7010.9960.57</a>
1	125	125	1)	97	-	179	0.79	●	<a href="#">7010.9961.63</a>
1	125	125	1)	97	-	179	0.79	●	<a href="#">7010.9961.57</a>
1.5	125	125	1)	91	-	240	2.1	●	<a href="#">7010.9962.63</a>
1.5	125	125	1)	91	-	240	2.1	●	<a href="#">7010.9962.57</a>
2	125	125	1)	88	-	315	4.1	●	<a href="#">7010.9963.63</a>
2	125	125	1)	88	-	315	4.1	●	<a href="#">7010.9963.57</a>
2.5	125	125	1)	84	-	375	6.9	●	<a href="#">7010.9964.63</a>
2.5	125	125	1)	84	-	375	6.9	●	<a href="#">7010.9964.57</a>
3.15	125	125	1)	80	-	450	12	●	<a href="#">7010.9965.63</a>
3.15	125	125	1)	80	-	450	12	●	<a href="#">7010.9965.57</a>
3.5	125	125	1)	79	-	490	15	●	<a href="#">7010.9966.63</a>
3.5	125	125	1)	79	-	490	15	●	<a href="#">7010.9966.57</a>
4	125	125	1)	76	-	545	21	●	<a href="#">7010.9967.63</a>
4	125	125	1)	76	-	545	21	●	<a href="#">7010.9967.57</a>
4	125	125	1)	76	-	545	21	●	<a href="#">7010.9967.59</a>
5	125	125	1)	87	-	620	29	●	<a href="#">7010.9968.63</a>
5	125	125	1)	87	-	620	29	●	<a href="#">7010.9968.57</a>
6.3	125	125	2)	85	-	850	51	●	<a href="#">7010.9969.63</a>
6.3	125	125	2)	85	-	850	51	●	<a href="#">7010.9969.57</a>

Rated Current [A]	Rated Voltage [VAC]	Rated Voltage [VDC]	Breaking Capacity	Voltage Drop 1.0 I <sub>n</sub> typ. [mV]	Power Dissipation 1.1 I <sub>n</sub> typ. [mW]	Power Dissipation 1.25 I <sub>n</sub> typ. [mW]	Melting I <sup>2</sup> t 10.0 Intyp. [A <sup>2</sup> s]	 Order Number
8	65	65	3)	83	-	1200	83	● 7010.9970.63
8	65	65	3)	83	-	1200	83	● 7010.9970.57
10	65	65	3)	81	1100	-	140	● 7010.9971.63
10	65	65	3)	81	1100	-	140	● 7010.9971.57
12	65	65	3)	80	1150	-	215	● 7010.9972.63
12	65	65	3)	80	1150	-	215	● 7010.9972.57
15	65	65	3)	78	1750	-	360	● 7010.9973.63
15	65	65	3)	78	1750	-	360	● 7010.9973.57

 Most Popular.

Availability for all products can be searched real-time: <http://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER>

1) 50 A @ 125 VAC/DC

2) 63 A @ 125 VAC/DC

3) 150 A @ 65 VAC/DC

**Packaging Unit**     .xx = .63 Plastic Bag (100 pcs.)  
                                 .xx = .57 Blister Tape 18 cm Reel (1500 pcs.)