


RS 100
AP 100 D OR

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 1429-0
 Fax: +49 5231 14292083
 www.weidmueller.com


Flexible - More flexible - Profilform

Modular housings in profile form - the flexible modular system comprising coloured and transparent plastic profiles and carrier modules

The combination of standard pitches mounted side by side in any arrangement and metre goods cut accurate to the millimetre creates the perfect balance between flexibility and economic efficiency:

- Pitch profiles with standard widths ranging from 5mm to 45mm allow the mounting of all standard PCB formats.
- Variable heights ensure maximum component density, even with larger electronics components.
- The different installation variations mean that mounting the enclosure directly is as easy as clipping components onto the terminal rail
- Solid hoods protect the module reliably from external influences

The recipe for success: variable profile + modular form components = flexible enclosure concept that offers a large surface area for the PCBs.

The modular concept is designed for modules with high space requirements and suitable for small component quantities and different widths.

General ordering data

Type	AP 100 D OR
Order No.	1185160000
Version	End plate, RS 100 Orange, End plate, Width: 21.5 mm
GTIN (EAN)	4008190058388
Qty.	20 pc(s).

RS 100
AP 100 D OR

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 1429-0
 Fax: +49 5231 14292083
 www.weidmueller.com

Technical data**Dimensions and weights**

Length	108.2 mm	Length (inches)	4.26 inch
Width	21.5 mm	Width (inches)	0.846 inch
Height	21.9 mm	Height (inches)	0.862 inch
Net weight	7.1 g		

System characteristics

Version	End plate	Cross-connection	No
Contact to terminal rail	No	Protection degree	IP20
Encapsulation option	No		

Material data

Insulating material	PA 66	Colour	Orange
Colour chart (similar)	RAL 2000	CTI	≥ 600
UL 94 flammability rating	V-2	Storage temperature, min.	-25 °C
Storage temperature, max.	55 °C	Max. relative humidity during storage	80 %
Operating temperature, min.	-50 °C	Operating temperature, max.	100 °C
Temperature range, installation, min.	-25 °C	Temperature range, installation, max.	100 °C

Classifications

ETIM 3.0	EC000886	ETIM 5.0	EC000886
ETIM 6.0	EC001031	UNSPSC	30-21-18-27
eClass 5.1	27-14-11-33	eClass 6.2	27-14-11-33
eClass 7.1	27-14-11-33	eClass 8.1	27-14-11-33
eClass 9.0	27-14-11-33	eClass 9.1	27-18-27-90

Notes

Notes

Descriptive text technical data

3 heights are available for the cover profile and the end plates:**TS mounting without cover: TS 32 = 45 mm, TS 35x7.5 = 40.5 mm****TS mounting with low cover: TS 32 = 89 mm, TS 35x7.5 = 84.5 mm****TS mounting with high cover: TS 32 = 121 mm, TS 35x7.5 = 116.5 mm****Direct mounting, without/low/high cover: 24 / 69 / 99 mm****Dimensions of the PCB****Thickness: 1.6 (±0.2) mm, width: 100 (+0.5) mm****Dimension of RS section = PCB length - 4.5 mm****Dimension of ADP section = PCB length - 1 mm****Example:****PCB length 160 mm, RS = 155.5 mm, ADP = 159 mm****Approvals**

Approvals



ROHS

Conform

Data sheet**RS 100**
AP 100 D OR**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 1429-0
Fax: +49 5231 14292083
www.weidmueller.com**Technical data****Downloads**

Brochure/Catalogue

[FL ANALO.SIGN.CONV. EN](#)
[MB DEVICE MANUF. EN](#)
[CAT 2 PORTFOLIOGUIDE EN](#)
[FL MACHINE SAFETY EN](#)
[FL 72H SAMPLE SER EN](#)
[PO OMNIMATE EN](#)

Data sheet

**RS 100
AP 100 D OR**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 1429-0
 Fax: +49 5231 14292083
 www.weidmueller.com

Drawings

DIRECT MOUNTING
FOR BOTH SIDES (RIGHT AND LEFT)

