Product data sheet Characteristics

LC1SKGC200U7

TeSys SK mini contactor - 2P (2 NO) - AC-3 - 690 V 5 A - 240 V AC coil



Main	
Comr	

Main	
Commercial Status	Commercialised
Range	TeSys
Product name	TeSys SK
Product or component type	Mini contactor
Device short name	LC1SKGC
Contactor application	Motor control Resistive load
Utilisation category	AC-1 AC-3
Power pole contact composition	2P
Pole contact composition	2 NO
[Ue] rated operational voltage	690 V AC 50/60 Hz for power circuit
[le] rated operational current	20 A (<= 50 °C) AC AC-1 5 A at <= 400 V AC AC-3
Control circuit type	AC 50/60 Hz
Control circuit voltage	240 V AC 50/60 Hz
[Ith] conventional free air thermal current	20 A at <= 55 °C for power circuit
Irms rated making capacity	50 A AC conforming to IEC 60947 50 A AC conforming to NF C 63-110
Rated breaking capacity	40 A at <= 400 V conforming to IEC 60947 40 A at <= 400 V conforming to NF C 63-110
[lcw] rated short-time withstand current	40 A <= 55 °C power circuit
Associated fuse rating	20 A gl at <= 440 V for power circuit
Average impedance	4 mOhm at 50 Hz - Ith 20 A for power circuit
[Ui] rated insulation voltage	690 V for power circuit conforming to CSA C22.2 No 14 690 V for power circuit conforming to VDE 0110 group C 690 V for power circuit conforming to UL 508 690 V for power circuit conforming to IEC 60947 690 V for power circuit conforming to BS 5424
Mounting support	Rail
Standards	BS 5424 IEC 60947 NF C 63-110 VDE 0660
Product certifications	CSA UL
Connections - terminals	Connector 2 cable(s) 0.351.5 mm² - cable stiffness: flexible - with cable end Connector 1 cable(s) 0.356 mm² - cable stiffness: flexible - with cable end Connector 2 cable(s) 0.352.5 mm² - cable stiffness: flexible - without cable end Connector 1 cable(s) 0.56 mm² - cable stiffness: flexible - without cable end Connector 2 cable(s) 1.54 mm² - cable stiffness: solid Connector 1 cable(s) 1.56 mm² - cable stiffness: solid

Operating time	714 ms coil energisation and NO closing 68 ms coil de-energisation and NO opening
Mechanical durability	10 Mcycles
Operating rate	1200 cyc/h

Complementary

Control circuit voltage limits	0.20.75 Uc at <= 55 °C drop-out 50/60 Hz 0.851.1 Uc at <= 55 °C operational 50/60 Hz	
Inrush power in VA	16 VA at 20 °C 50/60 Hz	
Hold-in power consumption in VA	4.2 VA at 20 °C 50/60 Hz	
Heat dissipation	1.4 W at 50/60 Hz	

Environment

IP degree of protection	IP2x conforming to VDE 0106
Protective treatment	TC conforming to DIN 50015 TC conforming to IEC 60068
Ambient air temperature for operation	-2050 °C
Ambient air temperature for storage	-5070 °C
Operating altitude	2000 m without derating in temperature
Height	56 mm
Width	27 mm
Depth	55.5 mm
Product weight	0.132 kg

