



CCTVX CAMBF8

2MP HD Bullet Camera

SPECIFICATIONS

Model NO.	CAMBF8
Camera	
Image Sensor	IMX323
Main processor	Hi3516CV300
Resolution	1080P
Effective Pixels	1985(H)*1105(V)
Compression	H.264/H.265/JPEG/AVI/MJPEG
TV System	PAL/NTSC
Electronic Shutter Time	Auto: PAL 1/25-1/10000Sec; NTSC 1/25-1/10000Sec
S/N Ratio	≥52dB
Scanning System	Progressive
SD Card	NO
Video Output	Network
LENS Type	
Focus Length	Board Lens 3.6mm/F2.0
Focus Control	Fixed
Lens Type	Fixed
Pixels	3Mp
Night Vision	
Infrared LED	42μx 2PCS
Infrared Distance	30M
IR Status	Under 10 Lux By CDS
IR Power On	CDS Auto Control
Network	
Ethernet	RJ-45 (10/100Base-T)
Protocol	TCP/IP,ICMP,HTTP,HTTPS,FTP,DHCP,DNS,DDNS,RTP,RTSP,RTCP,NTP,SMTP
ONVIF	Support ONVIF 2.4
P2P	YES, Support QR Code
POE	Optional, Support IEEE 802.3af
WIFI	Support, WIFI Range: No obstacles 300m Max.
Video Delay	0.3S (Within the Lan)
Main Stream 1	1920*1080@25fps
Main Stream 2	/
Main Stream 3	/
Sub Stream 1	720*480@25fps
Sub Stream 2	/
Sub Stream 3	/
Tri Stream	352*288@25fps
IE Brower	IE8-11, Google Chrome, Firefox, Safari, Mac Safari
Smart Phone	iPhone, iPad, Android, Android Pad
Camera Features	
Day/Night	Color/ B&W (IR-CUT)
Image Config	Saturation/Brightness/Contrast /Sharpness, Mirror, 3D NR , White Balance, FLK(Flicker Control)
Corridor Pattern	Supported
Defog Mode	Supported
BLC	Supported
WDR	Supported
Motion Detection	Supported
Privacy Masking	3 Rectangular Zone
Recording Mode	NVR/NAS/CMS/Web
Language	Chinese Simplified, Chinese Traditional, English, Bulgarian, Polish, Farsi, German, Russian, French, Korean, Portuguese, Japanese, Turkish, Spanish, Hebrew, Italian,Nederlands
General	
Housing	Metal, IP66
Anti-cut Bracket	3-Axis
IR Cut Filter	YES
Operation Temperature	S
Storage Temperature	-20 ~ +60 RH95% Max
Power Source	DC12V±10%, 500mA
Dimension	157(W) x 70(H) x 66(D)mm
Weight	650g