


Keysight N2820A/21A

High-Sensitivity, High Dynamic Range Current Probes

See the details without losing sight of the big picture

[Data Sheet](#)



Key features and specifications

- Measure current as low as 500 nA
- Measure current as high as 5 A
- Measure AC and DC
- Bandwidth
 - 3 MHz - Zoom-Out channel
 - 500 kHz - Zoom-In channel
- 2-channel vertical zoom mode enables accurate peak and idle current measurements
- New oscilloscope measurement current consumption over time (Charge)
- AutoProbe interface driving 1 M Ω input to oscilloscope
- Wide dynamic range - > 20,000:1 or 86 dB
- Probe accessories included with the probe or available separately: interchangeable Rsense heads (20 m Ω , 100 m Ω , and user-defined), MBB receptacles, headers, and hook-up wire

Industry's highest sensitivity, highest dynamic range AC/DC current probes

As modern battery-powered devices and integrated circuits become more 'green' and energy efficient, there is a growing need to make low level, wide dynamic range current measurements to ensure the current consumption of these devices is within acceptable limits.

The new N2820A Series high-sensitivity current probes address the need for high-sensitivity current measurements with a wide dynamic range. These probes also offer the advantage of small physical connections to the DUT because today's application environments require an extremely small form factor. The N2820A Series probes have higher sensitivity - up to 200X greater than existing clamp-on current probes with sub-milliampere low level sensitivity.



Figure 1. Keysight's ultra sensitive N2820A/N2821A current probes (with resolution as low as 50 μ A) excel at measuring small current levels typically found in battery powered devices.

See the details without losing sight of the big picture

This N2820A current probe comes with two parallel amplifiers possessing different gain settings. The low gain side allows you to see the entire waveform (or the 'zoomed out' view) and the high gain amplifier provides a 'zoomed in' view.

The precision sense resistor is positioned in the interchangeable Rsense head that is plugged into the probe body. The probe body can be found at the same location as the differential amplifier. On the 'user-defined' sense head, there is no resistor, which allows the probe to be used with the user's sense resistor on the target. The user will need to enter the sense resistor value into the scope.

| | | |
|--|--|--|
| <ul style="list-style-type: none"> - 500 mW - 250 μA to 5 A - \pm 1% tolerance - For smaller voltage drop or lower burden on your circuit - Order N2822A for replacement head | <ul style="list-style-type: none"> - 500 mW - 50 μA to 2.2 A - \pm 1% tolerance - For higher sensitivity, bandwidth and lower noise - Order N2824A for replacement head | <ul style="list-style-type: none"> - Use your own sense R on your target - Choose between 1 mΩ to 1 MΩ - Check the resistor power rating ($P = I^2R$) - Order N2825A for replacement head |
| <p>20 mΩ</p>  | <p>100 mΩ</p>  | <p>User-defined</p>  |

Figure 2. Types of sense resistor heads.

The supplied Make-Before-Break (MBB) connectors allow you to quickly probe multiple locations on your DUT without having to solder or unsolder the leads. The MBB header may be mounted on the user's target board. It fits into standard 0.1" spacing for 0.025" square pins. Users should plan their PCB layouts accordingly. The MBB can be used with all sense resistor probe heads including the user-defined probe head. The MBBs are a great way to easily connect and disconnect across multiple locations on the target board without interrupting the circuit under test.



Figure 3. Probing with the MBB connector.

Two channel versus one channel

Keysight offers two current probe models in the N2820A Series: N2820A two-channel and N2821A one-channel. The N2821A looks identical to the N2820A probe but does not include the secondary cable that is shown in Figure 4. The N2820A probe connects to two oscilloscope channels to provide simultaneous low and high gain views for wider dynamic range measurement, while the N2821A probe provides one user-selectable view at a time.



Figure 4. The N2820A 2-channel high-sensitivity current probe. The N2821A does not include the secondary cable.

Current consumption over time measurement

With current waveforms captured, you now want to calculate the average current consumption of the system over time. Keysight's Infiniium oscilloscopes provide an area under the curve measurement (Charge) where you can easily calculate the integrated current consumptions over time.




Figure 5. Infiniium oscilloscope coupled with the N2820A current probe provides the area under the curve measurement for accurate current consumption measurement.

Oscilloscope compatibility

The N2820A and N2821A current probes are compatible with Keysight oscilloscopes shown in the characteristics table. The N2820A Series current probes, together with Keysight's Infiniium 9000 H-Series high-definition oscilloscopes, deliver the ultimate high definition measurement solution, letting users view and resolve small current details not traditionally seen on 8-bit oscilloscopes.



Figure 6. The InfiniiVision 3000 X- or 4000 X-Series oscilloscope can also be paired with the N2820A/21A current probes to provide the same simultaneous low- and/or high-gain views for wider dynamic range current measurement.

| Probe characteristics | | |
|---|--|---|
| Bandwidth (-3 dB) | Zoom-out channel: DC to 3 MHz | |
| | Zoom-in channel: DC to 500 kHz | |
| Risetime ($T_r = 0.35/\text{bandwidth}$, 10 to 90%) | Zoom-out channel: < 0.116 μsec | |
| | Zoom-in channel: < 0.7 μsec | |
| Minimum measurable current ¹ | 250 μA (with N2822A 20 m Ω , 500 mW) | |
| | 50 μA (with N2824A 100 m Ω , 500 mW) | |
| | 5 mA (with N2825A user-defined 1 m Ω , 500 mW) | |
| | 500 nA (with N2825A user-defined 1 k Ω , 500 mW) | |
| Maximum measurable current | 5 A (with N2822A 20 m Ω , 500 mW) | |
| | 2.2 A (with N2824A 100 m Ω , 500 mW) | |
| | 5 A ² (with N2825A user-defined 1 m Ω , 500 mW) | |
| | 1.2 mA ² (with N2825A user-defined 1 k Ω , 500 mW) | |
| Gain ⁵ | Zoom-in channel: 300 \pm 3% | |
| | Zoom-out channel: 1.97 \pm 3% | |
| Output voltage rate | Zoom-in channel: 6 V/A (with N2822A 20 m Ω) 30 V/A (with N2824A 100 m Ω) | |
| | Zoom-out channel: 0.04 V/A (with N2822A 20 m Ω) 0.2 V/A (with N2824A 100 m Ω) | |
| DC amplitude accuracy | \pm 3% or 10 μA (whichever is greater) | |
| Max input voltage | \pm 12 V | |
| Burden voltage (voltage drop on Rsense) | Measured current ¹ Rsense | |
| Dynamic range | 20,000:1, 86 dB (N2820A) | |
| | 1,000:1, 60 dB (N2821A) | |
| Output impedance | 1 M Ω | |
| Noise (ACrms) | 150 μA (with N2822A 20 m Ω , hi res mode on) ³ | |
| | 240 μA (with N2822A 20 m Ω , hi res mode off) | |
| | 30 μA (with N2824A 100 m Ω , hi res mode on) ³ | |
| | 50 μA (with N2824A 100 m Ω , hi res mode off) | |
| Sensor resistor accuracy | \pm 1% (N2822A, N2824A) | |
| Sensor resistor power rating | 500 mW (N2822A, N2824A) | |
| Temperature coefficient of sensor resistor | < 20 ppm/ $^{\circ}\text{C}$ | |
| Cable lengths | Sensor leads: 16 cm | |
| | Probe cable: 1.2 m | |
| Temperature | Operating: 0 to +40 $^{\circ}\text{C}$ | |
| | Non-operating: -40 to +70 $^{\circ}\text{C}$ | |
| Humidity | Operating: tested at 95% RH at +40 $^{\circ}\text{C}$ | |
| | Non-operating: tested at 90% RH, +65 $^{\circ}\text{C}$ | |
| ESD | 8 kV HBM | |
| Standard accessories | 1 each 20 m Ω resistor sensor head | 5 each MBB headers |
| | 1 each 100 m Ω resistor sensor head | 5 each MBB receptacles |
| | 1 each user defined resistor sensor head | 1 each ground lead |
| | 5 each twisted leads (22 AWG) with sockets | 1 each screw driver |
| | 5 each twisted leads (22 AWG) without sockets | 1 each passive cable (with N2820A only) |
| | | 1 each user guide manual (English) |
| Compatible oscilloscopes | InfiniiVision 3000 X-Series (with software version 2.30 or higher) | |
| | InfiniiVision 4000 X-Series (with software version 3.10 or higher) and 6000 X-Series | |
| | Infiniium S, 9000A, 9000 H-Series (with software version 4.20 or higher) ⁴ | |

1. Vsupply is equal to 5 V, solder attached.

2. Max current varies with max resistor power rating. The examples in the table assume 500 mW power rating.

3. With scope with high resolution mode on, sampling rate < 2.5 MSa/s, 20 MHz low pass filter on.

4. Infiniium V, 90000A, 90000 X-, and 90000 Q-Series are not compatible with N2820A/21A current probe.

5. Denotes warranted specification after 20-minute warm up. All others entries in the table are characteristics.

Product configuration

| Model numbers | Descriptions |
|---------------|--|
| N2820A | High-sensitivity 2-ch current probe |
| N2821A | High-sensitivity 1-ch current probe |

| Replacement part numbers | Descriptions |
|--------------------------|--|
| N2822A | 20 mΩ resistor tips |
| N2824A | 100 mΩ resistor tips |
| N2825A | User-defined resistor tips |
| N2826A | Replacement wires (15.5 cm, 22 AWG bare wires) (qty 5) |
| N2827A | Passive cable (for N2820A secondary channel) |
| N2828A | Replacement MBB (Make Before Break) headers (qty 5) |
| N2829A | Replacement MBB (Make Before Break) receptacles and 15.5 cm, AWG 22 socketed wires (qty 5 each) |




Figure 7. Minimum/Maximum current range with N2822A/N2824A head, 500 mW sense R, solder attached, High resolution mode on.




Figure 8. N2825A head.



www.axistandard.org

AdvancedTCA® Extensions for Instrumentation and Test (AXIe) is an open standard that extends the AdvancedTCA for general purpose and semiconductor test. The business that became Keysight was a founding member of the AXIe consortium. ATCA®, AdvancedTCA®, and the ATCA logo are registered US trademarks of the PCI Industrial Computer Manufacturers Group.



www.lxistandard.org

LAN eXtensions for Instruments puts the power of Ethernet and the Web inside your test systems. The business that became Keysight was a founding member of the LXI consortium.




www.pxisa.org

PCI eXtensions for Instrumentation (PXI) modular instrumentation delivers a rugged, PC-based high-performance measurement and automation system.

Evolving

Our unique combination of hardware, software, support, and people can help you reach your next breakthrough. **We are unlocking the future of technology.**



From Hewlett-Packard to Agilent to Keysight

myKeysight

myKeysight

www.keysight.com/find/mykeysight

A personalized view into the information most relevant to you.

KEYSIGHT SERVICES

Accelerate Technology Adoption.
Lower costs.

Keysight Services

www.keysight.com/find/service

Our deep offering in design, test, and measurement services deploys an industry-leading array of people, processes, and tools. The result? We help you implement new technologies and engineer improved processes that lower costs.



Three-Year Warranty

www.keysight.com/find/ThreeYearWarranty

Keysight's committed to superior product quality and lower total cost of ownership. Keysight is the only test and measurement company with three-year warranty standard on all instruments, worldwide. And, we provide a one-year warranty on many accessories, calibration devices, systems and custom products.



Keysight Assurance Plans

www.keysight.com/find/AssurancePlans

Up to ten years of protection and no budgetary surprises to ensure your instruments are operating to specification, so you can rely on accurate measurements.

Keysight Channel Partners

www.keysight.com/find/channelpartners

Get the best of both worlds: Keysight's measurement expertise and product breadth, combined with channel partner convenience.

www.keysight.com/find/N2820A

For more information on Keysight Technologies' products, applications or services, please contact your local Keysight office. The complete list is available at: www.keysight.com/find/contactus

Americas

| | |
|---------------|------------------|
| Canada | (877) 894 4414 |
| Brazil | 55 11 3351 7010 |
| Mexico | 001 800 254 2440 |
| United States | (800) 829 4444 |

Asia Pacific

| | |
|--------------------|----------------|
| Australia | 1 800 629 485 |
| China | 800 810 0189 |
| Hong Kong | 800 938 693 |
| India | 1 800 11 2626 |
| Japan | 0120 (421) 345 |
| Korea | 080 769 0800 |
| Malaysia | 1 800 888 848 |
| Singapore | 1 800 375 8100 |
| Taiwan | 0800 047 866 |
| Other AP Countries | (65) 6375 8100 |

Europe & Middle East

| | |
|----------------|---------------|
| Austria | 0800 001122 |
| Belgium | 0800 58580 |
| Finland | 0800 523252 |
| France | 0805 980333 |
| Germany | 0800 6270999 |
| Ireland | 1800 832700 |
| Israel | 1 809 343051 |
| Italy | 800 599100 |
| Luxembourg | +32 800 58580 |
| Netherlands | 0800 0233200 |
| Russia | 8800 5009286 |
| Spain | 800 000154 |
| Sweden | 0200 882255 |
| Switzerland | 0800 805353 |
| | Opt. 1 (DE) |
| | Opt. 2 (FR) |
| | Opt. 3 (IT) |
| United Kingdom | 0800 0260637 |

For other unlisted countries:
www.keysight.com/find/contactus
(BP-11-29-16)



www.keysight.com/go/quality
Keysight Technologies, Inc.
DEKRA Certified ISO 9001:2015
Quality Management System