

Accessories ZB 10 F.10X3/10X5/10X10

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16 D-32758 Detmold

Germany

Fon: +49 5231 1429-0 Fax: +49 5231 14292083 www.weidmueller.com







Building installation wiring

For building installations, we offer a complete system that revolves around the 10×3 copper rail and comprises perfectly coordinated components: from installation terminal blocks, neutral conductor terminal blocks and distribution terminal blocks to comprehensive accessories such as busbars and busbar holders.

General ordering data

Туре	ZB 10 F.10X3/10X5/10X10
Order No.	<u>1261300000</u>
Version	Accessories, Clamping yoke for busbar, Rated cross-section: Clamping yoke, Feed-through (bushing)
GTIN (EAN)	4008190180201
Qty.	50 pc(s).



Accessories ZB 10 F.10X3/10X5/10X10

Weidmüller Interface GmbH & Co. KG

Silver

Klingenbergstraße 16 D-32758 Detmold

Germany

Fon: +49 5231 1429-0 Fax: +49 5231 14292083 www.weidmueller.com

Technical data

Dimensions and weights

Width	8 mm	Width (inches)	0.315 inch
Height	19.5 mm	Height (inches)	0.768 inch
Depth	29.1 mm	Depth (inches)	1.146 inch
Net weight	9.28 g		
Material data			

Colour

Rating data IECEx/ATEX

Material

Certificate No. (ATEX)	DEMKO03ATEX136028U	Certificate No. (IECEX)	IECEXULD13.0005U
Wire cross section max. (ATEX)	10 mm²	Wire cross section max. (IECEX)	10 mm²
Operating temperature range	For operating temperature range see EC Design Test Certificate / IEC Ex-	Ex 2014/34/EU label	
	Certificate of Conformity		II 2 G D
Safety notice	Installation instructions:		

The potential equalisation (PE) rail modules are suitable for use in housings in atmospheres with flammable gases and dust. For use in areas with flammable gases, these housings must meet the requirements of EN 60079-0 and EN 60079-7. For use in areas with flammable dust, these housings must meet the requirements of EN 60079-0 and EN 60079-31. When combined with other terminal block ranges and sizes, and

Steel

when other accessories are used, you must comply with the clearance and creepage distances given. Regarding accessory use, the manufacturer's instructions must be followed. List of restrictions: The PE rail modules are considered one component, with Ex marking when used with the busbar holders of type SH and WEW. When used independently, the above named components are not covered by this certificate.

System specifications

Version	for busbar 10 x 3 mm, for	
	busbar 10 x 5 mm	



Accessories ZB 10 F.10X3/10X5/10X10

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16 D-32758 Detmold Germany

Fon: +49 5231 1429-0 Fax: +49 5231 14292083 www.weidmueller.com

Technical data

Additional technical data

Feed-through (bushing)	Type of mounting	Screwed	
10400 007	\A/' (OOA)	0.4140	
	Vire cross section max. (CSA)	6 AWG	
	Feed-through (bushing) 12400-237 14 AWG	12400-237 Wire cross section max. (CSA)	12400-237 Wire cross section max. (CSA) 6 AWG

Conductors for clamping (rated connection)

Clamping screw	M 4	Stripping length	19 mm
Tightening torque, min.	1.2 Nm	Type of connection	Clamping yoke
Wire connection cross section, fine	ely	Wire connection cross section, so	olid
stranded, max.	10 mm ²	core max. rated connection	10 mm²
Wire connection cross section, soli	d	Wire connection cross-section, fir	nely
core, min. rated connection	1.5 mm ²	stranded, min.	2.5 mm ²

UL rating data

Certificate No. (UR)	E60693	Conductor size Factory wiring max. (UR) 6 AWG
Conductor size Factory wiring min. (UR)	16 AWG	Conductor size Field wiring max. (UR) 6 AWG
Conductor size Field wiring min. (UR)	16 AWG	

Classifications

ETIM 3.0	EC000001	ETIM 4.0	EC000001
ETIM 5.0	EC000001	ETIM 6.0	EC002848
UNSPSC	30-21-18-11	eClass 5.1	27-14-11-31
eClass 6.2	27-14-11-90	eClass 7.1	27-14-11-90
eClass 8.1	27-14-11-90	eClass 9.0	27-14-11-90
eClass 9.1	27-14-11-92		

Approvals

Approvals



ROHS	Conform

Downloads

Engineering Data EPI	
	LAN, WSCAD