

SmartPro 120V 1kVA 750W Medical-Grade Line-Interactive Tower UPS, 4 Outlets, Full Isolation, Expandable Runtime

MODEL NUMBER: **SMART1200XLHG**



Description

Tripp Lite's SMART1200XLHG medical-grade UPS system provides dependable battery backup and is fully compliant with UL 60601-1 regulations when plugged into a hospital-grade outlet, making it ideal for use in patient-care vicinities. The 1kVA/750W capacity provides up to 28 minutes of runtime for a half load or 10 minutes for a full load, so you can work through short power failures and perform an orderly system shutdown in a prolonged blackout.

Built-in line-interactive voltage regulation corrects brownouts as low as 81V and overvoltages as high as 143V to normal 120V nominal output without drawing battery power. The SMART1200XLHG's built-in isolation transformer with Faraday shield offers full isolation and removes common mode noise, while maintaining full AC surge suppression in all modes.

This UPS system features four NEMA 5-15R-HG hospital-grade outlets and has a hospital-grade NEMA 5-15P-HG plug with a six-foot cord for flexibility in placement. All four outlets provide both backup protection and surge protection rated to 940 joules.

The SMART1200XLHG also features diagnostic LEDs, as well as a USB port and a DB9 serial port that work with Tripp Lite's included PowerAlert software for safe, unattended system shutdown and file saves in the event of a prolonged power failure.

Features

Ideal UPS Backup in Healthcare Facilities

- Complies with UL 60601-1 standards for use in patient-care facilities
- Isolation transformer with Faraday shield offers full isolation and removes common mode noise
- 6 ft. power cord with 120V NEMA 5-15P-HG plug
- Floating AC output prevents noise coupling and meets agency requirements for isolation

Reliable Battery Backup and Surge Protection

- Supports half load up to 28 min. and full load up to 10 min.
- 4 NEMA 5-15R-HG outlets with 940-joule surge protection

Highlights

- 940-joule surge protection rating protects connected equipment
- 4 NEMA 5-15R-HG outlets and 120V NEMA 5-15P-HG plug
- Floating AC output prevents noise coupling
- Alarm mute/quiet control ideal for use near patients
- 28 min. runtime at half load; 10 min. at full load

Package Includes

- SMART1200XLHG 1kVA/750W Medical-Grade Tower UPS System
- USB monitoring cable, 6 ft.
- DB9 serial monitoring cable, 6 ft.
- PowerAlert Software
- Owner's Manual



- Filters out disruptive EMI/RFI line noise that can cause equipment damage or data loss
- Resists electrostatic discharge

LEDs and Audible Alarms

- Front LEDs indicate power, mode, load and battery status
- Alarms alert you to power failure, overload and low battery
- Mute/quiet mode ideal for use in quiet patient-care vicinities

Saves Files When You're Away

- Included PowerAlert® software enables safe, unattended system shutdown and file saving during power failures
- Connects to computer via DB9 or USB port with included cables

Specifications

OUTPUT	
Output Volt Amp Capacity (VA)	1000
Output kVA Capacity (kVA)	1
Output Watt Capacity (Watts)	750
Power Factor	0.8
Nominal Output Voltage(s) Supported	115V; 120V
Frequency Compatibility	60 Hz
Output Voltage Regulation (Line Mode)	-18%, +8%
Output Voltage Regulation (Battery Mode)	115V (+/- 5%)
Output Receptacles	(4) 5-15R
Output Receptacle Details	Hospital grade output receptacles
Output AC Waveform (AC Mode)	Sine wave
Output AC Waveform (Battery Mode)	PWM sine wave
INPUT	
Rated input current (Maximum Load)	9.2A
Nominal Input Voltage(s) Supported	120V AC
UPS Input Connection Type	5-15P-HG
Input Circuit Breakers	15A
UPS Input Cord Length (ft.)	6
UPS Input Cord Length (m)	1.8
Recommended Electrical Service	15A 120V



Input Cord Length (ft.)	6
Input Cord Length (m)	1.83
Input Phase	Single-Phase
BATTERY	
Full Load Runtime (min.)	10 min. (750w)
Half Load Runtime (min.)	28 min. (375w)
Expandable Battery Runtime	Extended runtime supported via optional external battery packs
External Battery Pack Compatibility	BP36V15-2U(limit 1); BP36V27-2US(multi-pack compatible); BP36V42-3U(multi-pack compatible)
DC System Voltage (VDC)	36
Battery Recharge Rate (Included Batteries)	Less than 4.5 hours from 10% to 90%
Internal UPS Replacement Battery Cartridge	RBC36SLT
Battery Access	Battery access door
Battery Replacement Description	Hot-swappable, user replaceable batteries
Expandable Runtime	Yes
VOLTAGE REGULATION	
Voltage Regulation Description	Automatic voltage regulation (AVR) maintains line power operation with an input voltage range of 81 to 143
Overvoltage Correction	Input voltages between 126 and 143 are reduced by 9%
Undervoltage Correction	Input voltages between 96 and 106 are boosted by 10%
Severe Undervoltage Correction	Input voltages between 81 and 95 are boosted by 21%
USER INTERFACE, ALERTS & CONTROLS	
Switches	2 Switches control off/on power status and alarm-cancel/self-test operation
Alarm Cancel Operation	Power-fail alarm can be silenced using alarm-cancel switch; once silenced, alarm will re-sound to indicate low-battery status
Audible Alarm	Factory-muted audible alarm indicates power-failure, overload and low-battery conditions
LED Indicators	5 LEDs indicate line power, battery power, overload, voltage regulation and battery low/replace status
SURGE / NOISE SUPPRESSION	
UPS AC Suppression Joule Rating	940
UPS AC Suppression Response Time	Instantaneous
EMI / RFI AC Noise Suppression	Yes
AC Suppression Joule Rating	940



ISOLATION	
Output Isolation Transformer	Hospital grade load isolation transformer
Leakage Current	Less than 100 microamps
PHYSICAL	
Installation Form Factors Supported with Optional Accessories	Wallmount(UPSWM - tower mounting kit)
Primary Form Factor	Tower
UPS Power Module Dimensions (hwd, in.)	12.5 x 7.5 x 9.5
UPS Power Module Dimensions (hwd, cm)	31.75 x 19.05 x 24.13
UPS Power Module Weight (lbs.)	45.2
UPS Power Module Weight (kg)	20.50
UPS Shipping Dimensions (hwd / in.)	18.2 x 11.8 x 13.5
UPS Shipping Dimensions (hwd / cm)	46.23 x 29.97 x 34.29
Shipping Weight (lbs.)	51
Shipping Weight (kg)	23.2
Cooling Method	Fan
UPS Housing Material	PVC
Primary UPS Height (mm)	318
Primary UPS Width (mm)	190
Primary UPS Depth (mm)	241
Shipping Height (mm)	462
Shipping Width (mm)	300
Shipping Depth (mm)	343
ENVIRONMENTAL	
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius
Relative Humidity	0 to 95%, non-condensing
AC Mode BTU / Hr. (Full Load)	162.8
Battery Mode BTU / Hr. (Full Load)	315.2
AC Mode Efficiency Rating (100% Load)	94%
COMMUNICATIONS	



Communications Interface	USB; DB9 Serial
Network Monitoring Port Description	Supports detailed monitoring of UPS and site power conditions
PowerAlert Software	For local monitoring via the UPS's built-in communication ports , download PowerAlert Local software at http://www.tripplite.com/poweralert
Communications Cable	USB and DB9 serial cabling included
LINE / BATTERY TRANSFER	
Transfer Time	2-4 milliseconds
Low Voltage Transfer to Battery Power (Setpoint)	81
High Voltage Transfer to Battery Power (Setpoint)	143
SPECIAL FEATURES	
Grounding Lug	Grounding lug (equipotential)
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported
High Availability UPS Features	Hot swappable batteries
CERTIFICATIONS	
UPS Certifications	Tested to UL1778 (USA); Tested to CSA (Canada); Meets FCC Part 15 Category A (EMI); Tested to UL60601-1 (medical grade)
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>