

SPECIFICATIONS - ERG50P

- I. INSTALLS 18-50 LB (80-222 N) CABLE TIES
- 2. ADJUSTABLE TENSION SETTINGS 1-8
- 3. INTEGRATED TENSION LOCKING SCREW
- 4. 360° ROTATING NOSE
- 5. I" [25.4mm] STROKE AIR CYLINDER WITH ANTI-RECOIL MECHANISM
- HIGH IMPACT POLYMER CONSTRUCTION WITH SOFT OVERMOLDED GRIP
- OVERSIZED ACTUATION TRIGGER
- 8. RETRACTABLE TOOL HANGERS ON TOP AND REAR OF TOOL
- 9. SPARE BLADE STORAGE, ONE SPARE BLADE INCLUDED-BLADE PART# CDS010461
- 10. 9 FT PNEUMATIC HOSE WITH QUICK-CONNECT COUPLER INCLUDED
- II. TOOL OPERATES ON 85-100 PSI NON-LUBRICATED AIR
- 12. TOOL WEIGHT 14 OZ

GENERAL NOTES Thomas@Betts *Ty-Rap** ALL DIMENSIONS ARE FOR REFERENCE ONLY. DIMENSIONS IN BRACKETS [] ARE IN METRIC UNITS. **ERG50P PNEUMATIC CABLE TIE** DESCRIPTION: **REVISIONS** INSTALLATION TOOL SEE ERN (****) DRAWING NO: FOR APPROVAL SIGNATURES ORIGINAL PROJECT NO / (ERN NO) SHEET NO: REV. NO: & RELEASE DATE. **WSD-000415** PROJECT NO: **** FD55630 / (2009886) 1 OF 1