

SmartOnline 120V 3kVA 2.4kW Double-Conversion UPS, 3U Rack/Tower, Extended Run, Pre-installed Network Management Card, USB, DB9 Serial

MODEL NUMBER: **SU3000RTXL3UN**



Description

Tripp Lite Smart Online UPS systems offer high performance power protection ideal for critical server and network equipment in datacenters, computer rooms and network closets. Online, double-conversion Uninterruptible Power Supply (UPS) maintains perfectly regulated output power by continuously converting raw AC input to DC, then re-converting output back to AC. Fully regulated sine wave AC output with +/-2% voltage regulation powers network equipment continuously, even during severe brownouts and overvoltages, all without depleting UPS battery reserves. Maintains battery-derived AC output during power failures with zero transfer time. Extended runtime options available. Highly efficient operation in optional economy mode saves BTU heat output and energy costs. Network management interfaces support communications via USB, RS-232, contact-closure and Pre-installed Network Management Card interface. Built-in DB9 port offers both enhanced RS-232 data and basic contact closure monitoring ability. HID-compliant USB interface enables integration with built-in power management and auto shutdown features of Windows and Mac OS X. PowerAlert UPS monitoring software is available via free download. Emergency Power Off (EPO) interface. LED display reports UPS operating mode, line power availability, battery mode operation, inverter operation and output power availability. Audible alarm with push-button momentary alarm-cancel. Programmable self-test. Fault-tolerant auto-bypass mode. Field-replaceable, hot-swappable internal batteries and external battery packs.

Features

- Tripp Lite SU3000RTXL3UN 3000VA / 3kVA / 2400W on-line, double-conversion 3U rackmount UPS
- Selectable 110/120V output (120V factory preset)
- NEMA L5-30P input, 4 NEMA 5-15/20R, 4 5-15R & 1 L5-30R outlets
- Two switched 4-outlet load banks support remote reboot or programmable load shedding options
- Supports 2% output voltage regulation and zero transfer time in double conversion mode
- Economy mode option offers enhanced efficiency operation, reduced power consumption and lower BTU emissions
- 14 minutes runtime at 50% load (1200W) and 5 minutes at 100% load (2400W) with internal batteries
- [BP72V15-2U](#) (limit 1), [BP72V28RT-3U](#) (multi-pack compatible) and [BP72V18-2US](#) (multi-pack compatible) external battery packs available (some configurations require Tripp Lite's External Battery Configuration Software)

Highlights

- 3000VA / 3kVA / 2400 watt on-line double-conversion 3U rack/tower UPS
- 110/120V +/-2% output at 50/60Hz, high efficiency economy mode option
- Expandable runtime, Hot-swap batteries, 26 in. / 66cm installed depth
- USB, RS232, EPO ports and Pre-installed Network Management Card interface
- Front panel status LEDs with detailed load and battery metering
- 2 independently switchable output load banks
- NEMA L5-30P input; L5-30R, 5-15/20R & 5-15R outlets

Package Includes

- SU3000RTXL3UN UPS with Pre-installed Network Management Card
- USB, DB9 and EPO Cabling
- Mounting hardware for 4 post rack enclosures
- Instruction manual



- Intelligent battery management system extends battery life
- LED Display reports UPS operating mode, line power availability, battery mode operation, inverter status and output power availability
- Audible alarm with push-button momentary alarm-cancel
- 4 post installation hardware included, Optional [2POSTRMKITHD](#) enables 2 post rack installation
- Single line TEL / Network surge suppression
- Electronic bypass maintains utility output during a variety of UPS fault conditions
- Built-in USB, RS-232, contact-closure and pre-installed Network Management Card interface
- HID-compliant USB interface enables integration with built-in power management and auto shutdown features of Windows and Mac OS X
- USB & Serial ports enable data-saving unattended shutdown when used with Tripp Lite's PowerAlert software, available via FREE download from www.tripplite.com/poweralert

Specifications

OUTPUT	
Output Volt Amp Capacity (VA)	3000
Output kVA Capacity (kVA)	3
Output Watt Capacity (Watts)	2400
Output kW Capacity (kW)	2.4
Output Capacity Details	OVERLOAD CAPACITY: Supports inverter operation up to 105% load continuously, 125% load for 3 minutes; 150% load for 30 seconds and >150% load for 0.5 seconds before switching to BYPASS (when bypass input voltage and frequency are WITHIN bypass limits) or SHUTDOWN (when bypass input voltage or frequency are OUTSIDE bypass limits)
Power Factor	0.8
Crest Factor	3:1
Nominal Output Voltage(s) Supported	110V; 120V
Nominal Voltage Details	120V default
Frequency Compatibility	50 / 60 Hz
Frequency Compatibility Details	Output frequency matches input nominal on startup, defaults to 60 Hz on cold-start
Output Voltage Regulation (Line Mode)	+/- 2%
Output Voltage Regulation (Economy Line Mode)	+/- 10%
Output Voltage Regulation (Battery Mode)	+/- 2%
Output Receptacles	(4) 5-15R; (4) 5-15/20R; (1) L5-30R
Load Management Receptacles	Two switchable four-outlet load banks, (bank 1 - four 5-15/20R, bank 2 - four 5-15R outlets)
Output Circuit Breakers	15A branch rated (x2) - each breaker protects 4 outlets, L5-30R is unbreakered
Output AC Waveform (AC Mode)	Sine wave
Output AC Waveform (Battery Mode)	Pure Sine wave



INPUT	
Rated input current (Maximum Load)	24A
Nominal Input Voltage(s) Supported	110V AC; 120V AC
UPS Input Connection Type	L5-30P
Input Circuit Breakers	40A
UPS Input Cord Length (ft.)	10
UPS Input Cord Length (m)	3.0
Recommended Electrical Service	30A 120V
Input Phase	Single-Phase
BATTERY	
Full Load Runtime (min.)	5 min. (2400w)
Half Load Runtime (min.)	14 min. (1200w)
Expandable Battery Runtime	Supports extended runtime with optional external battery packs
External Battery Pack Compatibility	BP72V15-2U (limit 1); BP72V28RT-3U (multi-pack compatible); BP72V18-2US (multi-pack compatible)
DC System Voltage (VDC)	72
Battery Recharge Rate (Included Batteries)	Less than 6 hours from 10% to 80% (typical, full load discharge)
Internal UPS Replacement Battery Cartridge	RBC96-3U (quantity 1)
Battery Access	Front panel battery access door
Battery Replacement Description	Hot-swappable, user replaceable batteries
Expandable Runtime	Yes
VOLTAGE REGULATION	
Voltage Regulation Description	Online, double-conversion power conditioning
Overvoltage Correction	2% output voltage regulation during overvoltages to 150
Undervoltage Correction	2% output voltage regulation during undervoltages to 80
Severe Undervoltage Correction	2% output voltage regulation during undervoltages to 65 (under 70% load only)
USER INTERFACE, ALERTS & CONTROLS	
Switches	2 switches control off/on power status and alarm-cancel/self-test operation
Alarm Cancel Operation	Power-fail alarm can be silenced using alarm-cancel switch
Audible Alarm	Audible alarm indicates UPS startup, power-failure, low-battery, overload, UPS fault and remote shutdown conditions
LED Indicators	14 LEDs indicate line power, online mode, economy/bypass mode, on-battery, overload, battery low, replace battery and fault status information; 4-LED meter displays load and battery charge levels; LED panel rotates for viewing in rack/tower formats



SURGE / NOISE SUPPRESSION	
UPS AC Suppression Joule Rating	510
UPS AC Suppression Response Time	Instantaneous
UPS Dataline Suppression	1 line TEL/DSL (1 in / 1 out); 10/100Base T Ethernet
EMI / RFI AC Noise Suppression	Yes
PHYSICAL	
Included Mounting Accessory Description	Includes 4 post rackmount installation accessories
Installation Form Factors Supported with Optional Accessories	2 post rackmount(2POSTRMKITHD); Tower(2-9USTAND)
Primary Form Factor	Rackmount
UPS Power Module Dimensions (hwd, in.)	5.2 x 17.8 x 26
UPS Power Module Dimensions (hwd, cm)	13.21 x 45.21 x 66.04
Rack Height (U Spaces)	3
Minimum Required Rack Depth (inches)	37
Minimum Required Rack Depth (cm)	93.98
UPS Power Module Weight (lbs.)	73.8
UPS Power Module Weight (kg)	33.48
UPS Shipping Dimensions (hwd / in.)	11.2 x 23 x 31.5
UPS Shipping Dimensions (hwd / cm)	28.45 x 58.42 x 80.01
Shipping Weight (lbs.)	112.4
Shipping Weight (kg)	51
Cooling Method	Fan
UPS Housing Material	Steel
Minimum Required Rack Depth (mm)	940
Primary UPS Height (mm)	132
Primary UPS Width (mm)	452
Primary UPS Depth (mm)	660
Shipping Height (mm)	284
Shipping Width (mm)	584
Shipping Depth (mm)	800



ENVIRONMENTAL	
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius
Relative Humidity	0 to 95%, non-condensing
AC Mode BTU / Hr. (Full Load)	1117
AC Economy Mode BTU / Hr. (Full Load)	523
Battery Mode BTU / Hr. (Full Load)	1224
AC Economy Mode Efficiency Rating (100% Load)	94%
COMMUNICATIONS	
Communications Interface	Contact closure; DB9 Serial; EPO (emergency power off); Pre-installed network card; Slot for SNMP/Web interface; USB (HID enabled)
Network Monitoring Port Description	Includes pre-installed Network Management Card; DB9 port supports RS232 and contact closure communications; Economy-mode setting option is available using PowerAlert software and DB9 Serial cable connection OR installed Network Management Card
PowerAlert Software	For local monitoring via the UPS's built-in communication ports, download PowerAlert Local software at http://www.tripplite.com/poweralert
Communications Cable	USB and DB9 cabling included
WatchDog Compatibility	Supports Watchdog application, OS and hard-reboot restart options for remote applications
LINE / BATTERY TRANSFER	
Transfer Time	No transfer time (0 ms.) in online, double-conversion mode
Low Voltage Transfer to Battery Power (Setpoint)	80V (100% load), 65V (<70% load)
High Voltage Transfer to Battery Power (Setpoint)	150
SPECIAL FEATURES	
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported
High Availability UPS Features	Automatic inverter bypass; Hot swappable batteries
Green Energy-Saving Features	High efficiency economy mode operation; Individually controllable load banks; Schedulable daily hours of economy mode operation
CERTIFICATIONS	
UPS Certifications	Tested to UL1778 (USA); Tested to CSA (Canada); Tested to NOM (Mexico); Meets FCC Part 15 Category A (EMI)
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$250,000 Ultimate Lifetime Insurance
---	---

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>