

## SmartPro 120V 550VA 300W Line-Interactive UPS, AVR, Tower, USB, Surge-only Outlets

MODEL NUMBER: **SMART550USB**



### Highlights

- 550VA tower 120V line interactive UPS
- Corrects brownouts as low as 89V without using battery power
- 3 UPS battery supported outlets, 3 surge-only outlets
- USB port, TEL/DSL/ethernet protection
- NEMA 5-15P input plug and 6 NEMA 5-15R outlets

### Package Includes

- SMART550USB UPS System
- USB and Telephone interconnection cables
- Instruction manual with warranty information

### Description

Tripp Lite's SMART550USB line interactive UPS system offers voltage regulation, surge suppression and long lasting battery support for personal computers, internetworking equipment and other sensitive electronics. Internal UPS circuits support entry level PC systems for up to 30 minutes during power failures so that connected equipment can be shutdown without data loss. Automatic Voltage Regulation (AVR) circuits regulate brownouts as low as 89 volts back to usable levels without using battery power. Offers complete desktop power protection in an attractive stealth black tower configuration. Includes 3 battery supported outlets for computer, monitor and one vital system peripheral, plus 3 additional surge suppression-only outlets for printers and other system accessories not requiring battery support. USB port enables optional unattended system shutdown without data loss in the case of extended power failure, USB cable included. PowerAlert software available via free download from [www.tripplite.com](http://www.tripplite.com). Built-in single line RJ11 phone suppression jacks protect modem, fax machine, cordless phone or other peripheral with a standard dialup/DSL phone connection. Built-in audible alarm and 4 front panel LEDs indicate line power status, battery power status, battery low/replace status and overload status. 550VA/300 watt power handling ability supports entry-level PCs, network workstations, point-of-sale equipment, small business phone systems, audio/video equipment and home theater systems. Offers 4.6 minutes battery runtime with a full load of 550VA/300 watts and 14.8 minutes with a half load of 275VA/150 watts. Supports battery replacement via built-in access panel. \$200,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only).

### Features

- SMART550USB line interactive UPS system offers voltage regulation and battery support, plus complete AC and dialup/DSL modem line surge suppression
- Supports entry level PC systems for up to 30 minutes during power failures to enable a safe system shutdown
- Supports a max load of 550VA/300 watts for 4.6 minutes and a half load of 275VA/150 watts for 14.8 minutes
- Automatic Voltage Regulation (AVR) circuits correct brownouts as low as 89 volts without using battery power
- Attractive stealth black tower configuration
- Includes 3 battery supported outlets, plus 3 additional surge suppression-only outlets, 6 foot AC line cord (all NEMA 5-15)
- USB port enables unattended shutdown without data loss during extended power failures, includes USB cable
- PowerAlert software available via free download from [www.tripplite.com](http://www.tripplite.com)
- Built-in RJ11 phone suppression jacks protect modem, fax machine or other peripheral with a dialup or DSL line phone connection
- Built-in audible alarm and 4 front panel LEDs indicate UPS system and line power status



- 550VA/300 watt power handling ability supports a variety of computer, internetworking, telecom and consumer electronics equipment
- Supports battery replacement via built-in access panel
- Compatible with 120V/60Hz applications for USA, Canada, Mexico and more
- \$200,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

## Specifications

OUTPUT	
Output Volt Amp Capacity (VA)	550
Output Watt Capacity (Watts)	300
Nominal Output Voltage(s) Supported	110V; 115V; 120V
Nominal Voltage Details	115v nominal output in battery mode
Frequency Compatibility	60 Hz
Output Voltage Regulation (Battery Mode)	+/- 5%
Output Receptacles	(6) 5-15R
UPS Output Receptacles (Surge Suppression Only)	3 UPS outlets, 3 surge-only outlets
Output AC Waveform (AC Mode)	Sine wave
Output AC Waveform (Battery Mode)	PWM sine wave
INPUT	
Rated input current (Maximum Load)	10A
Nominal Input Voltage(s) Supported	120V AC
UPS Input Connection Type	5-15P; Right-Angled
UPS Input Cord Length (ft.)	6
UPS Input Cord Length (m)	1.8
Recommended Electrical Service	15A 120V
Input Phase	Single-Phase
BATTERY	
Full Load Runtime (min.)	4.6 min. (300w)
Half Load Runtime (min.)	14.8 min. (150w)
DC System Voltage (VDC)	12
Battery Recharge Rate (Included Batteries)	Less than 4.2 hours from 10% to 90%
Internal UPS Replacement Battery Cartridge	<a href="#">RBC51</a>



Battery Access	Battery access door
Battery Replacement Description	Hot-swappable, user replaceable batteries
Expandable Runtime	No
<b>VOLTAGE REGULATION</b>	
Voltage Regulation Description	Automatic voltage regulation (AVR) maintains line power operation with input voltage as low as 89
Undervoltage Correction	Input voltages between 89 and 104 are boosted by 14%
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Switches	2 Switches control off/on power status and alarm-cancel/self-test operation
Alarm Cancel Operation	Power-fail alarm can be silenced using alarm-cancel switch; once silenced, alarm will re-sound to indicate low-battery status
Audible Alarm	Audible alarm indicates power-failure and low-battery conditions
LED Indicators	4 LEDs indicate line power, battery power, overload and battery low/replace status
<b>SURGE / NOISE SUPPRESSION</b>	
UPS AC Suppression Joule Rating	480
UPS AC Suppression Response Time	Instantaneous
UPS Dataline Suppression	1 line TEL/DSL (1 in / 1 out)
EMI / RFI AC Noise Suppression	Yes
<b>PHYSICAL</b>	
Installation Form Factors Supported with Included Accessories	Tower
Installation Form Factors Supported with Optional Accessories	Wallmount( <a href="#">UPSWM</a> - tower mounting kit)
Primary Form Factor	Tower
UPS Power Module Dimensions (hwd, in.)	8.5 x 5 x 6.5
UPS Power Module Dimensions (hwd, cm)	21.6 x 12.7 x 16.5
UPS Power Module Weight (lbs.)	14.4
UPS Power Module Weight (kg)	6.53
UPS Shipping Dimensions (hwd / in.)	12 x 8.2 x 9.2
UPS Shipping Dimensions (hwd / cm)	30.5 x 21 x 23.5
Shipping Weight (lbs.)	16
Shipping Weight (kg)	7.3
UPS Housing Material	PVC



Primary UPS Height (mm)	216
Primary UPS Width (mm)	127
Primary UPS Depth (mm)	165
Shipping Height (mm)	305
Shipping Width (mm)	208
Shipping Depth (mm)	234
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius
Relative Humidity	0 to 95%, non-condensing
AC Mode BTU / Hr. (Full Load)	68
Battery Mode BTU / Hr. (Full Load)	289
AC Mode Efficiency Rating (100% Load)	94%
<b>COMMUNICATIONS</b>	
Communications Interface	USB (HID enabled)
PowerAlert Software	For local monitoring via the UPS's built-in USB port, download PowerAlert Local software at <a href="http://www.tripplite.com/poweralert">http://www.tripplite.com/poweralert</a>
Communications Cable	USB interface cable included
WatchDog Compatibility	Supports Watchdog application, OS and hard-reboot restart options for remote applications
<b>LINE / BATTERY TRANSFER</b>	
Transfer Time	2-4 milliseconds
Low Voltage Transfer to Battery Power (Setpoint)	89
High Voltage Transfer to Battery Power (Setpoint)	139
<b>SPECIAL FEATURES</b>	
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported
High Availability UPS Features	Hot swappable batteries
<b>CERTIFICATIONS</b>	
UPS Certifications	Tested to UL1778 (USA); Tested to CSA (Canada); Tested to NOM (Mexico); Meets FCC Part 15 Category B (EMI)
<b>WARRANTY</b>	



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Product Warranty Period (U.S. & Canada)	3-year limited warranty
Product Warranty Period (Latin America)	3-year limited warranty
Product Warranty Period (International)	2-year limited warranty
Product Warranty Period (Mexico)	3-year limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$200,000 <a href="#">Ultimate Lifetime Insurance</a>

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>