

Protect It! 10-Outlet Surge Protector, 8 ft. Cord with Right-Angle Plug, 2395 Joules, Tel/DSL Protection, Black Housing

MODEL NUMBER: TLP1008TEL



Highlights

- 10 NEMA 5-15R outlets, including 4 for bulky transformers
- 2395-joule surge protection rating
- Filters out threatening EMI/RFI line noise
- 15A resettable circuit breaker prevents dangerous overloads
- 8 ft. AC power cord with right-angle NEMA 5-15P plug

Package Includes

- TLP1008TEL Protect It! 10-Outlet Surge Protector, Black Housing
- RJ11 telephone cable, 6 ft.
- Owner's manual

Description

Perfect for your home or office workstation, the TLP1008TEL Protect It!® 10-Outlet Surge Protector features a surge protection rating of 2395 joules to defend your sensitive electronic components against even the strongest surges and spikes.

Because residential power outlets have three wires—hot line (H), neutral (N) and ground (G)—the TLP1008TEL protects all three, covering the two protection modes: full normal mode (H-N) and common mode (N-G/H-G). It also filters out electromagnetic interference (EMI) and radio frequency interference (RFI) that can disrupt your electronics and inflict hardware damage or data loss.

Your devices plug into 10 NEMA 5-15R outlets, four of which are widely spaced to accept bulky transformers without blocking adjacent outlets. Sliding safety covers block accidental contact with unused outlets. RJ11 jacks allow connection of telephone/fax/modem equipment, which is also protected from surges.

An integrated 15A circuit breaker protects all outlets and shuts down connected equipment in case of overload. Diagnostic LEDs confirm your wall outlet is properly grounded and your connected equipment is protected.

The eight-foot AC power cord allows the TLP1008TEL to reach distant outlets, while its right-angle NEMA 5-15P plug allows furniture and equipment to be placed flush against the wall to save space in your workstation. Keyhole slots incorporated into the bottom panel provide convenient wall or desk mounting options for the black plastic housing.

Features

2395-Joule Surge Protection for Home or Office Electronics

- Protects your computer, printer, scanner, router, modem and other small home electronics against even the strongest surges and spikes
- Recommended for any desktop, network or home electronics application requiring AC line protection
- Full normal mode (H-N) and common mode (N-G/H-G) line surge suppression
- Filters out disruptive EMI/RFI line noise that can cause equipment damage or data loss
- Exceeds IEEE 587 Category A and B surge suppression specifications



10 Outlets Accept Wide Range of Electronic Devices

- 10 NEMA 5-15R AC outlets accept most computers and peripherals
- 4 widely spaced outlets accommodate bulky transformers without blocking other outlets
- Sliding safety covers block accidental contact with unused outlets

Telephone/DSL Protection

- RJ11 jacks (1 input/2 output) protect phone/fax/modem equipment from surges and spikes
- Built-in splitter protects 2 devices sharing one line
- 6 ft. RJ11 telephone cable included

Premium Safety Features

- On/off switch provides one-touch control over connected equipment
- Integrated 15A circuit breaker shuts down outlets in case of power overload
- Diagnostic LEDs confirm grounding and protection status at a glance
- Conforms to current UL 1449 3rd Edition safety standards

Fits Effortlessly Into Your Workstation

- 8 ft. AC power cord with right-angle NEMA 5-15P plug allows furniture and equipment to be placed flush against the wall
- Keyhole slots on bottom panel provide convenient wall or desk mounting options
- Black plastic housing designed for long life

Backed by Tripp Lite's Ultimate Lifetime Insurance

- \$150,000 Ultimate Lifetime Insurance covers any connected components damaged by power surge (U.S., Canada and Puerto Rico only)

Specifications

OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(10) 5-15R
Output (Watts)	1800W
Circuit Breaker (amps)	15A
Overload Protection	15A resettable circuit breaker
Transformer Accommodation	Supports 4 large transformer plug accessories without covering remaining outlets, accepts up to 8 transformers total
Outlet Safety Covers	Includes built-in sliding outlet safety covers
Outlet Orientation	Two rows of outlets, including 4 widely spaced for transformers
Right-Angle Outlets	No
INPUT	
Nominal Input Voltage(s) Supported	120V AC



Recommended Electrical Service	120V (110-125V)
Input Connection Type	NEMA 5-15P
Input Plug Features	Space-saving right angle input plug
Input Cord Length (ft.)	8
Input Cord Length (m)	2.44
Input Cord Gauge Type	14 gauge, SJT
Voltage Compatibility (VAC)	120
Maximum Surge Amps	120000
Right-Angle Plug	Yes
USER INTERFACE, ALERTS & CONTROLS	
Switches	Combination AC circuit breaker and two-position on/off power switch
Diagnostic LED Details	Built-in LEDs confirm suppressor "protection present" (green) and "grounded" (red) status
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	2395
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping Voltage (RMS)	150V
UL1449 Let Through Rating	400V - UL Verified
EMI / RFI Filtering	Up to 40dB
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	Yes
Telephone/DSL Protection Details	1 line
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
PHYSICAL	
Shipping Dimensions (hwd / in.)	14 x 7.75 x 2.25
Shipping Dimensions (hwd / cm)	35.56 x 19.69 x 5.72
Unit Dimensions (hwd / in.)	12 x 5.25 x 2
Unit Dimensions (hwd / cm)	30.48 x 13.33 x 5.08
Unit Weight (lbs.)	2
Unit Weight (kg)	0.91
Material of Construction	Plastic



Integrated Keyhole Mounting Tabs	Keyhole mounting tabs enable wall mounting
Housing Color	Black
Receptacle Color	Black
Color (AC Line Cord)	Black
Outlets Measurement (Center to Center)	Between Standard Outlets = 28.4mm; Between Standard and Transformer Outlets = 56.8mm
Keyhole Slot Mounting Measurement (Center to Center)	108mm
CERTIFICATIONS	
UL1449 3rd Edition (AC Suppression)	UL1449 3rd Edition
UL1363 (Power Tap)	UL1363
UL497A (Communications)	UL497A
FCC Part 68 (Communications)	FCC Part 68
cUL / CSA (Canada)	cUL
Industry Canada (Communications)	Industry Canada
Approvals	Exceeds IEEE 587 category A&B specifications
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$150,000 Ultimate Lifetime Insurance

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>