

Data Sheet

PR202xxVBDN

Page 1/3


P/N

PR202xxVBDN

xx=number of poles

2017/01/25

Illustration



see enlarged drawing at the end of the document

Product specification

- pin header, THR solderable
- centerline 2.54 mm, direction of connection vertical 0°
- color black
- dual rows



Data Sheet

PR202xxVBDN

Page 2/3

P/N

PR202xxVBDN

xx=number of poles

2017/01/25

Technical Data

General Data

Solder pin length	3.00 mm
min. number of poles	2
max. number of poles	40
protection category	IP 00

Approvals

Rated current	3 A
---------------	-----

Material

insulating material	PE-HT
Glow-Wire Flammability GWFI	-
Glow-Wire Flammability GWIT	-
contact pin material	CuZn
contact pin surface	Ni + Au Flash

Climatic properties

upper limit temperature	105 °C
lower limit temperature	-40 °C

General

solderability	Acc. to IPC/JEDEC J-STD-020D-MSL 1
Tolerance	ISO 2768 -mH

Data Sheet

PR202xxVBDN

Page 3/3

P/N


PR202xxVBDN

xx=number of poles

2017/01/25

Illustration

Drawing



$$L = (\text{pole size} - 1) \times \text{centerline} + 2.54 [0.1]$$

