

700W PowerVerter Ultra-Compact Inverter with 3 Outlets

MODEL NUMBER: PV700HF



Highlights

- 700W continuous output; 1400W peak output (instantaneous)
- Converts 12V DC (battery) power into 110-120V AC (household) power; 3 AC outlets
- Installs in minutes (integrated mounting feet included)
- Provides a quiet alternative to generator noise and fumes
- Includes "battery saver" low voltage alarm/shutdown

Package Includes

- PV700HF Ultra-Compact DC-to-AC Inverter
- Instruction manual with warranty information

Description

Utilize your vehicle's battery to efficiently power appliances, small electronics and office equipment on the road. Continuously supplies up to 700W of 120V AC power to 3 AC outlets from any 12V battery. Featuring an ultra-compact, lightweight design with metal housing, the PV700HF is the most rugged inverter available.

NOTE: To protect against high current draw that may occur during inverter failure, a fuse link rated at 125a should be positioned no more than 18" from the PV700HF's battery in the positive line.

Features

- Provides 120V AC power for a variety of mobile applications
- 700W continuous output power; 1400W peak output power (instantaneous)
- 3 AC outlets
- Ultra-compact extruded aluminum housing stands up to the toughest environments
- Cooling fan lengthens inverter service life & maintains cool operation
- Integrated mounting feet assure safe fixed installation
- Low battery alarm/shutdown detects low battery voltage and shuts down inverter
- Overload alarm/shutdown detects wattage overload on inverter outlets and shuts down inverter as a protective measure
- DC input terminals provide a solid connection to battery with user-supplied cables
- Lighted on/off switch shows inverter operations in cramped or dark environments
- Grooved surface for more efficient cooling

Specifications

OUTPUT



Nominal Output Voltage(s) Supported	120V
Frequency Compatibility	60 Hz
Output Receptacles	(3) 5-15R
Output (Watts)	700
Continuous Output Capacity (Watts)	700
Peak Output Capacity (Watts)	1400
Output Voltage Regulation	Maintains PWM sine wave output voltage of 115 V AC (+/- 8 V AC)
Output Frequency Regulation	60 Hz (+/- 3 Hz)
INPUT	
Recommended Electrical Service	Requires 12V DC input source capable of delivering 80A for the required duration (when used at full capacity). For automotive applications, hardwire installation with 125A battery system fusing is recommended
Maximum Input Amps / Watts	Full continuous load - 80A at 12V DC, No load - 0.95A at 12V DC, Shutdown - 150 micro amps
Input Connection Type	Set of 2 DC bolt-down wiring terminals
Input Cord Length Details	User supplies cabling. Minimum gauges for full load operation: 6 gauge or larger (see instruction manual)
Voltage Compatibility (VDC)	12
BATTERY	
DC System Voltage (VDC)	12
USER INTERFACE, ALERTS & CONTROLS	
Switches	Lighted on/off power switch
Audible Alarm	Dual-function alarm indicates overload conditions or low DC input voltage of 10.5V or less
PHYSICAL	
Shipping Dimensions (hwd / in.)	3.75 x 6.25 x 10.3
Shipping Dimensions (hwd / cm)	9.53 x 15.88 x 26.16
Shipping Weight (lbs.)	3.5
Shipping Weight (kg)	1.6
Unit Dimensions (hwd / in.)	2.75 x 8.17 x 5
Unit Dimensions (hwd / cm)	7 x 20.75 x 12.6
Unit Weight (lbs.)	2.8
Unit Weight (kg)	1.26
Cooling Method	Fan
Material of Construction	Aluminum/sheet metal



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

ENVIRONMENTAL	
Relative Humidity	0-95% non-condensing
SPECIAL FEATURES	
Remote Control Capability	No
TVSS Grounding	Main grounding screw for connecting inverter to earth, vehicle, or boat grounding systems
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>