



Datenblatt - Fiche technique - Data sheet

11.04.5595



ROLINE Monitorkabel DVI, ST-ST, (24+1) dual link, 10m

ROLINE Câble DVI pour écran, M-M, (24+1) dual link, 10,0m

ROLINE Monitor Cable, DVI (24+1), Dual Link, M/M, 10 m




ROHS-COMPLIANT

LTR	REV.	DESCRIPTION	DATE
△*2	B	ECR # 071205-4 ADD LENGTH	12/05/07'
△*2	C	ECR # 080509-7 EDIT PACKING,ADD BAR CODE	05/09/08'

L+T

DVI_D M

PLASTIC:BLACK



PIN1
PIN9
PIN17
PIN24
PIN8
PIN16

KEY

P2

PIN17
PIN8
PIN16
PIN24

KEY

P1

TDB-0075

REMARK:

1. CABLE:UL -20276 [28AWG(7/0.127)*1P+DRAIN WIRE+AL/MY+MYLAR]*7C+28AWG(7/0.127)*1P+28AWG(7/0.127)*3C+AL/MYLAR+BRAID SHIELDS(85%)*T.C PVC JACKET, OD: 8.6±0.15mm, COLOR:BLACK(INK-K01).
2. CONNECTOR: P1&P2:DVI_D 25P: 24P+KEY MALE, GOLD FLASH CONTACT, NICKEL PLATED SHELL.
3. SHIELD: P1&P2 COPPER FOIL 360° SOLDERED TO CONNECTOR SHELL & CABLE SHIELDING
4. HOOD: P1&P2:MOLDED TYPE, PVC 45P, COLOR:BLACK(INK-K01)
5. FERRITE CORE: (28.5*17.5*9.5) x 2
6. TEST REQUEST:
 - (1) 100% SHORT OPEN & MIS WIRE TEST.
 - (2) CONTACT RESISTANCE 3 OHMS MAX.
 - (3) INSULATION RESISTANCE 10M OHMS MIN.
 - (4) HI-POT VOLTAGE: 300V DC.
7. PACKING: EACH PC / POLY BAG + P/N LABEL

WIRE CONNECTION

P1	WIRE COLOR	P2
1		1
2		2
3		3
4		4
5		5
6		6
7		7
9		9
10		10
11		11
12		12
13		13
14		14
15		15
16		16
17		17
18		18
19		19
19		19
20		20
21		21
22		22
23		23
24		24
SHELL	BRAID SHIELDS	SHELL



200-0839-2	11.99.5598	15000	150	4	7611990175253
200-0839-1	11.04.5595	10000	100	10	7611990160938
DWG NO.	P / N	L (m/m)	T (m/m)	PCS/CTN	BAR CODE NO.

Tolerance	Inch	M/M
X	.015	.30
XX	.010	.10
XXX	.005	.05

Draw PANNIE 05/09/08'

Check	App'd	Customer	T-RAG
Engr	Scale NONE	Units	m/m
	Dwg No. 200-0839	REV: C	Sheet 1/1

Rotronic Co., Ltd.

Title
DVI_D - DVI_D DUAL LINK CABLE

Customer P/N: