


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
FT	0	P	LTR	DESCRIPTION	DATE	DWN	APVD
			P2	REVISED PER ECO-05-11481	2/22/06	SS	SH

- PARTS PACKAGED UNASSEMBLED.
- △ CABLE CLAMPING AREA ADJUSTABLE FROM .100 TO .410 SQ IN BY REVERSING CLAMPING INSERTS. (2 INSERTS SUPPLIED, -1 AND -2 ONLY)
- △ CABLE CLAMPING AREA ADJUSTABLE FROM .100 TO .410 SQ IN BY CHANGING CLAMPING INSERTS. (4 INSERTS SUPPLIED, -3 ONLY)
- .703 MAXIMUM CABLE OUTSIDE DIAMETER.
- △ BULK PACKAGED KITS TO BE ORDERED IN MULTIPLES OF 100 ONLY.
- △ SCREW FINISH ZINC WITH NON-HEXAVALENT CHROMATE.



△6	INDIVIDUAL	1-206138-1
△6	△5 BULK	1-206138-0
△6	SMALL PACK	206138-9
△6	INDIVIDUAL	206138-8
	INDIVIDUAL	206138-7
	SMALL PACK	206138-6
	△5 BULK	206138-3
	△5 BULK	206138-2
	INDIVIDUAL	206138-1
	PACKAGING	PART NUMBER

OBSOLETE

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN A GRAFF 4/23/91	Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: INCHES		CHK W.G.LENKER 7-22-92	NAME CABLE CLAMP KIT, STANDARD, SHELL SIZE 23, CPC	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD -	PRODUCT SPEC 108-10024	
0 PLC ± -		PRODUCT SPEC	APPLICATION SPEC	
1 PLC ± -		APVD	-	
2 PLC ± -		WEIGHT	-	
3 PLC ± -		SIZE CAGE CODE DRAWING NO RESTRICTED TO		
4 PLC ± -		A3 00779 C=206138		
ANGLES ± -		CUSTOMER DRAWING		
MATERIAL THERMOPLASTIC,		SCALE NTS SHEET 1 OF 1 REV P2		