





H8550VB ---T8550VB ---



H8550XB ---T8550XB ---



H8550RB Semi-rotary A splash proofing option







H8580AB ---


BODY

Panel cut-outs Flange

Cut-outs must be punched in the direction of insertion


В

Standard body with terminal barrier



BC

Body without terminal barrier



Dimensions for snap-in fixing

Panel thickness Dim X 0.75-1.25 19.1/19.2 1.25-2.00 19.3/19.4 2.00-3.00 19.7/19.8

OPTIONS

Finish

Matt finish only

Colour

Call factory for custom colours A full range is available for large orders

Legend printing

Select from the examples or call the factory for custom legends

Lamp voltage


Call factory for details of other available voltages

Protective cover L167

(designed to IP65) Snaps on to bodies with V or X style rockers and A style lens but reduces panel thickness by 0.8mm



DIMENSIONS (mm)



Terminal spacing between 1a & 3b - 6.0, between 2a & 4b - 9.5


Examples of printing



11



T8660VB ---



24.0

19.1/19.2

19.3/19.4

19.7/19.8

Double Pole dimensions for snap-in fixing Panel thickness Dimension X

0.75-1.24

1.25-1.99

2.00-3.00


OPTIONS Finish Matt finish only Colour Call factory for custom colours A full range is available for large orders Legend printing Select from the examples or call the factory for custom legends Lamp voltage Call factory for details of other available voltages Blanking plate A8634FB Dummy unit to fill unused panel holes Single pole size only **Protective covers** L167 for SP L180 for DP (designed to IP65) Snap on to bodies with V rocker or F lens but reduce panel thickness by 0.8mm. Not for use with momentary types

Single Pole options


Most switches shown can have single

pole switching in double pole bodies

T8650VB ---



T8653VB ---



13

8620 & 8670 Rocker Switches - 3 Positions 10A 250Vac



In house test 10A 28Vdc

μ contact gap Technical data on pages 4 & 5




CL141

CL142



UL 90°C, file E45221, CSA file LR10990













W T8353EB ---












H8350HB --Example of actuator

BODY

Panel cut-out Flange
Cut-outs must be punched in the direction of insertion

- **B** Standard body
- **D** As B body but with PCB support peg
- **E** Softline style body with radiused bezel
- **F** As E body but with PCB support peg



Dimensions for snap-in fixing

Dimension X
19.1/19.2
19.3/19.4
19.7/19.8

OPTIONS

Finish

Matt finish standard except on J and D actuators which are gloss

Coloui

Call factory for custom colours A full range is available for large orders

Legend printing

Select from the examples or call factory for custom legends

Special buttons


Some of the many options are shown Call the factory for the full range


L167 Protective cover (designed to IP65)



Snaps on to switch bodies fitted with "A" or "J" style actuators but reduces panel thickness by 0.8mm

DIMENSIONS (mm)





Spacing between centre of terminals 1 & 3 or 2 & 4 is 10.0mm

Examples of printing

