


F462, Film, Metallized Polypropylene, Commercial Grade, 0.01 uF, 5%, 1,250 V, 85C, Lead Spacing = 10mm



Dimensions

L	13mm MAX
H	11mm MAX
T	5mm MAX
S	10mm +/-0.4mm
LL	17mm -1mm
F	0.6mm +/-0.05mm
G	0.5mm NOM

Packaging Specifications

Packaging:	Bulk, Bag
Packaging Quantity:	2000

General Information

Supplier:	KEMET
Series:	F462
Dielectric:	Metallized Polypropylene
Style:	Radial
Features:	MKP, Pulse
RoHS:	Yes
Lead:	Wire Leads
Miscellaneous:	The Rated Voltage Decreases 2%/C Between +85C And +105C (1.25%/C For AC). ClimCat: 55/105/56

Specifications

Capacitance:	0.01 uF
Capacitance Tolerance:	5%
Voltage DC:	1250 VDC, 750 VDC (105C)
Voltage AC:	400 VAC
Temperature Range:	-55/+105C
Rated Temperature:	85C
Dissipation Factor:	0.04% 1kHz, 0.06% 10kHz, 0.25% 100kHz
Insulation Resistance:	100 GOhms
Max dVdt:	2,200 V
Inductance:	6 nH