



### Heat Shrinkable Tubing 2:1 flexible and coloured


#### HFT-A - self extinguishing

This high performance thin wall tubing is used extensively for electrical and mechanical protection. It is also well proven for sleeve marking to identify wiring circuits. It shrinks uniformly to form a permanent insulation covering.

The transparent version is used for bundling and cable protection where visual inspection is required. It is often used as a see through protective sleeve over cable markers.

#### Features and Benefits

- Flexible heat shrink tubing
- Fast shrinking, easy handling, good mechanical strength
- Easy to print on
- Wide range of colours
- Internal diameters up to 4 inches (101.6 mm)
- UL-224 ,CSA listed and VG approved



HFT-A conforms to major standards used in all Defence industries.



Standard sizes available in colours black, red, blue, yellow, white and green-yellow.

<b>MATERIAL</b>	Polyolefin, cross-linked (PO-X)
<b>Shrink Ratio</b>	2:1
<b>Operating Temperature</b>	-55 °C to +135 °C
<b>Minimum Shrink Temperature</b>	+100 °C
<b>Longitudinal change after shrinkage</b>	+5 %/-10 %
<b>Dielectric Strength</b>	20 kV/mm according to IEC 60684 P2
<b>Flammability</b>	Self extinguishing
<b>Specifications</b>	ASN-E0126, CSA, DEF STAN 59-97/3, LEA, MIL-DTL-23053/5C, NF F 00-608, NSA937211, PAN6493, SAE - AMS - DTL-23053 / 5C, UL224 125 °C 600V, VG 95343




TYPE	Supplied Ø D min.	Size (imperial)	Recov. Ø d max.	Wall (WT)	Reel Length	Colour	Designation as per VG-Norm	Article-No.
<b>HFT-A-1.2/0.6</b>	1.2	3/64 "	0.6	0.40	400 m	Black (BK)	VG 95343 T05 A 001A	305-01200
	1.2	3/64 "	0.6	0.40	400 m	Blue (BU)	VG 95343 T05 A 001 G	305-01206
	1.2	3/64 "	0.6	0.40	400 m	Red (RD)	VG 95343 T05 A 001 C	305-01202
	1.2	3/64 "	0.6	0.40	400 m	White (WH)	VG 95343 T05 A 001 L	305-01209
	1.2	3/64 "	0.6	0.40	400 m	Yellow (YE)	VG 95343 T05 A 001 E	305-01204
<b>HFT-A-1.6/0.8</b>	1.6	1/16 "	0.8	0.40	400 m	Black (BK)	VG 95343 T05 A 002 A	305-01600
	1.6	1/16 "	0.8	0.40	400 m	Blue (BU)	VG 95343 T05 A 002 G	305-01606
	1.6	1/16 "	0.8	0.40	400 m	Red (RD)	VG 95343 T05 A 002 C	305-01602
	1.6	1/16 "	0.8	0.40	400 m	White (WH)	VG 95343 T05 A 002 L	305-01609
	1.6	1/16 "	0.8	0.40	400 m	Yellow (YE)	VG 95343 T05 A 002 E	305-01604

All dimensions in mm. Subject to technical changes.  
Minimum Order Quantity (MOQ) may differ from package content.



For product specific approvals and specifications please refer to the Appendix.



## Heat Shrinkable Tubing 2:1 flexible and coloured

## HFT-A - self extinguishing




Heat Shrinkable Tubing 2:1

TYPE	Supplied Ø D min.	Size (imperial)	Recov. Ø d max.	Wall (WT)	Reel Length	Colour	Designation as per VG-Norm	Article-No.
HFT-A-2.4/1.2	2.4	3/32 "	1.2	0.50	100 m	Blue (BU)	VG 95343 T05 A 003 G	305-02406
	2.4	3/32 "	1.2	0.50	100 m	Red (RD)	VG 95343 T05 A 003 C	305-02402
	2.4	3/32 "	1.2	0.50	100 m	White (WH)	VG 95343 T05 A 003 L	305-02409
	2.4	3/32 "	1.2	0.50	100 m	Yellow (YE)	VG 95343 T05 A 003 E	305-02404
	2.4	3/32 "	1.2	0.50	400 m	Black (BK)	VG 95343 T05 A 003 A	305-02400
HFT-A-3.2/1.6	3.2	1/8 "	1.6	0.50	100 m	Blue (BU)	VG 95343 T05 A 004 G	305-03206
	3.2	1/8 "	1.6	0.50	100 m	Green-Yellow (GNYE)	VG 95343 T05 A 004 N	305-03245
	3.2	1/8 "	1.6	0.50	100 m	Red (RD)	VG 95343 T05 A 004 C	305-03202
	3.2	1/8 "	1.6	0.50	100 m	White (WH)	VG 95343 T05 A 004 L	305-03209
	3.2	1/8 "	1.6	0.50	100 m	Yellow (YE)	VG 95343 T05 A 004 E	305-03204
	3.2	1/8 "	1.6	0.50	400 m	Black (BK)	VG 95343 T05 A 004 A	305-03200
HFT-A-4.8/2.4	4.8	3/16 "	2.4	0.50	75 m	Blue (BU)	VG 95343 T05 A 005 G	305-04806
	4.8	3/16 "	2.4	0.50	75 m	Green-Yellow (GNYE)	VG 95343 T05 A 005 N	305-04845
	4.8	3/16 "	2.4	0.50	75 m	Red (RD)	VG 95343 T05 A 005 C	305-04802
	4.8	3/16 "	2.4	0.50	75 m	White (WH)	VG 95343 T05 A 005 L	305-04809
	4.8	3/16 "	2.4	0.50	75 m	Yellow (YE)	VG 95343 T05 A 005 E	305-04804
	4.8	3/16 "	2.4	0.50	300 m	Black (BK)	VG 95343 T05 A 005 A	305-04800
HFT-A-6.4/3.2	6.4	1/4 "	3.2	0.60	75 m	Blue (BU)	VG 95343 T05 A 006 G	305-06406
	6.4	1/4 "	3.2	0.60	75 m	Green-Yellow (GNYE)	VG 95343 T05 A 006 N	305-06445
	6.4	1/4 "	3.2	0.60	75 m	Red (RD)	VG 95343 T05 A 006 C	305-06402
	6.4	1/4 "	3.2	0.60	75 m	White (WH)	VG 95343 T05 A 006 L	305-06409
	6.4	1/4 "	3.2	0.60	75 m	Yellow (YE)	VG 95343 T05 A 006 E	305-06404
	6.4	1/4 "	3.2	0.60	300 m	Black (BK)	VG 95343 T05 A 006 A	305-06400
HFT-A-9.5/4.8	9.5	3/8 "	4.8	0.60	50 m	Blue (BU)	VG 95343 T05 A007 G	305-09506
	9.5	3/8 "	4.8	0.60	50 m	Green-Yellow (GNYE)	VG 95343 T05 A007 N	305-09545
	9.5	3/8 "	4.8	0.60	50 m	Red (RD)	VG 95343 T05 A007 C	305-09502
	9.5	3/8 "	4.8	0.60	50 m	White (WH)	VG 95343 T05 A007 L	305-09509
	9.5	3/8 "	4.8	0.60	50 m	Yellow (YE)	VG 95343 T05 A007 E	305-09504
	9.5	3/8 "	4.8	0.60	150 m	Black (BK)	VG 95343 T05 A007 A	305-09500
HFT-A-12.7/6.4	12.7	1/2 "	6.4	0.60	50 m	Blue (BU)	VG 95343 T05 A 008 G	305-12706
	12.7	1/2 "	6.4	0.60	50 m	Green-Yellow (GNYE)	VG 95343 T05 A 008 N	305-12745
	12.7	1/2 "	6.4	0.60	50 m	Red (RD)	VG 95343 T05 A 008 C	305-12702
	12.7	1/2 "	6.4	0.60	50 m	White (WH)	VG 95343 T05 A 008 L	305-12709
	12.7	1/2 "	6.4	0.60	50 m	Yellow (YE)	VG 95343 T05 A 008 E	305-12704
	12.7	1/2 "	6.4	0.60	100 m	Black (BK)	VG 95343 T05 A 008 A	305-12700

All dimensions in mm. Subject to technical changes.  
Minimum Order Quantity (MOQ) may differ from package content.



For product specific approvals and specifications  
please refer to the Appendix.



### Heat Shrinkable Tubing 2:1 flexible and coloured

#### HFT-A - self extinguishing



TYPE	Supplied Ø D min.	Size (imperial)	Recov. Ø d max.	Wall (WT)	Reel Length	Colour	Designation as per VG-Norm	Article-No.
HFT-A-19.0/9.5	19.0	3/4 "	9.5	0.80	25 m	Blue (BU)	VG 95343 T05 A 009 G	305-19006
	19.0	3/4 "	9.5	0.80	25 m	Green-Yellow (GNYE)	VG 95343 T05 A 009 N	305-19045
	19.0	3/4 "	9.5	0.80	25 m	Red (RD)	VG 95343 T05 A 009 C	305-19002
	19.0	3/4 "	9.5	0.80	25 m	White (WH)	VG 95343 T05 A 009 L	305-19009
	19.0	3/4 "	9.5	0.80	25 m	Yellow (YE)	VG 95343 T05 A 009 E	305-19004
	19.0	3/4 "	9.5	0.80	50 m	Black (BK)	VG 95343 T05 A 009 A	305-19000
HFT-A-25.4/12.7	25.4	1 "	12.7	0.90	25 m	Blue (BU)	VG 95343 T05 A 010 G	305-25406
	25.4	1 "	12.7	0.90	25 m	Green-Yellow (GNYE)	VG 95343 T05 A 010 N	305-25445
	25.4	1 "	12.7	0.90	25 m	Red (RD)	VG 95343 T05 A 010 C	305-25402
	25.4	1 "	12.7	0.90	25 m	White (WH)	VG 95343 T05 A 010 L	305-25409
	25.4	1 "	12.7	0.90	25 m	Yellow (YE)	VG 95343 T05 A 010 E	305-25404
	25.4	1 "	12.7	0.90	50 m	Black (BK)	VG 95343 T05 A 010 A	305-25400
HFT-A-38.0/19.0	38.0	1-1/2 "	19.0	1.00	50 m	Black (BK)	VG 95343 T05 A 011 A	305-38100
	38.0	1-1/2 "	19.0	1.00	50 m	Blue (BU)	VG 95343 T05 A 011 G	305-38106
	38.0	1-1/2 "	19.0	1.00	50 m	Green-Yellow (GNYE)	VG 95343 T05 A 011 N	305-38145
	38.0	1-1/2 "	19.0	1.00	50 m	Red (RD)	VG 95343 T05 A 011 C	305-38102
	38.0	1-1/2 "	19.0	1.00	50 m	White (WH)	VG 95343 T05 A 011 L	305-38109
	38.0	1-1/2 "	19.0	1.00	50 m	Yellow (YE)	VG 95343 T05 A 011 E	305-38104
HFT-A-50.8/25.4	51.0	2 "	25.4	1.10	35 m	Black (BK)	VG 95343 T05 A 012 A	305-50800
	51.0	2 "	25.4	1.10	35 m	Blue (BU)	VG 95343 T05 A 012 G	305-50806
	51.0	2 "	25.4	1.10	35 m	Red (RD)	VG 95343 T05 A 012 C	305-50802
	51.0	2 "	25.4	1.10	35 m	White (WH)	VG 95343 T05 A 012 L	305-50809
	51.0	2 "	25.4	1.10	35 m	Yellow (YE)	VG 95343 T05 A 012 E	305-50804
HFT-A-76.0/38.0	76.0	3 "	38.0	1.30	25 m	Black (BK)	VG 95343 T05 A 013 A	305-76200
	76.0	3 "	38.0	1.30	25 m	Blue (BU)	VG 95343 T05 A 013 G	305-76206
	76.0	3 "	38.0	1.30	25 m	Red (RD)	VG 95343 T05 A 013 C	305-76202
	76.0	3 "	38.0	1.30	25 m	White (WH)	VG 95343 T05 A 013 L	305-76209
	76.0	3 "	38.0	1.30	25 m	Yellow (YE)	VG 95343 T05 A 013 E	305-76204
HFT-A-101.6/50.8	101.6	4 "	50.8	1.40	25 m	Black (BK)	VG 95343 T05 A 014 A	305-91600
	101.6	4 "	50.8	1.40	25 m	Blue (BU)	VG 95343 T05 A 014 G	305-91606
	101.6	4 "	50.8	1.40	25 m	Red (RD)	VG 95343 T05 A 014 C	305-91602
	101.6	4 "	50.8	1.40	25 m	White (WH)	VG 95343 T05 A 014 L	305-91609
	101.6	4 "	50.8	1.40	25 m	Yellow (YE)	VG 95343 T05 A 014 E	305-91604

All dimensions in mm. Subject to technical changes.  
Minimum Order Quantity (MOQ) may differ from package content.



For product specific approvals and specifications please refer to the Appendix.