

PULSE RESISTORS, SURFACE MOUNT


PRM SERIES



- ☐ High voltage/ high surge capability
- ☐ Cost effective surface mount package
- ☐ Available on RCD's exclusive SWIFT Toprogram

OPTIONS

- ☐ Option ER: Group A Screening per MIL-R-39008 RCR
- □ Option B: Increased power
- □ Option X: Non-inductive








Pulse tolerant surface mount resistors!

Series PRM withstand high energy pulses, and are superior to conventional film & wirewound types. The heavy duty construction features a ceramic core, enabling improved thermal transfer and long term stability. Elements are protected by flame-retardant molding for excellent environmental performance. Alpha-numeric marking is standard. PRM resistors are cost effective in a wide variety of pulse applications including telecom line feed resistors, snubber circuits, inrush currents, capacitor charge/discharge circuits, lightning surges, etc.




SPECIFICATIONS

RCD Type	Wattage Rating			Max. Peak	Resistance	DIMENSIONS Inch [mm]							
	Std	Opt B	Voltage ^{1,3,4}	Pulse Voltage ^{2,4}	Range	Α	В	С	D	E	F	G	Н
PRM1/8	.125W	.5W	150V	2KV	0.1Ω - 2K	.200 ± .02 [5.1 ± .5]		.120 ± .01 [3.18± .25]	.025 Min. [.63]	.045 ± .015 [1.14 ± .38]	.080 [2.0]	.100 [2.5]	.08 [2.0]
PRM1/4	.25W	1W	250V	3.5KV	0.1Ω -10K	.258 ± .02 [6.55 ± .5]	.110± .015 [2.79± .38]	.150± .015 [3.81± .38]	.032 Min. [0.8]	.060 ± .015 [1.5 ± .38]	.100 [2.5]	.125 [3.2]	.120
PRM1/2	.5W	2W	350V	5KV	0.1Ω -24K	.472 ± .024 [12 ± .6]	.208 ± .02 [5.3 ± .5]	.228± .016 [5.8± .4]	.050 Min. [1.27]	.070 ± .02 [1.78 ± .5]	.160 [4.0]	.180 [4.57]	.200 [5.0
PRM1	1W	4W	500V	10KV	0.1Ω -100K	.811 ± .020 [20.6 ± .5]	.275± .020 [6.99± .5]	.273± .020 [6.93± .5]	.063 Min. [1.6]	.102 ± .028 [2.6 ± .7]	.200 [5.0]	.200 [5.0]	.600 [15.2

1Rated continuous voltage = $\sqrt{(PxR)}$, nte value listed. 2Pulse voltage capability is dependent on res.value, waveform, & repetition rate. 3 Expanded range available 4Miltiply by 0.7 on Opt.X parts

SURGE CAPABILITY



TYPICAL PERFORMANCE CHARACTERISTICS

Wattage Derating	1.25%/°C >70°C (Opt. B to be derated 0.8%/°C >25°C)				
Max.Induc*: Opt. X≤50Ω Max.Induc*: Opt. X>50Ω	0.2uH PRM1/8-1/2, .3uH PRM1 0.37uH PRM1/8-1/2, .6uH PRM1				
Short-time Overload	±0.5%				
Temperature Cycling	±0.5%				
TCR (20ppm avail.)	±120ppm/°C (<0.2Ω=200ppm)				
Moisture Resistance	±1%				
Shock and Vibration	±0.2%				
Effect of Soldering	±0.2%				
Voltage Coefficient	±0.005%/V				
Load Life	±0.5% Std, ±1% Opt.B				
Operating Temp Range	-55 to +150°C, +275°C avail.				
Dielectric Strength	500V (1KV avail.)				

^{*} specify Opt.75 for induc levels 50% that of Opt.X, or Opt.76 for 33% that of Opt.X

APPLICATION NOTE

Use chart above to select model to meet desired surge level. Pulse not to exceed peak V & j ratings (derate 30% for Opt.X), and average power during repetitive pulses nte rated W. 30% safety factor is recommended for infrequent pulses, 50% typ. for repetitive pulses (request Note R42 for derating factors attributable to pulse width, rep. rate, temp., altitude, humidity). Verify by evaluating under worst-case conditions. Depending on specifics, PR series can often satisfy the surge requirements of UL-217, -268, -294, -497, -508, -913, -943, -991, -1459, -1971, ANSI/IEEE C62.41, CCITT (Rec. K17), Bellcore TR-NWT-001089 & TR-TSY-000057, CSA C22.2-225, IEC 664, IEC 801.5, IEEE587, Can. Doc. CS-03, FCC Part 68., etc. Consult factory for assistance.

