



'T' PIECE with Inspection Cover:



CONDUIT SIZE (mm)	ORDERING CODE	DIMENSIONS (mm)			
		NUT DIAMETER	CENTRE HEIGHT	NOMINAL LENGTH	BODY DEPTH
3 x 10	YYNB0101	22.8	38.7	68.5	26.8
3 x 12	YYNB0202	22.8	38.7	68.5	26.8
3 x 16	YYNB0303	26.0	37.6	69.5	30.7
3 x 20	YYNB0404	31.0	42.7	80.0	35.0
3 x 25	YYNB0505	39.0	51.5	95.0	43.0
3 x 32	YYNB0606	46.1	61.0	109.0	51.0

MATERIAL: NYLON


MALREDUCING CAP NUT & SEAL:



CONDUIT SIZE (mm)	ORDERING CODE	DIMENSIONS (mm)	
		NUT DIAMETER	NOMINAL BORE
12 x 10	YRNB 0201	22.8	10.1
16 x 12	YRNB 0302	26.0	13.0
20 x 12	YRNB 0402	31.0	13.0
20 x 16	YRNB 0403	31.0	16.1
25 x 12	YRNB 0502	39.0	13.0
25 x 16	YRNB 0503	39.0	16.1
25 x 20	YRNB 0504	39.0	21.0
32 x 20	YRNB 0604	46.1	21.0

MATERIAL: NYLON – NEOPRENE

COMBINED CONDUIT CLIP:



CONDUIT SIZE (mm)	ORDERING CODE	DIMENSIONS (mm)				
		CONDUIT HOLE	CENTRE HEIGHT	BASE WIDTH	BASE DEPTH	FIXING HOLE
10	YCC*01	10.0	13.0	22.6	11.6	4.2
12	YCC*02	13.0	13.0	22.6	11.6	4.2
16	YCC*03	15.8	15.0	26.7	13.7	5.1
20	YCC*04	21.2	19.5	33.8	17.5	6.1
25	YCC*05	28.5	23.0	43.8	20.7	6.1
32	YCC*06	34.7	26.0	52.8	23.2	6.2
40	YCC*07	42.5	33.0	64.5	27.0	6.2
50	YCC*08	54.5	39.0	81.0	32.1	6.2

MATERIAL: NYLON

* ADD 'B' FOR BLACK

PROPERTIES:

IP RATING WITH RECOMMENDED CONDUITS

OPERATING TEMPERATURE

APPROVALS

IP 66 (NO INGRESS OF TALCUM POWDER UNDER VACUUM AND NO INGRESS OF WATER WITH NOZZLE SPRAY FROM 3m).

STATIC - 40 TO +120° C.

DYNAMIC -5 TO + 120° C.

UR COMPONENT RECOGNISED.

The Company's policy is one of continuous improvement and reserves the right to change specifications at any time without prior notice.