

SAFETY DATA SHEET

Complies with OSHA Hazard Communication Standard 29 CFR 1910.1200

Product Name: GLASS TREATMENT COMPOUND

SECTION 1. PRODUCT AND COMPANY IDENTIFICATION

Product Type: Glass Cleaner
Product Name: **GLASS TREATMENT COMPOUND**
Part Number(s): **10-1756**

Emergency Contact: Chemtrec
Phone: (800) 424-9300

SECTION 2. HAZARDOUS INGREDIENTS

Physical hazards	Flammable liquids	Category 2
Health hazards	Not classified.	
Environmental hazards	Not classified.	
OSHA defined hazards	Not classified.	

Label elements



Signal word	Danger
Hazard statement	Highly flammable liquid and vapor.
Precautionary statement	
Prevention	Keep away from heat/sparks/open flames/hot surfaces. - No smoking. Keep container tightly closed. Ground/bond container and receiving equipment. Use explosion-proof electrical/ventilating/lighting equipment. Use only non-sparking tools. Take precautionary measures against static discharge. Wear protective gloves/eye protection/face protection.
Response	If on skin (or hair): Take off immediately all contaminated clothing. Rinse skin with water/shower. In case of fire: Use appropriate media to extinguish.
Storage	Store in a well-ventilated place. Keep cool.
Disposal	Dispose of contents/container in accordance with local/regional/national/international regulations.
Hazard(s) not otherwise classified (HNOC)	Static accumulating flammable liquid can become electrostatically charged even in bonded and grounded equipment. Sparks may ignite liquid and vapor. May cause flash fire or explosion.
Supplemental information	None.



1801 Morgan Street
Rockford, IL 61102
Phone: (815) 968-9661
Fax: (815) 968-9731
www.gcelectronics.com

SDS Number: 203
Revision Date: 08/18/2015
Supersedes Date: 03/27/2014

SAFETY DATA SHEET

Complies with OSHA Hazard Communication Standard 29 CFR 1910.1200

Product Name: GLASS TREATMENT COMPOUND

SECTION 3. COMPOSITION/ INFORMATION ON INGREDIENTS

Mixtures

Chemical name	Common name and synonyms	CAS number	%
2-PROPANOL		67-63-0	4
Other components below reportable levels			96

*Designates that a specific chemical identity and/or percentage of composition has been withheld as a trade secret.

SECTION 4. FIRST-AID MEASURES

Inhalation	Move to fresh air. Call a physician if symptoms develop or persist.
Skin contact	Take off immediately all contaminated clothing. Rinse skin with water/shower. Get medical attention if irritation develops and persists.
Eye contact	Immediately flush eyes with plenty of water for at least 15 minutes. Remove contact lenses, if present and easy to do. Get medical attention if irritation develops and persists.
Ingestion	Rinse mouth. Get medical attention if symptoms occur.
Most important symptoms/effects, acute and delayed	Direct contact with eyes may cause temporary irritation.
Indication of immediate medical attention and special treatment needed	Provide general supportive measures and treat symptomatically. Thermal burns: Flush with water immediately. While flushing, remove clothes which do not adhere to affected area. Call an ambulance. Continue flushing during transport to hospital.
General information	Take off all contaminated clothing immediately. Ensure that medical personnel are aware of the material(s) involved, and take precautions to protect themselves. Wash contaminated clothing before reuse.

SECTION 5. FIRE-FIGHTING MEASURES

Suitable extinguishing media	Water fog. Foam. Carbon dioxide (CO2). Dry chemical powder, carbon dioxide, sand or earth may be used for small fires only.
Unsuitable extinguishing media	Do not use water jet as an extinguisher, as this will spread the fire.
Specific hazards arising from the chemical	Vapors may form explosive mixtures with air. Vapors may travel considerable distance to a source of ignition and flash back. This product is a poor conductor of electricity and can become electrostatically charged. If sufficient charge is accumulated, ignition of flammable mixtures can occur. To reduce potential for static discharge, use proper bonding and grounding procedures. This liquid may accumulate static electricity when filling properly grounded containers. Static electricity accumulation may be significantly increased by the presence of small quantities of water or other contaminants. Material will float and may ignite on surface of water. During fire, gases hazardous to health may be formed.



1801 Morgan Street
 Rockford, IL 61102
 Phone: (815) 968-9661
 Fax: (815) 968-9731
 www.gcelectronics.com

SDS Number: 203
 Revision Date: 08/18/2015
 Supersedes Date: 03/27/2014

SAFETY DATA SHEET

Complies with OSHA Hazard Communication Standard 29 CFR 1910.1200

Product Name: GLASS TREATMENT COMPOUND

SECTION 5. FIRE-FIGHTING MEASURES (CONTINUED)

Special protective equipment and precautions for firefighters	Self-contained breathing apparatus and full protective clothing must be worn in case of fire.
Fire fighting equipment/instructions	In case of fire and/or explosion do not breathe fumes. Move containers from fire area if you can do so without risk.
Specific methods	Use standard firefighting procedures and consider the hazards of other involved materials.
General fire hazards	Highly flammable liquid and vapor.

SECTION 6. ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures	Keep unnecessary personnel away. Keep people away from and upwind of spill/leak. Eliminate all ignition sources (no smoking, flares, sparks, or flames in immediate area). Wear appropriate protective equipment and clothing during clean-up. Do not touch damaged containers or spilled material unless wearing appropriate protective clothing. Ventilate closed spaces before entering them. Use appropriate containment to avoid environmental contamination. Transfer by mechanical means such as vacuum truck to a salvage tank or other suitable container for recovery or safe disposal. Local authorities should be advised if significant spillages cannot be contained. For personal protection, see section 8 of the SDS.
Methods and materials for containment and cleaning up	Eliminate all ignition sources (no smoking, flares, sparks, or flames in immediate area). Take precautionary measures against static discharge. Use only non-sparking tools. Keep combustibles (wood, paper, oil, etc.) away from spilled material. Large Spills: Stop the flow of material, if this is without risk. Dike the spilled material, where this is possible. Cover with plastic sheet to prevent spreading. Use a non-combustible material like vermiculite, sand or earth to soak up the product and place into a container for later disposal. Following product recovery, flush area with water. Small Spills: Absorb with earth, sand or other non-combustible material and transfer to containers for later disposal. Clean surface thoroughly to remove residual contamination.
Environmental precautions	Never return spills to original containers for re-use. For waste disposal, see section 13 of the SDS. Avoid discharge into drains, water courses or onto the ground. Use appropriate containment to avoid environmental contamination.



1801 Morgan Street
 Rockford, IL 61102
 Phone: (815) 968-9661
 Fax: (815) 968-9731
 www.gcelectronics.com

SDS Number: 203
 Revision Date: 08/18/2015
 Supersedes Date: 03/27/2014

SAFETY DATA SHEET

Complies with OSHA Hazard Communication Standard 29 CFR 1910.1200

Product Name: GLASS TREATMENT COMPOUND

SECTION 7. HANDLING AND STORAGE

Precautions for safe handling

Do not handle, store or open near an open flame, sources of heat or sources of ignition. Protect material from direct sunlight. When using do not smoke. Explosion-proof general and local exhaust ventilation. Minimize fire risks from flammable and combustible materials (including combustible dust and static accumulating liquids) or dangerous reactions with incompatible materials. Handling operations that can promote accumulation of static charges include but are not limited to: mixing, filtering, pumping at high flow rates, splash filling, creating mists or sprays, tank and container filling, tank cleaning, sampling, gauging, switch loading, vacuum truck operations. Take precautionary measures against static discharges. All equipment used when handling the product must be grounded. Use non-sparking tools and explosion-proof equipment. Avoid prolonged exposure. Wear appropriate personal protective equipment. Observe good industrial hygiene practices.

For additional information on equipment bonding and grounding, refer to the Canadian Electrical Code in Canada, (CSA C22.1), or the American Petroleum Institute (API) Recommended Practice 2003, "Protection Against Ignitions Arising out of Static, Lightning, and Stray Currents" or National Fire Protection Association (NFPA) 77, "Recommended Practice on Static Electricity" or National Fire Protection Association (NFPA) 70, "National Electrical Code".

Conditions for safe storage, including any incompatibilities

Keep away from heat, sparks and open flame. Prevent electrostatic charge build-up by using common bonding and grounding techniques. Eliminate sources of ignition. Avoid spark promoters. Ground/bond container and equipment. These alone may be insufficient to remove static electricity. Store in a cool, dry place out of direct sunlight. Store in original tightly closed container. Store in a well-ventilated place. Keep in an area equipped with sprinklers. Store away from incompatible materials (see Section 10 of the SDS).

SECTION 8. EXPOSURE CONTROLS/ PERSONAL PROTECTION

Occupational exposure limits

US. OSHA Table Z-1 Limits for Air Contaminants (29 CFR 1910.1000)

Components	Type	Value
2-PROPANOL (CAS 67-63-0)	PEL	980 mg/m3
		400 ppm

US. ACGIH Threshold Limit Values

Components	Type	Value
2-PROPANOL (CAS 67-63-0)	STEL	400 ppm
	TWA	200 ppm



1801 Morgan Street
 Rockford, IL 61102
 Phone: (815) 968-9661
 Fax: (815) 968-9731
 www.gcelectronics.com

SDS Number: 203
 Revision Date: 08/18/2015
 Supersedes Date: 03/27/2014

SAFETY DATA SHEET

Complies with OSHA Hazard Communication Standard 29 CFR 1910.1200

Product Name: GLASS TREATMENT COMPOUND

SECTION 8. EXPOSURE CONTROLS/ PERSONAL PROTECTION (CONTINUED)

US. NIOSH: Pocket Guide to Chemical Hazards

Components	Type	Value
2-PROPANOL (CAS 67-63-0)	STEL	1225 mg/m3
	TWA	500 ppm
		980 mg/m3
		400 ppm

Biological limit values

ACGIH Biological Exposure Indices

Components	Value	Determinant	Specimen	Sampling Time
2-PROPANOL (CAS 67-63-0)	40 mg/l	Acetone	Urine	*

* - For sampling details, please see the source document.

Appropriate engineering controls Explosion-proof general and local exhaust ventilation. Good general ventilation (typically 10 air changes per hour) should be used. Ventilation rates should be matched to conditions. If applicable, use process enclosures, local exhaust ventilation, or other engineering controls to maintain airborne levels below recommended exposure limits. If exposure limits have not been established, maintain airborne levels to an acceptable level. Eye wash fountain and emergency showers are recommended.

Individual protection measures, such as personal protective equipment

- Eye/face protection** Wear safety glasses with side shields (or goggles).
- Skin protection**
- Hand protection** Wear appropriate chemical resistant gloves. Suitable gloves can be recommended by the glove supplier.
- Other** Wear suitable protective clothing.
- Respiratory protection** If engineering controls do not maintain airborne concentrations below recommended exposure limits (where applicable) or to an acceptable level (in countries where exposure limits have not been established), an approved respirator must be worn.
- Thermal hazards** Wear appropriate thermal protective clothing, when necessary.

General hygiene considerations When using do not smoke. Always observe good personal hygiene measures, such as washing after handling the material and before eating, drinking, and/or smoking. Routinely wash work clothing and protective equipment to remove contaminants.



1801 Morgan Street
Rockford, IL 61102
Phone: (815) 968-9661
Fax: (815) 968-9731
www.gcelectronics.com

SDS Number: 203
Revision Date: 08/18/2015
Supersedes Date: 03/27/2014

SAFETY DATA SHEET

Complies with OSHA Hazard Communication Standard 29 CFR 1910.1200

Product Name: GLASS TREATMENT COMPOUND

SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

Appearance

Physical state Liquid.
Form Liquid.
Color CLEAR

Odor MILD

Odor threshold Not available.

pH Not available.

Melting point/freezing point 32 °F (0 °C)

Initial boiling point and boiling range 210.74 °F (99.3 °C) estimated

Flash point 64.3 °F (17.9 °C) estimated

Evaporation rate Not available.

Flammability (solid, gas) Not applicable.

Upper/lower flammability or explosive limits

Flammability limit - lower (%) 2.5 % estimated

Flammability limit - upper (%) 12 % estimated

Explosive limit - lower (%) Not available.

Explosive limit - upper (%) Not available.

Vapor pressure 2.42 hPa estimated

Vapor density Not available.

Relative density Not available.

Solubility(ies)

Solubility (water) Not available.

Partition coefficient (n-octanol/water) Not available.

Auto-ignition temperature 750.2 °F (399 °C) estimated

Decomposition temperature Not available.

Viscosity Not available.



1801 Morgan Street
Rockford, IL 61102
Phone: (815) 968-9661
Fax: (815) 968-9731
www.gcelectronics.com

SDS Number: 203
Revision Date: 08/18/2015
Supersedes Date: 03/27/2014

SAFETY DATA SHEET

Complies with OSHA Hazard Communication Standard 29 CFR 1910.1200

Product Name: GLASS TREATMENT COMPOUND

SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES (CONTINUED)

Other information

Density	8.24 lbs/gal
Explosive properties	Not explosive.
Flammability class	Flammable IB estimated
Oxidizing properties	Not oxidizing.
Percent volatile	99.94 % estimated
Specific gravity	0.99
VOC (Weight %)	4 % estimated

SECTION 10. STABILITY AND REACTIVITY

Reactivity	The product is stable and non-reactive under normal conditions of use, storage and transport.
Chemical stability	Material is stable under normal conditions.
Possibility of hazardous reactions	No dangerous reaction known under conditions of normal use.
Conditions to avoid	Avoid heat, sparks, open flames and other ignition sources. Avoid temperatures exceeding the flash point. Contact with incompatible materials.
Incompatible materials	Strong oxidizing agents.
Hazardous decomposition products	No hazardous decomposition products are known.

SECTION 11. TOXICOLOGICAL INFORMATION

Information on likely routes of exposure

Inhalation	Prolonged inhalation may be harmful.
Skin contact	No adverse effects due to skin contact are expected.
Eye contact	Direct contact with eyes may cause temporary irritation.
Ingestion	Expected to be a low ingestion hazard.

Symptoms related to the physical, chemical and toxicological characteristics Direct contact with eyes may cause temporary irritation.

Information on toxicological effects

Acute toxicity



1801 Morgan Street
Rockford, IL 61102
Phone: (815) 968-9661
Fax: (815) 968-9731
www.gcelectronics.com

SDS Number: 203
Revision Date: 08/18/2015
Supersedes Date: 03/27/2014

SAFETY DATA SHEET

Complies with OSHA Hazard Communication Standard 29 CFR 1910.1200

Product Name: GLASS TREATMENT COMPOUND

SECTION 11. TOXICOLOGICAL INFORMATION (CONTINUED)

Components	Species	Test Results
2-PROPANOL (CAS 67-63-0)		
Acute		
Dermal		
LD50	Rabbit	12800 mg/kg
Oral		
LD50	Dog	4797 mg/kg
	Mouse	3600 mg/kg
	Rabbit	5.03 g/kg
	Rat	4.7 g/kg

* Estimates for product may be based on additional component data not shown.

Skin corrosion/irritation	Prolonged skin contact may cause temporary irritation.
Serious eye damage/eye irritation	Direct contact with eyes may cause temporary irritation.
Respiratory or skin sensitization	
Respiratory sensitization	Not a respiratory sensitizer.
Skin sensitization	This product is not expected to cause skin sensitization.
Germ cell mutagenicity	No data available to indicate product or any components present at greater than 0.1% are mutagenic or genotoxic.
Carcinogenicity	This product is not considered to be a carcinogen by IARC, ACGIH, NTP, or OSHA.
OSHA Specifically Regulated Substances (29 CFR 1910.1001-1050)	
Not listed.	
Reproductive toxicity	This product is not expected to cause reproductive or developmental effects.
Specific target organ toxicity - single exposure	Not classified.
Specific target organ toxicity - repeated exposure	Not classified.
Aspiration hazard	Not an aspiration hazard.
Chronic effects	Prolonged inhalation may be harmful.



1801 Morgan Street
 Rockford, IL 61102
 Phone: (815) 968-9661
 Fax: (815) 968-9731
 www.gcelectronics.com

SDS Number: 203
 Revision Date: 08/18/2015
 Supersedes Date: 03/27/2014

SAFETY DATA SHEET

Complies with OSHA Hazard Communication Standard 29 CFR 1910.1200

Product Name: GLASS TREATMENT COMPOUND

SECTION 12. ECOLOGICAL INFORMATION

Ecotoxicity The product is not classified as environmentally hazardous. However, this does not exclude the possibility that large or frequent spills can have a harmful or damaging effect on the environment.

Components	Species	Test Results
2-PROPANOL (CAS 67-63-0)		
Aquatic		
Fish	LC50 Bluegill (<i>Lepomis macrochirus</i>)	> 1400 mg/l, 96 hours

* Estimates for product may be based on additional component data not shown.

Persistence and degradability No data is available on the degradability of this product.

Bioaccumulative potential

Partition coefficient n-octanol / water (log Kow)	
2-PROPANOL	0.05

Mobility in soil No data available.

Other adverse effects No other adverse environmental effects (e.g. ozone depletion, photochemical ozone creation potential, endocrine disruption, global warming potential) are expected from this component.

SECTION 13. DISPOSAL CONSIDERATIONS

Disposal instructions Collect and reclaim or dispose in sealed containers at licensed waste disposal site. Dispose of contents/container in accordance with local/regional/national/international regulations.

Local disposal regulations Dispose in accordance with all applicable regulations.

Hazardous waste code The waste code should be assigned in discussion between the user, the producer and the waste disposal company.

Waste from residues / unused products Dispose of in accordance with local regulations. Empty containers or liners may retain some product residues. This material and its container must be disposed of in a safe manner (see: Disposal instructions).

Contaminated packaging Since emptied containers may retain product residue, follow label warnings even after container is emptied. Empty containers should be taken to an approved waste handling site for recycling or disposal.

SECTION 14. TRANSPORTATION INFORMATION

DOT

Not regulated as dangerous goods.

DOT information on packaging may be different from that listed.



1801 Morgan Street
Rockford, IL 61102
Phone: (815) 968-9661
Fax: (815) 968-9731
www.gcelectronics.com

SDS Number: 203
Revision Date: 08/18/2015
Supersedes Date: 03/27/2014

SAFETY DATA SHEET

Complies with OSHA Hazard Communication Standard 29 CFR 1910.1200

Product Name: GLASS TREATMENT COMPOUND

SECTION 15. REGULATORY INFORMATION

US federal regulations This product is a "Hazardous Chemical" as defined by the OSHA Hazard Communication Standard, 29 CFR 1910.1200.

TSCA Section 12(b) Export Notification (40 CFR 707, Subpt. D)

Not regulated.

CERCLA Hazardous Substance List (40 CFR 302.4)

Not listed.

SARA 304 Emergency release notification

Not regulated.

OSHA Specifically Regulated Substances (29 CFR 1910.1001-1050)

Not listed.

Superfund Amendments and Reauthorization Act of 1986 (SARA)

Hazard categories Immediate Hazard - No
Delayed Hazard - No
Fire Hazard - Yes
Pressure Hazard - No
Reactivity Hazard - No

SARA 302 Extremely hazardous substance

Not listed.

SARA 311/312 Hazardous chemical No

SARA 313 (TRI reporting)

Not regulated.

Other federal regulations

Clean Air Act (CAA) Section 112 Hazardous Air Pollutants (HAPs) List

Not regulated.

Clean Air Act (CAA) Section 112(r) Accidental Release Prevention (40 CFR 68.130)

Not regulated.

Safe Drinking Water Act (SDWA) Not regulated.

US state regulations

US. California Controlled Substances. CA Department of Justice (California Health and Safety Code Section 11100)

Not listed.

US. California. Candidate Chemicals List. Safer Consumer Products Regulations (Cal. Code Regs, tit. 22, 69502.3, subd. (a))

2-PROPANOL (CAS 67-63-0)

US. Massachusetts RTK - Substance List

2-PROPANOL (CAS 67-63-0)



1801 Morgan Street
Rockford, IL 61102
Phone: (815) 968-9661
Fax: (815) 968-9731
www.gcelectronics.com

SDS Number: 203
Revision Date: 08/18/2015
Supersedes Date: 03/27/2014

SAFETY DATA SHEET

Complies with OSHA Hazard Communication Standard 29 CFR 1910.1200

Product Name: GLASS TREATMENT COMPOUND

SECTION 16. OTHER INFORMATION (CONTINUED)

GC Electronics believes that the information contained herein is accurate and reliable as of the date of this material safety data sheet, but no representation guarantee or warranty, express or implied, is made as to the accuracy, reliability or completeness of the information. Persons receiving information are encouraged to make their own determination as to the information's suitability and completeness for their particular application. NO INFORMATION CONTAINED HEREIN CONSTITUTES A PRODUCT WARRANTY OF ANY KIND, WHETHER EXPRESS OR IMPLIED; AND ALL IMPLIED WARRANTIES OF MERCHANT ABILITY AND OF FITNESS FOR A PARTICULAR PURPOSE ARE HEREBY DISCLAIMED BY GC ELECTRONICS.