I. MATERIALS AND FINISHES: BODY - BeCu, GOLD PLATING, .000030 [0.8] THICK OVER NICKEL CONTACT - BeCu, GOLD PLATING, .000030 [0.8] THICK OVER NICKEL INSULATOR - PTFE

2. ELECTRICAL:

A. IMPEDANCE: 50 OHM

B. FREQUENCY RANGE: DC - 26.5 GHz
C. VSWR(RETURN LOSS): 1.2 (20.8 dB), MAX. DC-10GHz 1.4 (15.6 dB), MAX. 10-18GHz

D. DIELECTRIC WITHSTANDING VOLTAGE: 500 VRMS, MIN.

3. PHYSICAL:

A. DURABILTIY: 100 CYCLES MIN.

B. ENGAGEMENT FORCE: 15 LB [67 N] MAX
C. DISINGAGEMENT FORCE: 2 LB [9 N] MIN
E. TEMERATURE RANGE: -65° C TO 165° C

4. PACKAGING:


A. QUANTITY: SINGLE PACK

B. MARKING: , AMPHENOL, SMP-FS-C07, DATE CODE


5. SEE AMPHENOL SPEC 349-50685 FOR CABLÉ

ASSEMBLY INSTRUCTIONS.





SCALE 6.000



CUSTOMER OUTLINE DRAWING ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES AND TOLERANCES ARE: 2 PLACE DECIMAL 3 PLACE DECIMAL ANGLES $\pm .015 \ (0,381\ \text{mm}) \ \pm .005 \ (0,127\ \text{mm}) \ \pm 1^{\circ}$ NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol Corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. The furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights or permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.	REFERENCE GEN# ASSYF2_SMP EAR# 967585-1 615X-1633-100	DRAWN MIKE HOYACK ENGINEER OWEN BARTHELMES APPROVED	DATE 02-0c+-01 DATE 15-Feb-01 DATE	SMP FEMALE SOCKET CONTACT TO .086 S/R CABLE	Amphenol Corporation Communication and Network Products Division Danbury, CT U.S.A. 06810
		CAD FILE		CODE ID DWG SIZEDRAWING	SCALE: 18.0:1 SHEET 2 OF 2 NO. REV
		I:\SMP\SMP-FS-C07			SMP-FS-C07 01