# Product data sheet Characteristics

# LC1D09EHE

TeSys D contactor - 3P - <= 440 V - 9 A AC-3 - 48...130 V AC/DC coil



### Main

| Main  |  |   |
|---|--|---|
| Range                                       | TeSys  |   |
| Product name                                | TeSys D Green  |   |
| Product or component type                   | Contactor  |   |
| Device short name                           | LC1D   |   |
| Contactor application                       | Motor control<br>Resistive load  |   |
| Utilisation category                        | AC-1<br>AC-3   | }<br>*  |
| Poles description                           | 3P   |   |
| Pole contact composition                    | 3 NO   |   |
| [Ue] rated operational voltage              | <= 690 V AC 25400 Hz for power circuit   |   |
| [le] rated operational current              | 25 A (<= 60 °C) at <= 440 V AC AC-1 for power circuit<br>9 A (<= 60 °C) at <= 440 V AC AC-3 for power circuit  |   |
| Motor power kW                              | 4 kW at 380400 V AC 50/60 Hz<br>2.2 kW at 220230 V AC 50/60 Hz<br>5.5 kW at 500 V AC 50/60 Hz<br>5.5 kW at 660690 V AC 50/60 Hz<br>4 kW at 415440 V AC 50/60 Hz                        | or o  |
| [Uc] control circuit voltage                | 48130 V DC<br>48130 V AC 50/60 Hz  |   |
| Coil type                                   | AC/DC electronic   |   |
| Auxiliary contact composition               | 1 NO + 1 NC  |   |
| [Uimp] rated impulse withstand voltage      | 6 kV conforming to IEC 60947   |   |
| Overvoltage category                        | III  |   |
| [Ith] conventional free air thermal current | 25 A at <= 60 °C for power circuit<br>10 A at <= 60 °C for signalling circuit  |   |
| Irms rated making capacity                  | 250 A at 440 V for power circuit conforming to IEC 60947<br>140 A AC for signalling circuit conforming to IEC 60947-5-1<br>250 A DC for signalling circuit conforming to IEC 60947-5-1 | Tick of the state |
| Rated breaking capacity                     | 250 A at 440 V for power circuit conforming to IEC 60947   | —— <u>-</u><br>ز  |
| [lcw] rated short-time withstand current    | 105 A <= 40 °C 10 s power circuit  |   |

|                                | 210 A <= 40 °C 1 s power circuit 30 A <= 40 °C 10 min power circuit 61 A <= 40 °C 1 min power circuit 100 A 1 s signalling circuit 120 A 500 ms signalling circuit 140 A 100 ms signalling circuit   |
|--------------------------------|--|
| Associated fuse rating         | 20 A gG at <= 690 V coordination type 2 for power circuit 25 A gG at <= 690 V coordination type 1 for power circuit 10 A gG for signalling circuit conforming to IEC 60947-5-1   |
| Average impedance              | 2.5 mOhm at 50 Hz - Ith 25 A for power circuit   |
| [Ui] rated insulation voltage  | 690 V for power circuit conforming to IEC 60947-4-1<br>690 V for signalling circuit conforming to IEC 60947-1  |
| Electrical durability          | 2.4 Mcycles 9 A AC-3 at Ue <= 440 V<br>650000 cycles 25 A AC-1 at Ue <= 440 V<br>83000 cycles AC-4 at Ue <= 440 V  |
| Power dissipation per pole     | 0.2 W AC-3<br>1.56 W AC-1  |
| Protective cover               | With   |
| Mounting support               | Plate<br>Rail  |
| Standards                      | EN/IEC 60947-4-1<br>UL 60947-4-1<br>CSA C22.2 No 60947-4-1<br>EN/IEC 60947-5-1   |
| Product certifications         | UL<br>CSA<br>CCC<br>EAC<br>KC  |
| Connections - terminals        | Control circuit: screw clamp terminals 2 cable(s) 12.5 mm² - cable stiffness: flexible - with cable end Power circuit: screw clamp terminals 1 cable(s) 14 mm² - cable stiffness: flexible - without cable end Control circuit: screw clamp terminals 1 cable(s) 14 mm² - cable stiffness: flexible - without cable end Control circuit: screw clamp terminals 2 cable(s) 14 mm² - cable stiffness: flexible - without cable end Control circuit: screw clamp terminals 1 cable(s) 14 mm² - cable stiffness: flexible - with cable end Control circuit: screw clamp terminals 1 cable(s) 14 mm² - cable stiffness: solid - without cable end Control circuit: screw clamp terminals 2 cable(s) 14 mm² - cable stiffness: solid - without cable end Power circuit: screw clamp terminals 1 cable(s) 14 mm² - cable stiffness: flexible - without cable end Power circuit: screw clamp terminals 2 cable(s) 14 mm² - cable stiffness: flexible - without cable end Power circuit: screw clamp terminals 2 cable(s) 14 mm² - cable stiffness: flexible - with cable end Power circuit: screw clamp terminals 2 cable(s) 12.5 mm² - cable stiffness: solid - without cable end Power circuit: screw clamp terminals 2 cable(s) 14 mm² - cable stiffness: solid - without cable end Power circuit: screw clamp terminals 2 cable(s) 14 mm² - cable stiffness: solid - without cable end |
| Tightening torque              | Power circuit: 1.7 N.m - on screw clamp terminals - with screwdriver flat Ø 6 mm Power circuit: 1.7 N.m - on screw clamp terminals - with screwdriver Philips No 2 Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver flat Ø 6 mm Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver Philips No 2  |
| Operating time                 | 4555 ms closing<br>2090 ms opening   |
| Safety reliability level       | B10d = 1369863 cycles contactor with nominal load conforming to EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load conforming to EN/ISO 13849-1  |
| Mechanical durability          | 15000000 cycles  |
| Operating rate                 | 3600 cyc/h at <= 60 °C   |
| Complementary                  |  |
| Coil technology                | Built-in bidirectional peak limiting   |
| Control circuit voltage limits | <= 0.1 Uc drop-out at 60 °C  |

| Complementary                   |  |
|---------------------------------|--|
| Coil technology                 | Built-in bidirectional peak limiting                           |
| Control circuit voltage limits  | <= 0.1 Uc drop-out at 60 °C<br>0.851.1 Uc operational at 60 °C |
| Inrush power in VA              | 25 VA at 20 °C 50/60 Hz  |
| Inrush power in W               | 24 W at 20 °C  |
| Hold-in power consumption in VA | 1.3 VA at 20 °C 50/60 Hz                                       |
| Hold-in power consumption in W  | 0.8 W at 20 °C   |
|                                 |  |

| Heat dissipation             | 0.8 W at 50/60 Hz  |  |
|------------------------------|--|--|
| Auxiliary contacts type      | Type mechanically linked (1 NO + 1 NC) conforming to IEC 60947-5-1  Type mirror contact (1 NC) conforming to IEC 60947-4-1 |  |
| Signalling circuit frequency | 25400 Hz   |  |
| Minimum switching current    | 5 mA for signalling circuit  |  |
| Minimum switching voltage    | 17 V for signalling circuit  |  |
| Non-overlap time             | 1.5 ms on de-energisation (between NC and NO contact) 1.5 ms on energisation (between NC and NO contact)                   |  |
| Insulation resistance        | > 10 MOhm for signalling circuit   |  |

## Environment

| IP20 front face conforming to IEC 60529   |
|---|
| TH conforming to IEC 60068-2-30   |
| 3   |
| -2560 °C  |
| -6080 °C  |
| -4070 °C at Uc  |
| 3000 m without derating in temperature  |
| 850 °C conforming to IEC 60695-2-1  |
| V1 conforming to UL 94  |
| Vibrations contactor open 2 Gn, 5300 Hz Vibrations contactor closed 4 Gn, 5300 Hz Shocks contactor open 10 Gn for 11 ms Shocks contactor closed 15 Gn for 11 ms |
| 77 mm   |
| 45 mm   |
| 86 mm   |
| 0.368 kg  |
| Grey SE GREY 6<br>Green SE GREEN 2  |
|   |

# Offer Sustainability

| Sustainable offer status         | Green Premium product   |  |
|----------------------------------|---|--|
| RoHS (date code: YYWW)           | Compliant - since 1640 - Schneider Electric declaration of conformity |  |
|                                  | Schneider Electric declaration of conformity                          |  |
| REACh                            | Reference not containing SVHC above the threshold                     |  |
|                                  | Reference not containing SVHC above the threshold                     |  |
| Product environmental profile    | Available   |  |
|                                  | Product environmental   |  |
| Product end of life instructions | Available   |  |
|                                  | End of life manual  |  |