

8330S

Description

This is a two-part, smooth, silver paste adhesive that cures to form a hard, durable polymer. In its cured state, it is extremely electrically and thermally conductive. It adheres strongly to metals and glass, and it adheres well to most plastics used in electronic assemblies.

It has a convenient 1-to-1 mix ratio and a long 4 hour working life. The mixed adhesive essentially acts like a one-part adhesive for the duration of a work shift. But unlike one-part adhesives, it does not require high curing temperatures or frozen storage, and it has a very long shelf life.

Applications & Usages

The 8330S is used as a solder replacement for bonding heat-sensitive electronic components and for making conductive bonds where solder is not an option, such as when bonding to glass, soft metals or plastics. It allows for quick cold soldering repairs of electronic devices, makes excellent thermal connections, provides excellent EMI/RFI shielding, and is very effective at filling in seams between metal plates. It is useful in applications where the high curing temperatures of one-part epoxy systems can potentially damage components.

Its primary applications are in the assembly of electronic devices. It is used in the automobile, aerospace, marine, communication, instrumentation, and industrial control equipment industries. It is also widely used by hobbyists and makers.

Benefits and Features

Electrical resistivity: 0.0007 Ω·cm

Thermal Conductivity: 1.75 W/(m·K)

1:1 mix ratio by volume

Working life: 4 hours

Cure time: 2 hours at 65 °C

Good adhesive strength

Strong resistance to water, brine, acids, bases, and aliphatic hydrocarbons

Room temperature storage

Shelf life greater than three years

Usage Parameters

Properties	Value
Working Life a)	4 h
Shelf Life	≥3 y
Full Cure @65 °C [149 °F]	2 h
Full Cure @80 °C [176 °F]	1 h
-	

a) Working life value assume 5 g and room temperature unless stated otherwise.

Rev. Date: 28 April 2017 / Ver. 2.06

ENVIRONMENT

✓ RoHS

✓ REACH compliant

Temperature Ranges

Properties	Value
Constant Service	-40 to 150 °C
Temperature	[-40 to 302 °F]
Storage Temperature	16 to 27 °C
of Unmixed Parts	[60 to 80 °F]
	_



8330S

Principal Components

Name

Part A: Epoxide Resin Metallic Silver Part B: Aliphatic Amines Metallic Silver **CAS Number**

28768-*32-3* + *17557-23-3* 7440-22-4 *68082-29-1*, *112-24-3*, *68541-13-9*, *4246-51-9* 7440-22-4

Properties of Cured 8330S

Physical Properties	Method	Value a)
Color	Visual	Silvery Grey
Density @26 °C [79 °F]	ASTM D 1475	2.82 g/mL
Hardness	Shore D durometer	73D
Tensile Strength	ASTM D 638	9.0 N/mm ² [1 300 lb/in ²]
Elongation	"	7.8%
Compressive Strength	ASTM D 695	36 N/mm ² [5 200 lb/in ²]
Lap Shear Strength (Stainless Steel 304)	ASTM D 1002	1.3 N/mm ² [190 lb/in ²]
(Aluminum 5052)	"	2.6 N/mm ² [380 lb/in ²]
Water absorption		0.32%
Outgassing (Total Mass Loss) @24 h	ASTM E 595	0.40 %
Water vapor release (WVR)	"	0.14 %
Collectable Volatile Condensable Material	"	0.03%
Solderable		No
Electric Properties b)	Method	Value
Volume Resistivity	Method 5011.5	0.0007 Ω·cm
After 65 °C [149 °F] cure	in MIL-STD-883H	0.0007 22 0
Thermal Properties	Method	Value
Thermal Conductivity @25 °C [77 °F]	ASTM E 1461	1.75 W/(m·K)
@50 °C [122 °F]	"	1.75 W/(m·K)
@100 °C [212 °F]	n .	1.68 W/(m·K)
Glass Transition Temperature (Tg)	ASTM D 3418	34 °C [93 °F]
CTE c) prior T _g	ASTM E 831	97 ppm/°C
CTE c) after T _q	ASTM E 831	208 ppm/°C
Specific Heat @25 °C [77 °F]		0.787 J/(g·K)
		, , ,
Note: Specifications are for energy samples t	hatana aad at 00 0C	for the annual contraction of

Note: Specifications are for epoxy samples that were cured at 80 °C for 1 hour. Additional curing time at room temperature was given to allow for optimum curing. Samples were conditioned at 23 °C and 50% RH prior to most tests.

- a) $N/mm^2 = mPa$; $lb/in^2 = psi$
- b) The uncured epoxy mixture does not conduct electricity well and can have high resistance. To attain stated resistivity, ensure that the mix ratio is followed and that the product is fully cured by heat curing.
- c) Coefficient of Thermal Expansion (CTE) units are in ppm/°C = in/in/°C \times 10⁻⁶ = unit/unit/°C \times 10⁻⁶

8330S

Properties of Uncured 8330S

Physical Property	Mixture ((1A:1B)	
Color	Silver Grey		
Density ^{a)}	3.4 g/mL		
Mix Ratio by volume (A:B) Mix Ratio by weight (A:B) Solids Content (w/w)	1:1 1.115:1 100%		
Physical Property	Part A	Part B	
Color	Silver Grey	Silver Grey	
Density	3.4 g/mL	2.9 g/mL	
Flash Point	>127 °C [261 °F]	>93 °C [200 °F]	
Resistivity of uncured material	Off-scale (no reading)	Off-scale (no reading)	

a) Calculated value based on measures densities of each part

Compatibility

Adhesion—As seen in the substrate adhesion table, the 8330S epoxy adheres to most materials found on printed circuit assemblies; however, it is not compatible with contaminants like water, oil, and greasy flux residues that may affect adhesion. If contamination is present, clean the printed circuit assembly with electronic cleaner such as MG Chemicals 4050 Safety Wash, 406B Super Wash, or 824 Isopropyl Alcohol.

Substrate Adhesion in Decreasing Order

Physical Properties	Adhesion
Steel	Stronger
Aluminum	
Fiberglass	
Wood	
Paper, Fiber	
Glass	
Rubber	
Polycarbonate	
Acrylic	▼
Polypropylene a)	Weaker

a) Does not bond to polypropylene

Storage

Store between 22 and 27 °C [72 and 80 °F] in dry area away from sunlight. Prolonged storage or storage at or near freezing temperatures can result in crystallization. If crystallization occurs, reconstitute the component to its original state by temporarily warming it to 50 to 60 °C [122 to 140 °F]. To ensure full homogeneity, stir thoroughly the warm component, reincorporating all settled material. Re-secure container lid and let cool down before use.

Rev. Date: 28 April 2017 / Ver. 2.06

8330S

Health, Safety, and Environmental Awareness

Please see the 8330S **Safety Data Sheet** (SDS) parts A and B for more details on transportation, storage, handling and other security guidelines.

Health and Safety: The 8330S parts can ignite if the liquid is both heated and exposed to flames or sparks.

Wear safety glasses or goggles and disposable polyvinyl chloride, neoprene, or nitrile gloves while handling liquids. Part B in particular causes skin burns and may cause sensitization if exposed over a long period of time. The epoxy will not wash off once cured: wear protective work clothing. Wash hands thoroughly after use or if skin contact occurs. Do not ingest.

Use in well-ventilated area since vapors may cause irritation of the respiratory tract and cause respiratory sensitization in susceptible individuals.

The cured epoxy resin presents no known hazard.

Part A

HMIS® RATING

HEALTH:	*	2
FLAMMABILITY:		1
PHYSICAL HAZARD:		0
PERSONAL PROTECTION:		

NFPA® 704 CODES



Approximate HMIS and NFPA Risk Ratings Legend:

0 (Low or none); 1 (Slight); 2 (Moderate); 3 (Serious); 4 (Severe)

Part B

HMIS® RATING

HEALTH:	*	3
FLAMMABILITY:		1
PHYSICAL HAZARD:		0
PERSONAL PROTECTION:		

NFPA® 704 CODES



Approximate HMIS and NFPA Risk Ratings Legend:

Rev. Date: 28 April 2017 / Ver. 2.06

0 (Low or none); 1 (Slight); 2 (Moderate); 3 (Serious); 4 (Severe)



8330S

Application Instructions

Follow the procedure below for best results. For mixing quantities that are less than 1 mL size or for stricter stoichiometry control, mix by weight ratio instead (requires a high precision balance). Heat cure is recommended to get the best possible conductivity.

To prepare 1:1 (A:B) epoxy mixture

- 1. Remove cap or cover.
- 2. For jars, stir each part individually to re-incorporate material that may have separated during storage.
- 3. Measure **one** part by volume of **A**.
- 4. Measure one part by volume of B.
- 5. Thoroughly mix the parts together with a stir stick until homogeneous.
- 6. Apply to with an appropriate sized stick for the application area.

CAUTION!

Do not cross contaminate. To avoid premature curing, use different stirring tools for parts A & B.

NOTE: Remember to recap the syringe or container promptly after use.

TIP: Due to the high viscosity and abrasiveness of the silver filler, you may preheat part A and part B to increase the flow and improve air release, but doing so will reduce the working time by about half for each 10 °C increments.

To heat cure the 8330S epoxy

Put in oven at 65 °C [149 °F] for 120 minutes or above. For optimum conductivity and faster cure, heat cure at temperatures up to 100 °C.

TIP: Hair dryers are normally rated not to exceed 60 °C, so they can generally be used to accelerate the cure.

You can cure the epoxy faster by using higher temperatures of up to 100 °C [212 °F].

<u>ATTENTION:</u> Keep the curing temperature well below temperature limit of heat sensitive components that may be present. As a guideline, remember that commercial grade devices normally can be safely operated up to 70 °C, industrial grade up to 85 °C, and military grade up to 175 °C.

<u>ATTENTION:</u> Heat guns can easily exceed the temperature limits for your assembly: they should not be used.

Packaging and Supporting Products

Cat. No.	Packaging	Net Volume		Net Weight		Packaging Weight	
8330S-21G 8330S-50ML	Syringe	6 mL	0.2 fl oz	18.7 g	0.66 oz	40 g	1.4 oz
8330S-200ML	Jar Can	50 mL 200 mL	1.6 fl oz 6.7 fl oz	156 g 625 g	5.51 oz 1.38 lb	220 g 710 g	0.5 lb 1.6 lb

Rev. Date: 28 April 2017 / Ver. 2.06



8330S

Technical Support

Contact us regarding any questions, improvement suggestions, or problems with this product. Application notes, instructions, and FAQs are located at www.mgchemicals.com.

Email: support@mgchemicals.com

Phone: +(1) 800-340-0772 (Canada, Mexico & USA)

+(1) 905-331-1396 (International)

Fax: +(1) 905-331-2862 or +(1) 800-340-0773

Mailing address: Manufacturing & Support Head Office

1210 Corporate Drive 9347–193rd Street

Burlington, Ontario, Canada Surrey, British Columbia, Canada

L7L 5R6 V4N 4E7

Warranty

M.G. Chemicals Ltd. warranties this product for 12 months from the date of purchase by the end user.

M.G. Chemicals Ltd. makes no claims as to shelf life of this product for the warranty. The liability of

M.G. Chemicals Ltd. whether based on its warranty, contracts, or otherwise shall in no case include incidental or consequential damage.

Disclaimer

This information is believed to be accurate. It is intended for professional end users having the skills to evaluate and use the data properly. *M.G. Chemicals Ltd.* does not guarantee the accuracy of the data and assumes no liability in connection with damages incurred while using it.

Rev. Date: 28 April 2017 / Ver. 2.06