


APHC-12706-S

Peltier Cooler Module

Data sheet



I_{max}	[A]	5.6
V_{max}	[Vdc]	14.7
$P_c \text{ max}$	[W]	54
ACR	[Ω]	2.2
ΔT_{max}	[$^{\circ}\text{C}$]	66
A	[mm]	40
A1	[mm]	44
B	[mm]	40
H	[mm]	4
L	[mm]	100
Wire	AWG	20

Features

- RoHs and Reach 161 compliant
- Solid-state reliability
- Built with high temperature solder with the ability to withstand $<200^{\circ}\text{C}$ assembly processing temperatures for short periods of time
- High integrity nickel diffusion barriers on elements
- High strength for rugged environments
- Porched style for enhanced leadwire strength
- Sealed & lapped for multi-module applications





- (At hot side temperature $T_h = 27^{\circ}\text{C} / 300\text{K}$, under dry N_2)
- $P_c \text{ max}$ = Cooling power at $\Delta T = 0$ and $I = I_{max}$
- ΔT_{max} = Temperature difference at $I = I_{max}$ and $P_c = 0$
- Max hot side temperature $T_h = 200^{\circ}\text{C}$ for best long term performance
- Max mounting pressure: 1.5MPa
- Wires: UL-style 1569, 105oC (Unstripped)



APHC-I2706-S

Peltier Cooler Module





Data sheet - At hot side temperature 25°C



APHC-I2706-S

Peltier Cooler Module

Data sheet - At hot side temperature 50°C



APHC-I2706-S

Peltier Cooler Module

Data sheet - At hot side temperature 75°C

