


## Plug - MSTBT 2,5/ 4-ST BK - 1893313

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Plug component, nominal current: 12 A, rated voltage (III/2): 320 V, number of positions: 4, pitch: 5 mm, connection method: Screw connection with tension sleeve, Color: black, contact surface: Tin



The figure shows a 10-position version of the product



### Key Commercial Data

|                                      |                                                                                      |
|--------------------------------------|--------------------------------------------------------------------------------------|
| Packing unit                         | 100 STK                                                                              |
| GTIN                                 |  |
| GTIN                                 | 4017918382117                                                                        |
| Weight per Piece (excluding packing) | 6.590 g                                                                              |
| Custom tariff number                 | 85366990                                                                             |
| Country of origin                    | Germany                                                                              |

### Technical data

#### Dimensions

|              |         |
|--------------|---------|
| Length [ l ] | 18.1 mm |
| Width [ w ]  | 20 mm   |
| Pitch        | 5 mm    |
| Dimension a  | 15 mm   |

#### General

|                             |                                      |
|-----------------------------|--------------------------------------|
| Range of articles           | MSTBT 2,5/...-ST                     |
| Type of contact             | Female connector                     |
| Number of positions         | 4                                    |
| Connection method           | Screw connection with tension sleeve |
| Insulating material group   | I                                    |
| Rated surge voltage (III/3) | 4 kV                                 |
| Rated surge voltage (III/2) | 4 kV                                 |
| Rated surge voltage (II/2)  | 4 kV                                 |

# Plug - MSTBT 2,5/ 4-ST BK - 1893313

## Technical data

### General

|                                        |                                                           |
|----------------------------------------|-----------------------------------------------------------|
| Rated voltage (III/3)                  | 250 V                                                     |
| Rated voltage (III/2)                  | 320 V                                                     |
| Rated voltage (II/2)                   | 630 V                                                     |
| Connection in acc. with standard       | EN-VDE                                                    |
| Nominal current $I_N$                  | 12 A                                                      |
| Nominal cross section                  | 2.5 mm <sup>2</sup>                                       |
| Maximum load current                   | 12 A (with a 2.5 mm <sup>2</sup> conductor cross section) |
| Insulating material                    | PA                                                        |
| Flammability rating according to UL 94 | V2                                                        |
| Internal cylindrical gage              | A3                                                        |
| Stripping length                       | 7 mm                                                      |
| Screw thread                           | M3                                                        |
| Tightening torque, min                 | 0.5 Nm                                                    |
| Tightening torque max                  | 0.6 Nm                                                    |

### Connection data

|                                                                                         |                      |
|-----------------------------------------------------------------------------------------|----------------------|
| Conductor cross section solid min.                                                      | 0.2 mm <sup>2</sup>  |
| Conductor cross section solid max.                                                      | 2.5 mm <sup>2</sup>  |
| Conductor cross section flexible min.                                                   | 0.2 mm <sup>2</sup>  |
| Conductor cross section flexible max.                                                   | 2.5 mm <sup>2</sup>  |
| Conductor cross section flexible, with ferrule without plastic sleeve min.              | 0.25 mm <sup>2</sup> |
| Conductor cross section flexible, with ferrule without plastic sleeve max.              | 2.5 mm <sup>2</sup>  |
| Conductor cross section flexible, with ferrule with plastic sleeve min.                 | 0.25 mm <sup>2</sup> |
| Conductor cross section flexible, with ferrule with plastic sleeve max.                 | 2.5 mm <sup>2</sup>  |
| Conductor cross section AWG min.                                                        | 24                   |
| Conductor cross section AWG max.                                                        | 12                   |
| 2 conductors with same cross section, solid min.                                        | 0.2 mm <sup>2</sup>  |
| 2 conductors with same cross section, solid max.                                        | 1 mm <sup>2</sup>    |
| 2 conductors with same cross section, stranded min.                                     | 0.2 mm <sup>2</sup>  |
| 2 conductors with same cross section, stranded max.                                     | 1.5 mm <sup>2</sup>  |
| 2 conductors with same cross section, stranded, ferrules without plastic sleeve, min.   | 0.25 mm <sup>2</sup> |
| 2 conductors with same cross section, stranded, ferrules without plastic sleeve, max.   | 1 mm <sup>2</sup>    |
| 2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, min. | 0.5 mm <sup>2</sup>  |
| 2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, max. | 1.5 mm <sup>2</sup>  |
| Minimum AWG according to UL/CUL                                                         | 30                   |
| Maximum AWG according to UL/CUL                                                         | 12                   |

### Standards and Regulations

|                                  |        |
|----------------------------------|--------|
| Connection in acc. with standard | EN-VDE |
|----------------------------------|--------|

## Plug - MSTBT 2,5/ 4-ST BK - 1893313

### Technical data

#### Standards and Regulations

|                                        |     |
|----------------------------------------|-----|
|                                        | CSA |
| Flammability rating according to UL 94 | V2  |

#### Environmental Product Compliance

|            |                                                                                                     |
|------------|-----------------------------------------------------------------------------------------------------|
| China RoHS | Environmentally Friendly Use Period = 50                                                            |
|            | For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration" |

### Classifications

#### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 272607xx |
| eCl@ss 4.1 | 27260701 |
| eCl@ss 5.0 | 27260701 |
| eCl@ss 5.1 | 27260701 |
| eCl@ss 6.0 | 27260704 |
| eCl@ss 7.0 | 27440402 |
| eCl@ss 8.0 | 27440309 |
| eCl@ss 9.0 | 27440309 |

#### ETIM

|          |          |
|----------|----------|
| ETIM 3.0 | EC001121 |
| ETIM 4.0 | EC002638 |
| ETIM 5.0 | EC002638 |
| ETIM 6.0 | EC002638 |

#### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30211810 |
| UNSPSC 7.0901 | 39121409 |
| UNSPSC 11     | 39121409 |
| UNSPSC 12.01  | 39121409 |
| UNSPSC 13.2   | 39121409 |

### Approvals

#### Approvals

#### Approvals

CSA / VDE Gutachten mit Fertigungsüberwachung / IECEx CB Scheme / cULus Recognized / EAC

#### Ex Approvals

## Plug - MSTBT 2,5/ 4-ST BK - 1893313

### Approvals

#### Approval details

|                                |                                                                                   |       |
|--------------------------------|-----------------------------------------------------------------------------------|-------|
| CSA                            |  | 13631 |
|                                | B                                                                                 | D     |
| mm²/AWG/kcmil                  | 28-12                                                                             | 28-12 |
| Nominal current I <sub>N</sub> | 10 A                                                                              | 10 A  |
| Nominal voltage U <sub>N</sub> | 300 V                                                                             | 300 V |

|                                            |                                                                                   |                                                                                                                                                                                                              |          |
|--------------------------------------------|-----------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------|
| VDE Gutachten mit<br>Fertigungsüberwachung |  | <a href="http://www.vde.com/en/Institute/OnlineService/VDE-approved-products/Pages/Online-Search.aspx">http://www.vde.com/en/Institute/OnlineService/<br/>VDE-approved-products/Pages/Online-Search.aspx</a> | 40004701 |
|                                            |                                                                                   |                                                                                                                                                                                                              |          |
| mm²/AWG/kcmil                              | 0.2-2.5                                                                           |                                                                                                                                                                                                              |          |
| Nominal current I <sub>N</sub>             | 12 A                                                                              |                                                                                                                                                                                                              |          |
| Nominal voltage U <sub>N</sub>             | 250 V                                                                             |                                                                                                                                                                                                              |          |

|                                |                                                                                     |                                                           |                |
|--------------------------------|-------------------------------------------------------------------------------------|-----------------------------------------------------------|----------------|
| IECEE CB Scheme                |  | <a href="http://www.iecee.org/">http://www.iecee.org/</a> | DE1-58978-B1B2 |
|                                |                                                                                     |                                                           |                |
| mm²/AWG/kcmil                  | 0.2-2.5                                                                             |                                                           |                |
| Nominal current I <sub>N</sub> | 12 A                                                                                |                                                           |                |
| Nominal voltage U <sub>N</sub> | 250 V                                                                               |                                                           |                |

|                                |                                                                                     |                                                                                                                                                       |                 |
|--------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------|
| cULus Recognized               |  | <a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a> | E60425-19931011 |
|                                | B                                                                                   | D                                                                                                                                                     |                 |
| mm²/AWG/kcmil                  | 30-12                                                                               | 30-12                                                                                                                                                 |                 |
| Nominal current I <sub>N</sub> | 15 A                                                                                | 10 A                                                                                                                                                  |                 |
| Nominal voltage U <sub>N</sub> | 300 V                                                                               | 300 V                                                                                                                                                 |                 |

|     |                                                                                     |         |
|-----|-------------------------------------------------------------------------------------|---------|
| EAC |  | B.01742 |
|-----|-------------------------------------------------------------------------------------|---------|

### Accessories

#### Accessories

#### Bridge

## Plug - MSTBT 2,5/ 4-ST BK - 1893313

### Accessories

Insertion bridge - EBP 2- 5 - 1733169



Insertion bridge, fully insulated, for connectors with 5.0 or 5.08 mm pitch, no. of positions: 2

Insertion bridge - EBP 3- 5 - 1733172



Insertion bridge, fully insulated, for connectors with 5.0 or 5.08 mm pitch, no. of positions: 3

Insertion bridge - EBP 4- 5 - 1733185



Insertion bridge, fully insulated, for connectors with 5.0 or 5.08 mm pitch, no. of positions: 4

### Cable housing

Cable housing - KGG-MSTB 2,5/ 4 - 1803882



Cable housing, pitch: 0 mm, number of positions: 4, dimension a: 20 mm, color: green

### Coding element

Coding profile - CP-MSTB - 1734634



Coding profile, is inserted into the slot on the plug or inverted header, red insulating material

### Labeled terminal marker

## Plug - MSTBT 2,5/ 4-ST BK - 1893313

### Accessories

Marker card - SK 5/3,8:FORTL.ZAHLEN - 0804183



Marker card, Card, white, labeled, Horizontal: Consecutive numbers 1 - 10, 11 - 20, etc. up to 91 - (99)100, Mounting type: adhesive, for terminal block width: 5 mm, Lettering field: 5 x 3.8 mm

---

### Screwdriver tools

Screwdriver - SZS 0,6X3,5 - 1205053



Actuation tool, for ST terminal blocks, insulated, also suitable for use as a bladed screwdriver, size: 0.6 x 3.5 x 100 mm, 2-component grip, with non-slip grip

---

### Terminal marking

Marker card - SK U/3,8 WH:UNBEDRUCKT - 0803906



Marker card, Sheet, white, unlabeled, can be labeled with: CMS-P1-PLOTTER, PLOTMARK, Office printing systems, Mounting type: adhesive, for terminal block width: 210 mm, Lettering field: 186 x 3.8 mm

---

Cable housing - KGG-MSTB 2,5/ 4 BK - 1962011

Cable housing, pitch: 0 mm, number of positions: 4, dimension a: 20 mm, color: black

---