Product datasheet Characteristics

RSL1PREU

interface plug-in relay - Zelio RSL - 1 C/O - 48 V DC - 6 A - with LED



Main

IVICIII		5
Range of product	Zelio Relay	
Series name	Interface relay	—- 1
Product or component type	Plug-in relay	
Device short name	RSL	
Contacts type and composition	1 C/O	—_ ¿
Contact operation	Standard	relia
[Uc] control circuit voltage	48 V DC	
[Ithe] conventional enclosed thermal current	6 A at -4055 °C	Suitabil
Status LED	With	—— <u>çiri</u>
Shape of pin	Flat (PCB type)	
Sale per indivisible quantity	10	

Complementary

Fixing mode	Plastic compression spring	
Average resistance	10600 Ohm (DC) at 23 °C +/- 10 %	
[Ui] rated insulation voltage	277 V conforming to cUL 250 V conforming to EN/IEC	9
[Uimp] rated impulse withstand voltage	6 kV conforming to IEC	
Contacts material	Silver alloy (AgSnO2)	7
[le] rated operational current	6 A 1 C/O (AC-1/DC-1) conforming to IEC/UL	5
Minimum switching current	100 mA	
Maximum switching voltage	277 V	<u>.</u> <u>.</u> <u>.</u> <u>.</u> .
Switching voltage	12 V	*
Maximum switching capacity	1500 VA 150 W	
Minimum switching capacity	120 mW	Ę
Operating rate	<= 72000 cycles/hour no-load	

<= 360	cycles/hour	under	heal

Mechanical durability	<= 10000000 cycles
Electrical durability	60000 cycles for resistive load (6 A at 250 V, AC-1)
Operating time	5 ms 12 ms reset
Marking	CE
Protection category	RT III
Operating position	Any position
Height	78.6 mm
Width	6.2 mm
Depth	101 mm
Terminals description ISO n°1	(11-12-14)OC (A1-A2)CO
Product weight	0.029 kg
Load current	6 A at 250 V AC for 0.5 mm mounting distance
Average coil consumption	0.17 W DC
Drop-out voltage threshold	>= 0.05 Uc
Contact terminal arrangement	Separate
Connections - terminals	Spring terminals (1 x 0.21 x 1.5 mm² / AWG 24AWG 16) flexible cable with cable end Spring terminals (1 x 0.21 x 1.5 mm² / AWG 24AWG 16) solid cable without cable end
Tightening torque	1040 N.m
Safety reliability data	B10d = 60000
Clamping force	1040 N
Control type	Without push-button
Mounting support	35 mm symmetrical DIN rail
Device presentation	Complete product

Environment

Input voltage	48 V AC/DC (input voltage limit: 43.257.6 V)
Dielectric strength	1000 V AC (between contacts) 4000 V AC (between coil and contact)
Standards	EN/IEC 61810-1 CSA C22.2 No 14 UL 508
Product certifications	GOST CSA UL
Ambient air temperature for storage	-4085 °C
Vibration resistance	5 gn +/- 1 mm (f = 10150 Hz) 10 cycles in operation conforming to EN/IEC 60068-2-6 10 gn +/- 1 mm (f = 10150 Hz) 10 cycles not operating conforming to EN/IEC 60068-2-6
IP degree of protection	IP40 conforming to EN/IEC 60529
Shock resistance	5 gn for11 ms not operating conforming to EN/IEC 60068-2-27 10 gn for11 ms in operation conforming to EN/IEC 60068-2-27
Ambient air temperature for operation	-4055 °C

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1417 - Schneider Electric declaration of conformity
	Schneider Electric declaration of conformity
REACh	Reference not containing SVHC above the threshold
	Reference not containing SVHC above the threshold
Product environmental profile	Available
	Product environmental
Product end of life instructions	Available
	End of life manual

Contractual warranty

Warranty period

18 months

Product datasheet Dimensions Drawings

RSL1PREU

Dimensions

