

## ACT20P ACT20P-BRIDGE-S

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 1429-0  
 Fax: +49 5231 14292083  
 www.weidmueller.com



### ACT20P: The flexible solution

- Precise and highly functional signal converters
- Simple configuration via display (Pro DCDC II), FDT/DTM software or DIP switch
- Release levers simplify handling
- More space in the control cabinet, from 12.5 mm wide for two channels

### General ordering data

Type	ACT20P-BRIDGE-S
Order No.	<a href="#">1067250000</a>
Version	ACT20P, Measuring bridge converter, Screw connection
GTIN (EAN)	4032248820856
Qty.	1 pc(s).

**ACT20P**  
**ACT20P-BRIDGE-S**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 1429-0  
 Fax: +49 5231 14292083  
 www.weidmueller.com

**Technical data****Dimensions and weights**

Width	22.5 mm	Width (inches)	0.886 inch
Height	117.2 mm	Height (inches)	4.614 inch
Depth	113.6 mm	Depth (inches)	4.472 inch
Net weight	156.9 g		

**Temperatures**

Humidity	10...90 % (no condensation)	Operating temperature	-40 °C...70 °C
Storage temperature	-40 °C...85 °C		

**Probability of failure**

MTTF	543 Years
------	-----------

**Input**

Number of inputs	1	Sensor	Resistance measuring bridge, Total resistance of all parallel resistance measuring bridges: min. 87Ω
Sensor supply	120 mA @ 10 V (= 4 x 350 Ω bridge resistors)	Input measurement range	± 10 mV / ± 20 mV / ± 30 mV / ± 50 mV (adjustable)
Bridge supply voltage	5 V or 10 V	Bridge sensitivity	1.0 mV / V to 5.0 mV / V

**Output**

Type	Voltage and current output (configurable)	Output voltage, note	0 ... 11 V (adjustable)
Output current	0...22 mA (adjustable)	load impedance voltage	600 Ω
load impedance current	≤ 600 Ω		

**General data**

Configuration	DIP switch and button	Linearity	Typically ± 0.05 % of signal range
Long-term drift	0.1 % / 10.000 h	Mounting rail	TS 35
Power consumption	3 W @ 24 V DC	Repeat accuracy	± 0.05% of signal range
Step response time	< 400 ms (10...90 %)	Supply voltage	10...60 V DC
Temperature coefficient	typ. 0.005 % / °C		

**Insulation coordination**

EMC standards	EN 61326	Insulation voltage	5.7 kV (input / output, input / supply)
Pollution severity	2	Rated voltage	300 V <sub>eff</sub>
Standards	DIN EN 61010-1, DIN EN 61000-4-2	Surge voltage category	III

**Output (analogue)**

Type (analogue output)	Voltage and current output (configurable)
------------------------	-------------------------------------------

Creation date September 1, 2017 4:25:37 PM CEST

Catalogue status 25.08.2017 / We reserve the right to make technical changes.

2

**Data sheet**

**ACT20P  
ACT20P-BRIDGE-S**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 1429-0  
 Fax: +49 5231 14292083  
 www.weidmueller.com

**Technical data**

**Connection data**

Type of connection	Screw connection	Tightening torque, min.	0.4 Nm
Tightening torque, max.	0.6 Nm	Clamping range, rated connection	2.5 mm <sup>2</sup>
Clamping range, rated connection, min.	0.5 mm <sup>2</sup>	Clamping range, rated connection, max.	2.5 mm <sup>2</sup>
Wire connection cross section AWG, min.	AWG 30	Wire connection cross section AWG, max.	AWG 14


**Rated data UL**

UL certificate	Listing no.: E256486
----------------	----------------------

**Classifications**

ETIM 3.0	EC002479	ETIM 4.0	EC002653
ETIM 5.0	EC002653	ETIM 6.0	EC002653
eClass 5.1	27-21-01-07	eClass 6.2	27-21-01-20
eClass 7.1	27-21-01-20	eClass 8.1	27-21-01-20
eClass 9.0	27-21-01-20	eClass 9.1	27-21-01-90

**Approvals**

Approvals	
-----------	-------------------------------------------------------------------------------------

ROHS	Conform
------	---------

**Downloads**


Approval/Certificate/Document of Conformity	<a href="#">Declaration of Conformity</a>
Brochure/Catalogue	<a href="#">CAT 4.1 ELECTR 16/17 EN</a>
Engineering Data	<a href="#">EPLAN_WSCAD</a>
User Documentation	<a href="#">Quickstart_german.pdf</a> <a href="#">Instruction sheet</a>

**ACT20P  
ACT20P-BRIDGE-S**


**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 1429-0  
 Fax: +49 5231 14292083  
 www.weidmueller.com

**Drawings**

**Electric symbol**



**Dimensioned drawing**



dimensions

