
Surface Mount Chip LEDs

Technical Data

HSMB-C190/C170/C110

Features

- **Small Size**
- **Industry Standard Footprint**
- **Compatible with IR Solder**
- **Diffused Optics**
- **Operating Temperature Range of -30°C to +85°C**
- **Right Angle Package Available**
- **SiC Blue Color**
- **Available in 8 mm tape on 7" (178 mm) Diameter Reels**

Applications

- **Keypad Backlighting**
- **Push-Button Backlighting**
- **LCD Backlighting**
- **Symbol Backlighting**
- **Front Panel Indicator**

Description

These Blue chip LEDs are designed in an industry standard package for ease of handling and use. Blue color chip LED is a new product that offers color differentiation for backlighting applications.

The HSMB-C170 has the widely used 2.0 x 1.25 mm footprint. The HSMB-C190 has the industry standard 1.6 x 0.8 mm footprint, its low 0.8 mm profile and wide viewing angle make this LED exceptional for backlighting applications.

The HSMB-C110 is a right-angle package with the universally accepted dimensions of 3.2 x 1.0 x 1.5 mm. This part is ideal for



LCD backlighting and sidelighting applications.

All packages are compatible with IR reflow solder processes. The small size and wide viewing angle make these LEDs prime choices for backlighting applications and front panel illumination especially where space is a premium.


Device Selection Guide

Footprint (mm)	SiC Blue	Parts Per Reel
2.00 x 1.25	HSMB-C170	4000
1.60 x 0.80	HSMB-C190	4000
3.20 x 1.00 ^[1]	HSMB-C110	3000


Note:

1. Right-angle package.


Package Dimensions



HSMB-C190



HSMB-C170



HSMB-C110

NOTE:

1. ALL DIMENSIONS IN MILLIMETERS (INCHES).
2. TOLERANCE IS ± 0.1 mm (± 0.004 IN.) UNLESS OTHERWISE SPECIFIED.

Absolute Maximum Ratings at $T_A=25^\circ\text{C}$

Parameter	HSMB-C190/C170/C110	Units
DC Forward Current ^[1]	20	mA
Peak Pulsing Current ^[2]	100	mA
Power Dissipation	92	mW
Reverse Voltage ($I_R = 100\ \mu\text{A}$)	5	V
Maximum LED Junction Temperature	95	$^\circ\text{C}$
Operating Temperature Range	-30 to +85	$^\circ\text{C}$
Storage Temperature Range	-40 to +85	$^\circ\text{C}$
Soldering Temperature	See IR soldering profile (Figure 7)	

Notes:

1. Derate linearly as shown in Figure 4 for temperature above 25°C .
2. Pulse condition of 1/10 duty and 0.1 msec. width.

Optical Characteristics at $T_A=25^\circ\text{C}$

Part No.	Color	Luminous Intensity ^[1] I_v (mcd) @ 20 mA		Peak Wavelength λ_{peak} (nm)	Dominant Wavelength λ_d (nm)	Viewing Angle $2\theta_{1/2}$ (degrees) ^[2]
		Min.	Typ.	Typ.	Typ.	Typ.
HSMB-C190/C170	SiC Blue	1.60	6.0	428	466	170
HSMB-C110	SiC Blue	1.60	6.5	428	466	130

Notes:

1. The luminous intensity, I_v , is measured at the peak of the spatial radiation pattern, which may not be aligned with the mechanical axis of the lamp package.
2. $\theta_{1/2}$ is the off-axis angle where the luminous intensity is 1/2 the peak intensity.

Electrical Characteristics at $T_A=25^\circ\text{C}$

Part No.	Forward Voltage V_F (Volts) @ $I_F = 20\ \text{mA}$		Reverse Breakdown V_R (Volts) @ $I_R = 100\ \mu\text{A}$	Thermal Resistance $R_{\theta_{J-P}}$ ($^\circ\text{C}/\text{W}$)	Capacitance C (pF) @ $V_F = 0\ \text{V}$, $f = 1\ \text{MHz}$
	Typ.	Max.	Min.	Typ.	Typ.
HSMB-C190/C170	3.8	4.6	5	300	67
HSMB-C110	3.8	4.6	5	300	67




Figure 1. Relative Intensity vs. Wavelength.




Figure 2. Forward Current vs. Forward Voltage.




Figure 3. Relative Luminous Intensity vs. Forward Current.




Figure 4. Maximum Forward Current vs. Ambient Temperature.





Figure 5. Relative Intensity vs. Angle for HSMB-C110.




Figure 6. Relative Intensity vs. Angle for HSMB-C170 and HSMB-C190.




Figure 7. Recommended Reflow Soldering Profile.




Figure 8. Recommended Soldering Pattern for HSMB-C170.




Figure 9. Recommended Soldering Pattern for HSMB-C190.




Figure 10. Recommended Soldering Pattern for HSMB-C110.

Note:

1. All dimensions in millimeters (inches).




Figure 11. Reeling Orientation.




Figure 12. Reel Dimensions.

Note:

1. All dimensions in millimeters (inches).




Figure 13. Tape Dimensions.




Figure 14. Tape Leader and Trailer Dimensions.

Notes:

1. All dimensions in millimeters (inches).
2. Tolerance is ± 0.1 mm (± 0.004 in.) unless otherwise specified.

Convective IR Reflow Soldering

For more information on IR
reflow soldering, refer to
Application Note 1060, *Surface
Mounting SMT LED Indicator
Components*.

www.hp.com/go/led

For technical assistance or the location of
your nearest Hewlett-Packard sales office,
distributor or representative call:

Americas/Canada: 1-800-235-0312 or
408-654-8675

Far East/Australasia: Call your local HP
sales office.

Japan: (81 3) 3335-8152

Europe: Call your local HP sales office.

Data subject to change.

Copyright © 1999 Hewlett-Packard Co.

5968-7452E (10/99)