


CABLE SPECIFICATION

SPEC NO. : RG59/U SIAMESE CCS COAXIAL CABLE

Customer No. 24-10281

Construction Item		Unit	Construction Item
Conductors	Construction	mm	$1/0.81 \pm 0.05$
	Material	---	CCS
	Filler Material	---	---
	O. D.	mm	0.81 ± 0.05
Insulators	Material	---	Foamed PE
	Diameter	mm	3.70 ± 0.01
	Average Thickness	mm	1.44 ± 0.05
	Colour	---	White
Outer Conductors	AL-PET Foil	um	AL-P-AL
	Type	---	Braid
	Material	---	ALMG
	Coverage	%	60%
	Diamater	mm	3.80 ± 0.15
Jacket	Material	---	PVC (CM)
	Diameter	mm	6.9 ± 0.15
	Average Thickness	mm	1.5 ± 0.10
	Extrusion	---	---
	Surface	---	---
	Colour	---	Black
Power Wire	Construction	mm	$16 \times 0.254 \text{CU}$
	Diameter	mm	3.2PVC
Inking	Inking Colour	---	White
	Inking	---	Stellar Labs SIAMESE RG59/U TYPE COAX 75OHM 18AWG 75degC 2250MHz +2C18 E188601 (UL) CM RoHS COMPLIANT
Line	Length	ft	1000

CONFIGURATION:



GENERAL TOLERANCES
(UNLESS SPECIFIED)

LENGTH: $X \pm 1$
 $.X \pm 0.2$
 $.XX \pm 0.10$
 ANGLE: $X^\circ \pm 1^\circ$
 $.X^\circ \pm 0^\circ 30'$

UNIT:mm


REV:

DRAWING XIAOSHENG 2008/10/07

CHECK

APPROVE

Stellar Labs™



S. P. NO.

P. O. NO.

SIZE

NAME

DWG. NO.

PAGE

RG59/U SIAMESE CCS
COAXIAL CABLE

1/1