

For Patient-Care Vicinity – UL 1363A Medical-Grade Power Strip, 4 15A Hospital-Grade Outlets, Safety Covers, 7 ft. Cord

MODEL NUMBER: **PS-407-HG-OEM**



Highlights

- Approved for use in patient-care vicinities when properly mounted
- Complies with UL 1363A specifications
- 4 NEMA 5-15R-HG outlets with integrated locking safety covers
- 7 ft. cord with NEMA 5-15P-HG plug reaches nearby outlets
- Easy to mount on a variety of surfaces, e.g. IV poles

Package Includes

- PS-407-HG-OEM UL 1363A Medical-Grade Power Strip, 7 ft. cord
- Owner's manual

Description

The PS-407-HG-OEM Medical-Grade Power Strip supplies power to movable plug-connected components mounted to a rack, table or pedestal in operating rooms, patient-care vicinities, therapy rooms, imaging environments and administrative areas. Compliant with UL 1363A specifications, this 120V, 50/60 Hz power strip features a NEMA 5-15P-HG hospital-grade plug and four NEMA 5-15R-HG hospital-grade outlets that include integrated locking safety covers.

Two built-in resettable 15A circuit breakers control power to all outlets and protect the power strip against overloads. Switchless design prevents the unit from being accidentally shut off. The seven-foot power cord provides ample reach to the AC power source.

Mounting tabs and flanges let you install the PS-407-HG-OEM on a wide variety of surfaces, such as IV poles, mobile carts, crash carts and mobile medical workstations. The all-metal housing ensures safety and is guaranteed to last a long time in demanding environments.

Features

Power Distribution Anywhere in Any Medical Facility

- Ideal for use in operating rooms, patient-care vicinities, therapy rooms, imaging environments and administrative areas
- For use on IV poles, mobile carts, crash carts and mobile workstations, when properly mounted
- 120V, 50/60 Hz power strip complies with UL 1363A specifications

Versatile Medical-Grade Solution

- 4 NEMA 5-15R-HG hospital-grade outlets provide consistent power
- 7 ft. power cord with NEMA 5-15P-HG hospital-grade plug provides ample reach to the power source
- Rugged, all-metal housing for long life in demanding environments

Premium Safety Features

- Integrated locking outlet safety covers block access to unused outlets
- Dual resettable built-in 15A circuit breakers protect against dangerous overloads



- Switchless design prevents accidental shutoff

Ready to Use Right Out of the Box

- Built-in mounting tabs and flanges for easy installation on a variety of surfaces

Specifications

OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(4) 5-15R-HG
Circuit Breaker (amps)	15
Overload Protection	2 x 15amp breakers (1 line, 1 neutral)
Outlet Orientation	Single row of 4
Right-Angle Outlets	No
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A, 120V
Input Connection Type	NEMA 5-15P-HG
Input Cord Length (ft.)	7
Input Cord Length (m)	2.13
Input Cord Gauge Type	14 gauge, SJT
Voltage Compatibility (VAC)	120
USER INTERFACE, ALERTS & CONTROLS	
Switches	No power switch
PHYSICAL	
Shipping Dimensions (hwd / in.)	15 x 6 x 3.55
Shipping Dimensions (hwd / cm)	38.1 x 15.24 x 9.02
Shipping Weight (lbs.)	2.9
Shipping Weight (kg)	1.32
Unit Dimensions (hwd / in.)	8.65 x 2.5 x 1.5
Unit Dimensions (hwd / cm)	21.97 x 6.35 x 3.81
Unit Weight (lbs.)	2.77
Unit Weight (kg)	1.26
Material of Construction	Metal



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Receptacle Color	White
Color (AC Line Cord)	White
Outlets Measurement (Center to Center)	Inner outlets = 32.5mm
CERTIFICATIONS	
Approvals	TUV tested to UL 1363A
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>