





1189A Coax - Broadband CATV Coax Cable

		<p>For more information please call 1-800-Belden1</p> <p><u>See Put-ups and Colors</u></p>
---	--	---

Description:

18 AWG solid .040" bare copper-covered steel conductor, gas-injected foam polyethylene insulation, Duobond® IV quad shield (60% and 40% coverage), PVC jacket.

PHYSICAL CHARACTERISTICS:

CONDUCTOR:

Number of Coax	1
Total Number of Conductors	1
Series Type	Series 6
AWG	18
Stranding	Solid
Conductor Diameter	.040 in.
Conductor Material	BCCS - Bare Copper Covered Steel

INSULATION:

Insulation Material	Gas-injected FPE - Foam Polyethylene
Insulation Diameter	.180 in.

OUTER SHIELD:

Outer Shield Material Trade Name	Duobond® IV
Outer Shield Type	Tape/Braid/Tape/Braid

Outer Shield Material :

Layer Number	Trade Name	Type	Material	% Coverage (%)
1	Bonded Duofoil®	Tape	Bonded Aluminum Foil-Polyester Tape-Aluminum Foil	100
2		Braid	AL - Aluminum	60
3	Duofoil®	Tape	Aluminum Foil-Polyester Tape-Aluminum Foil	100
4		Braid	AL - Aluminum	40

Outer Shield % Coverage	100 %
-------------------------	-------

OUTER JACKET:

Outer Jacket Material	PVC - Polyvinyl Chloride
-----------------------	--------------------------

OVERALL NOMINAL DIAMETER:



1189A Coax - Broadband CATV Coax Cable

Overall Nominal Diameter	.298 in.
--------------------------	----------

MECHANICAL CHARACTERISTICS:

Operating Temperature Range	-40°C To +80°C
Bulk Cable Weight	32 lbs/1000 ft.
Max. Recommended Pulling Tension	162 lbs.
Min. Bend Radius (Install)	3 in.

APPLICABLE SPECIFICATIONS AND AGENCY COMPLIANCE:

APPLICABLE STANDARDS:

NEC/(UL) Specification	CATV, CM
CEC/C(UL) Specification	CM
EU CE Mark (Y/N)	Yes
EU RoHS Compliant (Y/N)	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004

FLAME TEST:

UL Flame Test	UL1685 UL Loading
---------------	-------------------

SWEEP TEST:

Sweep Testing	5 MHz - 1 GHz
---------------	---------------

PLENUM/NON-PLENUM:

Plenum (Y/N)	N
Plenum Number	1189AP

ELECTRICAL CHARACTERISTICS:

Nom. Characteristic Impedance	75 Ohms
Nom. Inductance	.097 μ H/ft
Nom. Capacitance Conductor to Shield	16.2 pF/ft
Nominal Velocity of Propagation	83 %
Nominal Delay	1.2 ns/ft
Nom. Conductor DC Resistance @ 20 Deg. C	28.0 Ohms/1000 ft
Nominal Outer Shield DC Resistance @ 20°C	4.8 Ohms/1000 ft

Minimum Structural Return Loss :

Description	Frequency (MHz)	Start Frequency (MHz)	Stop Frequency (MHz)	Minimum Structural Return Loss (dB)
		5	1000	20

Max. Attenuation :

1189A Coax - Broadband CATV Coax Cable

Description	Frequency (MHz)	Start Frequency (MHz)	Stop Frequency (MHz)	Max. Attenuation (dB/100 ft.)
	5			.67
	55			1.60
	211			2.87
	270			3.24
	300			3.43
	350			3.72
	400			4.00
	450			4.26
	550			4.71
	750			5.59
	870			6.00
	1000			6.54

Max. Operating Voltage - UL 350 V RMS

PUT-UPS AND COLORS:

Item	Description	Put-Up (ft.)	Ship Weight (lbs.)	Jacket Color	Notes
1189A 0091000	#18 GIFHDLDP DBL SH PVC	1000	35	WHITE	C
1189A 009U1000	#18 GIFHDLDP DBL SH PVC	U1000	35	WHITE	
1189A 009U500	#18 GIFHDLDP DBL SH PVC	U500	18	WHITE	
1189A 0101000	#18 GIFHDLDP DBL SH PVC	1000	35	BLACK	
1189A 010U1000	#18 GIFHDLDP DBL SH PVC	U1000	35	BLACK	
1189A 010U500	#18 GIFHDLDP DBL SH PVC	U500	18.5	BLACK	
1189A 2901000	#18 GIFHDLDP DBL SH PVC	1000	34	BEIGE, LIGHT	
1189A Q5H1000	#18 GIFHDLDP DBL SH PVC	1000	34	WHITE, NEUTRAL	C

C = CRATE REEL PUT-UP.

Revision Number: 3 Revision Date: 12-01-2005

1189A Coax - Broadband CATV Coax Cable

© 2005 Belden Wire & Cable Company
All Rights Reserved.

Although Belden Electronics Division ("Belden") makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden CDT Electronics Division believes this product to be in compliance with the following environmental regulations: California Proposition 65 Consent Judgment For Wire & Cable Mfgs. (San Francisco Superior Court Nos. 312962 And 320342); EU RoHS (Directive 2002/95/EC, 27-Jan-2003); Material manufactured prior to the compliance date may still be in stock at Belden facilities and in our Distributor's inventory. EU ELV (Directive 2000/53/EC, 18-Sept-2000); EU WEEE (Directive 2002/96/EC, 27-Jan-2003); And EU BFR (Directive 2003/11/EC, 6-Feb-2003). The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information and belief at the date of its publication. The information provided in the Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden CDT Electronics Division declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.