


OPTIONAL BACK PANEL SHOWN
 0.100 [2.54mm] TH'K- ALUMINUM
 0.075 [1.91mm] TH'K- WHITE STEEL

(4) EACH #10-32 BRASS
 INSERTS, AND STAINLESS
 STEEL FLANGE AND
 FEET SCREWS

(4) EACH #10-32 BRASS INSERTS
 AND STAINLESS STEEL
 CAPTIVE COVER SCREWS




FRONT VIEW
 WITH COVER REMOVED
 AND BACK PANEL DISPLAYED


(4) POLYCARBONATE
 FLANGES (GLUED)

CLOSED CELL
 NEOPRENE
 GASKET


.14 [3.68]



(4) EACH #10-32 BRASS
 INSERTS AND PLATED
 CARBON STEEL TRUSS SCREW



MATERIAL:
 BOX- INJECTED POLYCARBONATE
 STANDARD COVER- INJECTED POLYCARBONATE
 CLEAR COVER - INJECTED POLYCARBONATE



PART No. PCJ1084F

for more information visit
www.hammfg.com
 Data subject to change without notice
 Drawing Not to Scale