

**Accessories**  
**TS 35X7.5/LL/6 2M/ST/ZN**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 1429-0  
Fax: +49 5231 14292083  
www.weidmueller.com

**Building installation wiring**

For building installations, we offer a complete system that revolves around the 10×3 copper rail and comprises perfectly coordinated components: from installation terminal blocks, neutral conductor terminal blocks and distribution terminal blocks to comprehensive accessories such as busbars and busbar holders.

**General ordering data**

Type	TS 35X7.5/LL/6 2M/ST/ZN
Order No.	<a href="#">0514570000</a>
Version	Mounting rail, TS 35, TS 35 x 7.5, with slot, Steel, galvanized, chromium-plated, 2000 mm
GTIN (EAN)	4008190980009
Qty.	2 m

## Data sheet

### Accessories TS 35X7.5/LL/6 2M/ST/ZN

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 1429-0  
 Fax: +49 5231 14292083  
 www.weidmueller.com

## Technical data

### Dimensions and weights

Length	2,000 mm	Length (inches)	78.74 inch
Width	35 mm	Width (inches)	1.378 inch
Height	35 mm	Height (inches)	1.378 inch
Depth	7.5 mm	Depth (inches)	0.295 inch
Net weight	310 g		

### Material data

Material	Steel	Surface finish	galvanized, chromium-plated
Colour	Silver		

### System specifications

Version	with slot	Mounting rail	TS 35, TS 35 x 7.5
---------	-----------	---------------	--------------------

### Additional technical data

Installation advice	Direct mounting	Type of mounting	Screwed
---------------------	-----------------	------------------	---------

### Mounting rail

Drill-hole diameter	5.2 mm	Short circuit strength corresponds to E-Cu wire	16 mm <sup>2</sup>
Slit gap	7 mm	Slit length	18 mm
Slit width	6.2 mm	Slotted drill holes	Yes
Solder eyelet hole diameter (D)	5.2 mm	Spacing of holes, centre-to-centre	25 mm
Thickness	1 mm		

### Rating data

Standards	DIN EN 60715
-----------	--------------

### Classifications

ETIM 3.0	EC001285	ETIM 4.0	EC001285
ETIM 5.0	EC001285	ETIM 6.0	EC001285
eClass 6.2	27-14-11-43	eClass 7.1	27-14-11-43
eClass 8.1	27-14-11-43	eClass 9.0	27-14-11-43
eClass 9.1	27-40-06-02		

### Approvals

ROHS	Conform
------	---------

### Downloads

Brochure/Catalogue	<a href="#">CAT 1 TERM 16/17 EN</a>
Engineering Data	<a href="#">EPLAN, WSCAD, Zuken E3.S</a>