



Power Supply
GLiTE
POWER

coolermaster.com

400W 460W



400W (Regular) : RS-400-PSAR-J3
400W (Passive PFC) : RS-400-PSAP-J3
460W (Regular) : RS-460-PSAR-J3
460W (Passive PFC) : RS-460-PSAP-J3


Features

1. Compliance with the newest Intel standard ATX 12V V2.3
2. More than 70% efficiency at typical load operation
3. High Performance components design for better reliability
4. Green design to meet Energy Star and Blue Angel requirements
5. Multiple protection design (OVP/ OCP /SCP / OPP)
6. Support dual +12V1 and +12V2 outputs for higher power usage
7. One 4+4 pin +12V CPU connector for high-end CPU
8. EMI & Noise filter built in design

Close Up









intelligent 120mm fan speed controller



Honey combo structure increases airflow for better heat dissipation



Connector Solutions

	20+4Pin	4+4Pin	SATA	Peripheral	Floppy	PCI-e
						
400W	1	1	4	3	1	1
460W	1	1	4	3	1	1

Specifications

Type	Intel ATX12V V2.31
Dimension (W / H / D)	150 x 86 x 140 (mm)
Input Frequency Range	47~63Hz
Power Good Signal	100~500ms
Hold Up Time	>17ms
Efficiency	70% Typical
MTBF	>100,000hrs
Protection	OVP / OCP / OPP / SCP
Operation Temperature	0~40 °C (Nominal Input Voltage)
Fan	120mm Fan
Certification	CE / GOST / C-tick

400W

Model	RS-400-PSAR-J3			RS-400-PSAP-J3		
AC Input	110-120Vac / 220-240Vac			220-240Vac		
Input Current	8A@115Vac ; 5A@220Vac			5A		
DC Output	+3.3V	+5V	+12V1	+12V2	-12V	5Vsb
	20A	16A	16A	16A	0.8A	2.5A
	120W		276W		9.6W	12.5W

460W

Model	RS-460-PSAR-J3			RS-460-PSAP-J3		
AC Input	110-120Vac / 220-240Vac			220-240Vac		
Input Current	8.5A@115Vac ; 5A@220Vac			6.3A		
DC Output	+3.3V	+5V	+12V1	+12V2	-12V	5Vsb
	20A	20A	18A	18A	0.8A	2.5A
	130W		324W		9.6W	12.5W