


Part Number: 5502FE

Security & Sound, #22-4c, BC, Shielded, CMR



Product Description

Security & Sound Cable, Riser-CMR, 4-22 AWG stranded bare copper conductors with polyolefin insulation, Beldfoil® shield and PVC jacket with ripcord

Technical Specifications

Use

Suitable Applications:	22 AWG Bare Copper Conductors ~ PP Insulation ~ Cabled ~ Beldfoil® Shield Tape (Foil Side Out) With Drain Wire ~ Gray PVC Jacket With Ripcord ~ Sequential Footage Marking Every Two Feet
------------------------	---

Physical Characteristics (Overall)

Conductor

Element	AWG	Stranding	Material	Nominal Diameter	No. of Conductors
4	4	7x30	TC - Tinned Copper	7x30	4
BC - Bare Copper					

Total Number of Conductors:	5502FE
-----------------------------	--------

Insulation

Material	Nominal Wall Thickness
PP - Polypropylene	PP - Polypropylene in
0.008 in	

Color Chart

Color
Black
Red
White
Green
Black
Red
White
Green

Outer Shield Material

Type	Layer	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire Diameter	Drainwire AWG	Drainwire Construction n x D
Tape		Beldfoil®	Tape	100 %	7x32	TC - Tinned Copper mm	24	Solid mm
	100							

Outer Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness	Ripcord
PVC - Polyvinyl Chloride	PVC - Polyvinyl Chloride in	0.017 in	Yes
	0.017 in		

Electrical Characteristics

Capacitance

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Other Conductor to Shield	Nom. Capacitance Conductor to Shield
---	---	--------------------------------------

Construction and Dimensions

Print Legend:	NEW GENERATION(R) BY BELDEN 5502FE CMR 75C 4C22 SHIELDED (UL) E108998 OR C(UL) CMG---FT4 (2 FT., 7 DIGIT SEQUENTIAL) FEET
---------------	---

Conductor DCR

Individual Pair Nominal Shield DCR	Nominal Conductor DCR	Nominal Outer Shield DCR
16.4 Ohm/1000ft	16.4 Ohm/1000ft	16.1 Ohm/1000ft

Current

Max. Recommended Current [A]
Per conductor @ 25°C: 2.2 A

Voltage

Non-UL Voltage Rating	UL Voltage Rating
300V RMS	300V RMS
	16.1 Ohm/1000ft

Applicable Standards & Environmental Programs

CEC/C(UL) Specification:	CMR
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2005-04-01
CPR Euroclass:	Eca
CA Prop 65:	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Standards

CSA AWM Specification:	CMG
NEC Articles:	17 lbs/1000ft
NEC/(UL) Specification:	42 lbs
UL AWM Style:	800

Flame Test

CSA Flammability:	UL1666 Riser
IEEE Flammability:	FT4
UL Flammability:	6502FE

Suitability

Suitability - Aerial:	Yes
Suitability - Indoor:	Yes

Mechanical Characteristics

Storage Temp Range:	-20°C To +75°C
---------------------	----------------

Operating Temp Range:	0.145 in
Bulk Cable Weight:	17(lbs/1000ft)
Max Recommended Pulling Tension:	42(lbs)
Min Bend Radius/Minor Axis:	1.375(in)

Temperature Range

UL Temp Rating:	75°C
-----------------	------

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Part Number

Non-Plenum Number:	No
--------------------	----

History

Variants

Item #	Color
5502FE.00152	GRAY
5502FE.00305	GRAY
5502FE.00U305	GRAY
5502FE 0081000	Gray
5502FE 008500	Gray
5502FE 008C500	Gray
5502FE 008U1000	Gray
5502FE 008U500	Gray

© 2017 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS(Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be instock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.