

FCC WARNINGS

- Warning: Changes or modifications to this unit not expressly approved by the party responsible for compliance could void the user's authority to operate the equipment.

NOTE: This equipment has been tested and found to comply with the limits for a Class B digital device, pursuant to Part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference in a residential installation. This equipment generates, uses, and can radiate radio frequency energy and, if not installed and used in accordance with the instructions, may cause harmful interference to radio communications. However, there is no guarantee that interference will not occur in a particular installation. If this equipment does cause harmful interference to radio or television reception, which can be determined by turning the equipment off and on, the user is encouraged to try to correct the interference by one or more of the following measures:

- Reorient or relocate the receiving antenna.
- Increase the separation between the equipment and receiver.
- Connect the equipment into an outlet on a circuit different from that to which the receiver is connected.
- Consult the dealer or an experienced radio/TV technician for help.

WARNINGS AND PRECAUTIONS

- **WARNING:** To prevent fire or shock hazards, do not expose this unit to rain or moisture.
- **WARNING :** Where the mains plug or appliance coupler is used as the disconnect device, such disconnect device shall remain readily operable.

International Support

To download this User's Guide in English, Spanish, or French, or to get answers to frequently asked questions, visit the support section at: **www.iLiveElectronics.com**.

Para descargar este Manual del Usuario en Inglés, Español y Francés, o para obtener respuestas a preguntas frecuentes, visite la sección de apoyo en:
www.iLiveElectronics.com.

Pour télécharger ce guide de l'utilisateur en Anglais, Espagnol ou Français, ou pour obtenir des réponses à des questions fréquemment posées, consultez la rubrique d'assistance sur:
www.iLiveElectronics.com.

Contact Information

Website: www.iLiveElectronics.com

Email Support: prodinfo@dpiinc.com

Email Parts: partsinfo@dpiinc.com

Phone Support: 1-888-999-4215

Warranty

For Warranty Information and the most up-to-date version of this User's Guide, go to: www.iLiveElectronics.com.



***Protect for Today
Sustain for Tomorrow***

Specifications are subject to change without notice.
Copyright © 2015 Digital Products International (DPI, Inc.)
All other trademarks appearing herein are the property
of their respective owners.



Wireless Speaker + LED Lightbulb

User's Guide for Model No. ILED75-1262-01


Features

- Supports Bluetooth
- Supports profile A2DP (Advanced Audio Distribution Profile)
- Wireless range: 60 feet
- LED light bulb with effects
- Color-changing lights with auto and manual color-changing modes
- Built-in speaker
- Brightness: 165 lumens
- Color temperature: 5300K
- Standard light socket size E26
- AC input: 110V - 240V

Includes


- Remote control: requires a CR2025 battery (pre-installed)

Unit Overview




Remote

Note: Remote IR signal range is 20-23 ft (6-7 m).



Remote Batteries

Remote control requires one CR2025 coin/button cell battery (included).



Slide



Out

Pairing a Bluetooth Device

When pairing, remain within 3 feet of the unit.

1. Press the **Pair** button on the remote.
*The light will begin **flashing blue**.*
2. Using the controls on your Bluetooth device, scan for and select **ILED75** in your Bluetooth settings to pair. If your device requests a password, enter the default password **0000**. *Refer to the user's manual for your specific device for instructions on pairing and connecting Bluetooth devices.*
3. When successfully paired, the light will switch to **solid blue**, then resume the last light mode.
4. Use the **Play/Pause** button on the remote or your Bluetooth device to play or pause an audio track.

If your device should become unpaired or you find it is unable to connect, repeat the above steps.