



# PYLE<sup>®</sup> PRO

PREMIUM  
*series*



## SPECIFICATIONS

PPA6  
PPA8  
PPA10  
PPA12  
PPA15  
PPA18



[WWW.PYLE-USA.COM](http://WWW.PYLE-USA.COM)

# About Pyle Pro Premium Series Woofer

**Congratulations! You have purchased one of our high power Pyle Pro woofer. Pyle Pro Premium Series Woofer is the professional PA woofer series, which has been designed and manufactured for consistent and high performance.**

General Features of Pyle Pro Premium Series Woofers Include:

- *Strong Paper Cone*
- *Cloth Edge Suspension*
- *Bumped Vented Pole Piece*
- *High Temperate KAPTON Voice Coils*
- *8 Ohm Impedence*

**We do confident that Premium Series Woofer will bring you many hours of enjoyment over the years.**


# Abort This Booklet

In this booklet, you could find the SPECIFICATIONS and TEMPLATE of the woofer. With this information, you could achieve the best performance of woofer conveniently.

Below is the meaning of the rating abbreviations.

- F<sub>s</sub>** : "Tree Air Resonance ",this value is the lowest audible frequency (in Hz) of the woofer.
- Q** : This value describes the degree fo control("damping")which the speaker exhibits.Speaker damping is due to both MECHANICALcharacteristics (Q<sub>ms</sub>) and ELECTRICAL characteristic s(Q<sub>es</sub>). A speaker's TOTAL DAMPLING VALUE is referring as Q<sub>ts</sub>.
- SPL** : This value means the sensitivity of the speaker.
- X<sub>max</sub>** : The overall distance ( in millimeters) the cone and voice coil travel in a single excursion is referred to as X<sub>max</sub>.
- VAS** : This value describes(in cubic feet) the maximum amount fo air which is displaced by the speaker cone in a sinle excursion.

# PPA12



## SPECIFICATIONS

PYLE PRO PREMIUM-SERIES-Woofer for small enclosures

Performance Parameters		Physical & Installation Parameters	
Power (Watts Peak/RMS)	700/200	Voice Coil	2"KSV
Nom. Impedance	8	Magnet	60 oz
F <sub>s</sub> (Hz)	35.5	Cone	Paper
Q <sub>ms</sub>	2.62	Surround	Cloth
Q <sub>es</sub>	0.88	Spider	Super
Q <sub>ts</sub>	0.66	Dust cap	Poly-concave
SPL (db)	90.0	Frame	Stamped Steel
X-max (mm)		Terminals	Spade
V <sub>as</sub> (cu ft)	4.517	Backplate	Bumped & Vented

PYLE PRO Continually strives to improve the performance and value of its products- all specifications are subject to change.