


Separating transformer **CT-150-048-12-1**




Advantages

Fused versions available
Versions with DIN rail for additional components available
100 % finger-safe
Jumpers included for primary voltage selection
Impregnated for max. protection
Up to 2500 VA

Applications

As an industrial control transformer for adjustment of the voltage and simple electrical isolation.

Sample application



Standards



Separating transformer
to: EN 61558 part 1 with part 2-1, UL 5085-1/-2;2:2, CSA 22.2 No. 66

Approvals



UL 5085-1/-2, CSA 22.2 No.66



Separating transformer CT-150-048-12-1

Type		CT-150-048-12-1
Electrical data	Special features	
	Characteristics	Fused version
	Input	
	Rated input voltage	240 x 480 Vac
		2 x 3,3 Aac
	Frequency Range	50 - 60 Hz
	Output	
	Rated output voltage	120 Vac
	Power	1500 VA
	No-load voltage (app. x factor)	1.04
	Efficiency	94 %
	Standards	
	Classification	Separating transformer
	Approvals	
	Approvals	cURus
	Environment	
	Ambient temperature	max. 104 °F
	Type of cooling	Air natural
	Safety and protection	
	Type	Open type
	Insulation class	B, class 130
	Protection index	IP 00
	Safety class (prepared)	I
	Short circuit strength	non-short-circuit proof
	Core	EI 192/66

Type		CT-150-048-12-1
Mechanical data	Measures and weights	
	Weight	36.82 lbs
Mechanical data	Dimensions in inch	
	<p>The drawing shows two views of the transformer. The front view (left) has a width of 6.0 inches and a total width including mounting feet of 7.56 inches. The side view (right) shows a height of 7.8 inches, a top width of 2.56 inches, a base width of 5.0 inches, and a total base width including mounting feet of 6.5 inches.</p>	

Subject to change.