

USB to Dual DisplayPort Mini Docking Station - Dual 4K 60Hz - GbE - USB 3.0

Product ID: USBA2DPGB



This USB to dual DisplayPort mini docking station makes it easy to create a high-performance dual-4K workstation, connecting your MacBook or Windows® laptop to two DisplayPort monitors plus Gigabit Ethernet wired network. The dock features a compact design that's perfect for business professionals who need a highly functional workstation when working or traveling between multiple office locations, or when using shared workspaces.

Enhance your productivity with two 4K monitors

The mini docking station lets you transform your laptop into a highly productive workstation, by expanding the display capabilities of your laptop across two Ultra HD 4K monitors, even if your laptop video card doesn't natively support it. The USB 3.0 docking station supports low-latency, high-resolution 4K graphics on both video ports, using DisplayPort monitors. It works with any laptop that has an available USB 3.0 (USB-A) port.

The mini dock supports DisplayLink® graphics technology, with the DisplayLink-6950 chipset, to provide support for dual 4Kp60 displays. With the dual-4K mini dock, you can connect:

- 2x 4K DisplayPort displays at 4096 x 2160 resolution @ 60Hz / 3840 x 2160 @ 60Hz
- Single 5K display at 5120 x 2880 @ 60Hz

The mini docking station is ideal for producers, graphic and web designers, engineers, architects and many other professionals who work on advanced graphics applications. It offers a fast and easy way to maximize your laptop's workable screen space, giving you three screens in total when coupled with your laptop's display.

Easily adaptable to multiple workspaces

The mini dock's compact size is ideal for business professionals working in space restricted workspaces or multiple locations, and require a high-performance dual-monitor workstation.

The Gigabit Ethernet port provides a reliable network connection in areas where Wi-Fi is limited or unavailable.

Effortless setup

The mini docking station ensures easy plug-and-play setup with no drivers required. It's bus-powered from your laptop, so no external power adapter is required.

The USB-A2DPGB is backed by a StarTech.com 3-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Saves time for business professionals working or travelling between multiple office locations, or office and home
- Ideal for temporary or shared workspaces where your device port requirements are minimal, but you need a secure wired network connection
- Ideal for graphics, engineering or media environments that require multiple higher resolution 4K monitors, and basic device connections

Features

- Enhance your productivity by connecting your laptop to dual DisplayPort monitors, with 4K (3840 x 2160) resolution @ 60Hz in extended mode
- Mac and Windows compatible, works with any laptop with an available USB 3.0 (USB-A) port
- Compact, mini form factor for smaller work spaces and easy portability
- Extended length 30 cm attached cable for maximum desktop positioning flexibility
- DisplayLink-6950 chipset provides support for dual 4Kp60 displays
- Gigabit Ethernet port with Wake-on-LAN support adds wired network connection to your workstation
- Bus-powered from laptop so no external power adapter required
- Support for single 5K DisplayPort monitor

Hardware	Warranty	3 Years
	4K Support	Yes
	Bus Type	USB 3.0
	Chipset ID	DisplayLink - DL-6950
	Displays Supported	2
	Fast-Charge Port(s)	No
	Industry Standards	IEEE 802.3, IEEE 802.3u, IEEE 802.3ab USB 3.0 - Backward compatible with USB 2.0/1.1
Performance	Auto MDIX	Yes
	Compatible Networks	10/100/1000 Mbps
	Full Duplex Support	Yes
	Maximum Data Transfer Rate	5 Gbps (USB 3.0) 2 Gbps (Ethernet; Full-Duplex)
	Maximum Digital Resolutions	Dual displays - DisplayPort - 4096 x 2160 @ 60Hz / 3840 x 2160 @ 60Hz
	Type and Rate	USB 3.0 - 5 Gbit/s
	UASP Support	No
Connector(s)	Connector Type(s)	2 - DisplayPort Female 1 - Ethernet Gigabit Female 1 - USB Type-A (9 pin) USB 3.0 Male
Software	OS Compatibility	Windows® 7, 8, 8.1, 10 macOS X 10.10 to 10.13
Special Notes / Requirements	Note	USB 3.0 is also known as USB 3.1 Gen 1; this connectivity standard offers speeds up to 5Gbps. 4K resolution is supported on both video ports. A 4K-capable DisplayPort display is required to achieve 4Kx2K resolution.
	System and Cable Requirements	A host laptop with an available USB-A port.
Power	Power Source	USB-Powered
Environmental	Humidity	10-90% RH
	Operating Temperature	0°C to 40°C (32°F to 104°F)
	Storage Temperature	-10°C to 60°C (14°F to 140°F)
Physical Characteristics	Cable Length	140 mm [5.5 in]
	Color	Black

	Product Height	20 mm [0.8 in]
	Product Length	130 mm [5.1 in]
	Product Weight	126 g [4.4 oz]
	Product Width	58 mm [2.3 in]
Packaging Information	Shipping (Package) Weight	215 g [7.6 oz]
What's in the Box	Included in Package	1 - mini dock 1 - quick-start guide

Product appearance and specifications are subject to change without notice.