

**Z-series
ZDUB 2.5-2/2AN/DM**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 1429-0
Fax: +49 5231 14292083
www.weidmueller.com

**Spring connection with tension clamp Technology**

Tension clamp technology is a universal contact system for all common conductor connection types. Its fantastic level of flexibility makes the tension clamp a profitable alternative connection.

General ordering data

| | |
|------------|---|
| Type | ZDUB 2.5-2/2AN/DM |
| Order No. | 1704350000 |
| Version | Z-series, Feed-through terminal, Rated cross-section: 2.5 mm ² , Tension clamp connection, Dark Beige, Direct mounting |
| GTIN (EAN) | 4008190948092 |
| Qty. | 100 pc(s). |

Z-series
ZDUB 2.5-2/2AN/DM

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 1429-0
 Fax: +49 5231 14292083
 www.weidmueller.com

Technical data
Dimensions and weights

| | | | |
|------------|---------|-----------------|------------|
| Width | 5.1 mm | Width (inches) | 0.201 inch |
| Height | 33.5 mm | Height (inches) | 1.319 inch |
| Depth | 24 mm | Depth (inches) | 0.945 inch |
| Net weight | 3.72 g | | |

Temperatures

| | | | |
|----------------------------------|--------|----------------------------------|--------|
| Continuous operating temp., min. | -50 °C | Continuous operating temp., max. | 120 °C |
|----------------------------------|--------|----------------------------------|--------|

Material data

| | | | |
|---------------------------|-------|--------|------------|
| Material | Wemid | Colour | Dark Beige |
| UL 94 flammability rating | V-0 | | |

Rating data IECEx/ATEX

| | | | |
|---------------------------------|---|--------------------------------|--------------------------|
| Certificate No. (ATEX) | KEMA97ATEX2755U | ATEX certificate | KEMA97ATEX2755U_d.pdf |
| ATEX certificate | KEMA97ATEX2755U_e.pdf | Certificate No. (IECEX) | IECEXKEM07.0061U |
| IEC Ex certificate | IECEXKEM07.0061U_e.pdf | Max. voltage (ATEX) | 550 V |
| Current (ATEX) | 21 A | Wire cross section max. (ATEX) | 2.5 mm ² |
| Max. voltage (IECEX) | 550 V | Current (IECEX) | 21 A |
| Wire cross section max. (IECEX) | 2.5 mm ² | Voltage, cross-connection | CrossConnectionGuide.pdf |
| Operating temperature range | For operating temperature range see EC Design Test Certificate / IEC Ex-Certificate of Conformity | Marking EN 60079-7 | |
| Ex 2014/34/EU label | II 2 G D | | Ex e II |

System specifications

| | | | |
|-------------------------------|--|-----------------------------------|----------------|
| Version | Tension-clamp connection, can only be bridged at the clamping point, One end without connector | End cover plate required | Yes |
| Number of levels | 1 | No. of clamping points per level | 2 |
| Number of potentials per tier | 1 | Levels cross-connected internally | No |
| PE connection | No | Mounting rail | Mounting plate |

Additional technical data

| | | | |
|--------------------------|-------|---------------------|-----------------|
| Explosion-tested version | Yes | Installation advice | Direct mounting |
| Open sides | right | Type of mounting | Direct mounting |

CSA rating data

| | | | |
|-------------------------------|-----------|-------------------------------|--------|
| Certificate No. (CSA) | 12400-379 | Current size C (CSA) | 25 A |
| Voltage size C (CSA) | 600 V | Wire cross section max. (CSA) | 12 AWG |
| Wire cross section min. (CSA) | 26 AWG | | |

Z-series
ZDUB 2.5-2/2AN/DM

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 1429-0
 Fax: +49 5231 14292083
 www.weidmueller.com

Technical data
Conductors for clamping (rated connection)

| | | | |
|---|----------------------|---|--------------------------|
| Blade size | 0.6 x 3.5 mm | Clamping range, rated connection, max. | 4 mm ² |
| Clamping range, rated connection, min. | 0.13 mm ² | Connection direction | top |
| Gauge to IEC 60947-1 | A2 | Number of connections | 2 |
| Stripping length | 10 mm | Type of connection | Tension clamp connection |
| Wire connection cross section AWG, max. | AWG 12 | Wire connection cross section AWG, min. | AWG 26 |
| Wire connection cross section, finely stranded with wire-end ferrules DIN 46228/1, rated connection, max. | 1.5 mm ² | Wire connection cross section, finely stranded with wire-end ferrules DIN 46228/1, rated connection, min. | 0.5 mm ² |
| Wire connection cross section, finely stranded, max. | 2.5 mm ² | Wire connection cross section, solid core max. rated connection | 4 mm ² |
| Wire connection cross section, solid core, min. rated connection | 0.5 mm ² | Wire connection cross-section, finely stranded, min. | 0.5 mm ² |

Dimensions

| | |
|--------------|-------|
| TS 15 offset | 17 mm |
|--------------|-------|

Rating data

| | | | |
|---------------------------------|---------------------|--|---------|
| Rated cross-section | 2.5 mm ² | Rated voltage | 800 V |
| Rated current | 24 A | Current at maximum wires | 30 A |
| Standards | IEC 60947-7-1 | Volume resistance according to IEC 60947-7-x | 1.33 mΩ |
| Rated impulse withstand voltage | 8 kV | Pollution severity | 3 |

UL rating data

| | | | |
|---|--------|---|--------|
| Certificate No. (UR) | E60693 | Conductor size Factory wiring max. (UR) | 12 AWG |
| Conductor size Factory wiring min. (UR) | 26 AWG | Conductor size Field wiring max. (UR) | 12 AWG |
| Conductor size Field wiring min. (UR) | 26 AWG | Current size C (UR) | 20 A |
| Voltage size C (UR) | 600 V | | |

Classifications

| | | | |
|------------|-------------|------------|-------------|
| ETIM 3.0 | EC000897 | ETIM 4.0 | EC000897 |
| ETIM 5.0 | EC000897 | ETIM 6.0 | EC000897 |
| UNSPSC | 30-21-18-11 | eClass 5.1 | 27-14-11-20 |
| eClass 6.2 | 27-14-11-20 | eClass 7.1 | 27-14-11-20 |
| eClass 8.1 | 27-14-11-06 | eClass 9.0 | 27-14-11-06 |
| eClass 9.1 | 27-14-11-20 | | |

Product information

| | |
|---------------------------------|--|
| Descriptive text technical data | Direct mounting |
| Descriptive text accessories | The terminal blocks are cross-connected when using the ZQB 2.5 (1677120000). |

Data sheet**Z-series
ZDUB 2.5-2/2AN/DM**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 1429-0
Fax: +49 5231 14292083
www.weidmueller.com

Technical data**Approvals**

Approvals



ROHS Conform

Downloads

| | |
|---|--|
| Approval/Certificate/Document of Conformity | CFAT_ZDUB 2.5-2_2AN.pdf DE_PT1111_20160418_1310_ISSUE01.pdf |
| Engineering Data | EPLAN, WSCAD, Zuken E3.S |
| User Documentation | Beipackzettel_ZDUB.pdf |

Safety noteSafety notice [Safety Information](#)

Data sheet

Z-series
ZDUB 2.5-2/2AN/DM

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 1429-0
Fax: +49 5231 14292083
www.weidmueller.com

Drawings

