



Schneider Electric Relays

200 N. Martingale Rd., Suite 1000

Schaumburg, IL 60173

Phone: 847-441-2540 • Fax: 847-881-0741

E-Mail: relays@schneider-electric.com • Web site: www.serelays.com

ITEM # 725AXXSC3ML-24D, 725 POWER RELAYS / SPST-NO, 30 AMP RATING (DC)

Note that image may not be exact representation of part number.



[SPECIFICATIONS](#) | [CONTACT CHARACTERISTICS](#) | [COIL CHARACTERISTICS](#) | [PERFORMANCE CHARACTERISTICS](#) | [ENVIRONMENT](#) | [PRODUCT CERTIFICATIONS](#)

Specifications	
Check Inventory	Check Distributor Inventory
Status	Standard
Cover Style	DIN & Flange Cover
Weight	120 g 4.20 oz
Options	LED Push Button
Horsepower Rating	3 hp at 277 VAC 50/60 Hz, 1.5 hp at 120 VAC 50/60 Hz
Tungsten Rating	1.5 kW at 120 VAC 50/60 Hz
Terminal Style	Screw: Coil - M3.5 combination head; Contacts - M4 combination head
Protection Category (Finger Safe)	IP 20

Contact Characteristics

Contact Rating	30 A
Contact Configuration	SPST-NO
Contact Materials	Silver Alloy
Maximum Switching Voltage (V)	300 V
Switching Current at Voltage (AC, Resistive)	30 A at 277 VAC 50/60 Hz
Switching Current at Voltage (DC, Resistive)	30 A at 30 VDC
Minimum Switching Requirement	100 mA at 5 VDC (0.5 W)

Coil Characteristics

Nominal Input Voltage	24 VDC
Coil Resistance (Ohms)	275 Ohm
Operating Range - % of Nominal (AC)	75 to 110 %
Operating Range - % of Nominal (DC)	75 to 110 %
Average Consumption (AC / VA)	2.50 VA
Average Consumption (DC / W)	1.90 W

Performance Characteristics

Electrical Life (UL508), Operations at Rated Current (Resistive)	100000
Mechanical Life, Unpowered	5000000
Operating Time (Response Time)	30 ms
Dielectric Strength - Between Coil and Contact	4000 VAC (rms)
Dielectric Strength - Between Poles	2000 VAC (rms)

Environment

Ambient Air Temperature around the Device - Storage	-50 to +100 °C
Ambient Air Temperature around the Device - Operation	-20 to +55 °C
Connection	Load: 10 / Coil: 12 AWG Load: 5.26 / Coil: 3.3 mm_

Terminal Tightening Torque

Nominal: 10.6 / Max: 20.3 in lb
Nominal: 1.2 / Max: 2.3 N_m

Product Certifications

Agency Approvals

UL (E43641)
CSA (168986)
CE (per IEC 60947-1)
RoHs