



Shown with Packard Connector



MSP340 Pressure Transducer

SPECIFICATIONS

- ◆ **Low Cost OEM**
- ◆ **100% Leak Proof**
- ◆ **No O-Rings**
- ◆ **No Silicon Oil**
- ◆ **No Welds**

The MSP340 pressure transducer from the Microfused™ line of MEAS is great for high volume, commercial and industrial applications. This series is suitable for measurement of liquid or gas pressure, even for difficult media such as contaminated water, steam, and mildly corrosive fluids.

The transducer pressure cavity is machined from a solid piece of 17-4 PH stainless steel. The standard version includes a 1/4 NPT pipe thread allowing a leak-proof, all metal sealed system. There are no O-rings, welds or organics exposed to the pressure media. The durability is excellent.

MEAS' proprietary Microfused™ technology, derived from demanding aerospace applications, employs micromachined silicon piezoresistive strain gages fused with high temperature glass to a stainless steel diaphragm. This approach achieves media compatibility simply and elegantly while providing an exceptionally stable sensor without the p-n junctions of conventional micromachined sensors.

This product is geared to the OEM customer who uses medium to high volumes. The standard version is suitable for many applications, but the dedicated design team at our Transducer Engineering Center stands ready to provide a semi-custom design where the volume and application warrants.

FEATURES

- ◆ One-Piece Stainless Steel Construction
- ◆ Ranges up to 10kpsi or 700Bar
- ◆ mV or Amplified Outputs
- ◆ Ultra Compact Construction
- ◆ Hermetically Isolated Sensor Technology

APPLICATIONS

- ◆ Pumps and Compressors
- ◆ Hydraulic/Pneumatic Systems
- ◆ After Market Automotive
- ◆ Tank Pressure in Breathing Apparatuses
- ◆ Agriculture – Sprayers and Dusters
- ◆ Refrigeration – Freon and Ammonia Based

STANDARD RANGES

Range	psig	Range	Barg
0 to 50	◆	0 to 3	◆
0 to 100	◆	0 to 7	◆
0 to 300	◆	0 to 20	◆
0 to 500	◆	0 to 35	◆
0 to 1k	◆	0 to 70	◆
0 to 3k	◆	0 to 200	◆
0 to 5k	◆	0 to 350	◆
0 to 10k	◆	0 to 700	◆

PERFORMANCE SPECIFICATIONS

Supply Voltage: 5.0V, Ambient Temperature: 25°C (unless otherwise specified)



PARAMETERS	MIN	TYP	MAX	UNITS	NOTES
Zero Offset Tolerance	-2.0		2.0	%F.S.	1
Span Tolerance	-2.0		2.0	%F.S.	1
Accuracy (combined non linearity, hysteresis, and repeatability)	-1.0		1.0	%F.S.	2
Long Term Stability (1 year)	-0.25		0.25	%F.S.	
Isolation, Body to Any Lead (@250Vdc)	50			MΩ	
Temperature Error – Zero	-2.0		2.0	%F.S.	
Temperature Error – Span	-2.0		2.0	%F.S.	
Compensated Temperature	0		55	°C	
Operating Temperature	-20		+85	°C	
Storage Temperature	-40		+85	°C	
Pressure Cycles (Zero to Full Scale)	1			Million	
Proof Pressure	2X			Rated	
Burst Pressure	5X			Rated	
Load Resistance (RL, mV Output)		RL > 1		MΩ	
Load Resistance (RL, V Output)		RL > 5		KΩ	
Bandwidth		DC to 1KHz (typical)			
Shock		50g, 11 msec Half Sine Shock per MIL-STD-202G, Method 213B, Condition A			
Vibration		±20g, MIL-STD-810C, Procedure 514.2-2, Curve L			

For custom configurations, consult factory.

Notes

- Over compensated temperature range.
- Best fit straight line.

DIMENSIONS



MSP340

Pressure Transducer

PRESSURE PORT		
CODE	PORT	DIM C
2	1/4-19 bsPP	0.47[11.94]
3	1/8-28 BSPP	.315[8.00]
4	7/16-20 UNF MALE SAE J514 STRAIGHT THREAD O-RING BUNA-n70SH-904 D8.92mm X W1383mm	0.385[9.70]
5	1/4-18 NPT	0.45[11.43]
6	1/8-27 NPT	0.45[11.43]
Q	M10X1.0mm	0.420[10.67]

Connection Code			
CODE	CONNECTION	DIMENSIONS	
1	CABLE, 4 WIRE BELDEN#8444, 2 FEET	DIM A	1.62[41.15]
2	CABLE, 4 WIRE BELDEN#8444, 4 FEET	DIM A	1.62[41.15]
4	PACKARD Metri-Pack CONNECTOR	DIM A	1.68[42.67]
		DIM B	2.43[61.72]
M	CABLE, 4 WIRE BELDEN#8444, 1METER	DIM A	1.62 [41.15]
N	CABLE, 4 WIRE BELDEN #8444, 2 METER	DIM A	1.62 [41.15]
P	CABLE, 4WIRE BELDEN#8444, 5 METER	DIM A	1.62 [41.15]
R	CABLE, 4 WIRE BELDEN #8444, 10	DIM A	1.62 [41.15]

OUTPUT OPTIONS

Code	Output	Supply(V)		
		MIN	TYP	MAX
2	0 – 20mV/V (ratiometric)	2.5	5	12
3	0.5 – 4.5V (ratiometric)	4.75	5	5.25
4	1 – 5V	10		30

Packard connector not available with mV output.

Wiring Code

Code	Output	+Supply	-Supply	+Out	-Out
2	0 – 20mV/V (ratiometric)	Red	Black	Green	White
3	0.5 – 4.5 V (ratiometric)	Pin A	Pin B [Common]	Pin C	N/A
4	1 – 5 V	Pin A	Pin B [Common]	Pin C	N/A

ORDERING INFORMATION

M34	2	3	0	0000	5	100P	G
Model Name							
Output	See "Output Options" Table						
Cable Length	See "Connection Code" Table						
Port Material	0 =17-4PH W =Wetted 316 Stainless Steel A =Customer Special (US) B =Customer Special (EU) C =Customer Special (Asia)						
Special	0000 =Standard XXXX =Customer Special						
Pressure Port	See Pressure Port Table						
Pressure Range	Refer to "Pressure Range Table"						
Pressure Type	G =Gage C =Compound						

Pressure Range		
Psi Std.	bar std.	bar din.
100P	007B	006B
200P	010B	010B
300P	020B	016B
500P	035B	025B
01KP	070B	040B
03KP	200B	060B
05KP	350B	100B
10KP	700B	160B
15KP	01KB	250B
		400B
		600B
		01KB

NORTH AMERICA

Measurement Specialties, Inc.,
 a TE Connectivity Company
 Phone: 800-522-6752
 Email: customercare.frm@te.com

EUROPE

Measurement Specialties (Europe), Ltd.,
 a TE Connectivity Company
 Phone: 800-440-5100
 Email: customercare.lcsb@te.com

ASIA

Measurement Specialties (China), Ltd.,
 a TE Connectivity Company
 Phone: 0400-820-6015
 Email: customercare.shzn@te.com

TE.com/sensorsolutions

Measurement Specialties, Inc., a TE Connectivity company.

Measurement Specialties, TE Connectivity, TE Connectivity (logo) and EVERY CONNECTION COUNTS are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2015 TE Connectivity Ltd. family of companies All Rights Reserved.