

LET'S HUNTERS SEE IN THE DARK. FOR DEER, IT'S LIGHTS OUT.

RevealXR™

F A S T F R A M E

LONG-RANGE THERMAL IMAGING CAMERA AND 300 LUMEN LED LIGHT

Durable, all-in-one thermal imager, with a detection range of up to 900 feet, giving hunters a clear advantage when out in the wild. Loaded with FastFrame imaging for smooth scanning on the go.



206 x 156
Thermal
Sensor



20°
Field of
View



-40° F to 626° F
Detection
Range



900 ft
Distance



Works
Day & Night



seek™
thermal

thermal.com

Distributed by:
Thomas Jacks Limited, Apex House, Timothy's Bridge Road, Statford-upon-Avon, Warwickshire, CV37 9BF
t 01789 264100 f 01789 264200 e info@thomasjacks.co.uk www.thomasjacks.co.uk

**THOMAS
JACKS**





SCOUT

PERFORMANCE FOCUSED

- 900-foot detection distance for tracking any time
- 206 x 156 Thermal Sensor for accurate prey spotting
- Powerful 300 Lumen Light for hunting safety and visibility
- FastFrame imaging displays more than 15 frames per second, providing smooth thermal imaging



TRACK

LONG-RANGE DETECTION THAT'S EASY TO USE

- Intuitive, single-handed interface
- Library of color palettes to customize the built-in display
- Micro SD card for photo capture and USB transfer
- Lasts up to 10 hours in continuous thermal imaging mode



RECOVER

SEEK A NEW ADVANTAGE

- Quick startup provides instant detection
- Accurately scout terrain from afar
- Track and recover day or night
- Stay safe without giving position away



RevealXR™
FASTFRAME

SUBJECT TO U.S. EAR EXPORT REGULATIONS

SPECIFICATIONS

DETECTOR & OPTICS

Thermal Sensor	206 x 156
Detection Distance	900 feet (300 yards, 275 meters)
Field of View	20 Degree FOV
Temperature Range	-40F to 626F (-40C to 330C)
Frame Rate	> 15 Hz FastFrame
Focus	Fixed Focus
Lens Material	Chalcogenide
Microbolometer	Vanadium Oxide
Pixel Pitch	12 Microns
Spectral Range	7.5 - 14 Microns

SYSTEM SPECS

Flashlight	300 Lumen LED (programmable brightness)
Display Resolution	2.4" Color, 240 x 320
Temp. Display Scale	Fahrenheit or Celsius
Color Palettes	7 Options
Startup Time	< 3 seconds
User Interface	Self-contained device with 3 button navigation
Storage Media	MicroSD Card Included
Battery	3.7V Rechargeable lithium
Battery Life (operating)	Up to 10 hours continuous thermal

DEVICE & PACKAGE INFO

Country of Origin	Designed and manufactured in Santa Barbara, California, USA with global components
Color	Camo
Device Dimensions (H x W x D)	5 x 2.4 x 1.2 inches
Device Weight	6.25 ounces
Box Dimensions (H x W x D)	6.25 x 3.75 x 3.25 inches
Package Weight	18.5 ounces
Included in the box	Seek RevealXR, Welcome Guide, Wrist Lanyard, MicroSD Card, and USB Cable

DESCRIPTION

For support and user guides visit support.thermal.com

Seek™
thermal

thermal.com

Distributed by:
Thomas Jacks Limited, Apex House, Timothy's Bridge Road, Statford-upon-Avon, Warwickshire, CV37 9BF
t 01789 264100 f 01789 264200 e info@thomasjacks.co.uk www.thomasjacks.co.uk

THOMAS JACKS

