



Acer recommends Windows 10 Pro.



TOWER DESKTOP

Veriton Essential

- 7th Gen Intel® Core™ i7/i5/i3 Processor*
- Newly Designed Tower
- Dual Display Support
- Seamless Manageability and Security



Acer ControlCenter



Acer Office Manager



ProShield Security



TPM





802.11ac
Wireless
connection



NVIDIA®
GEFORCE

SPECIFICATIONS **Veriton** **ES2710G**



| | | | | |
|--|---|--|---|---|
| Product views | 1. Status LEDs 2. Power button 3. Optical media drive 4. USB 2.0 port | 5. USB 2.0 port 6. Audio jack 7. Microphone jack 8. Power connector | 9. PS/2 ports 10. HDMI port 11. VGA port 12. Two USB 3.0 ports | 13. Two USB 2.0 ports 14. Audio jacks 15. Ethernet (RJ-45) port |
| Operating system^{1, 2} | Windows 10 Pro 64-bit Windows 10 Home 64-bit FreeDOS™ Linpus Lite Linux | | | |
| CPU and chipset¹ | 7 th generation Intel® Core™ i7 processors, Intel® HD Graphics 630 7 th generation Intel® Core™ i5 processors, Intel® HD Graphics 630 7 th generation Intel® Core™ i3 processors, Intel® HD Graphics 630 Intel® Pentium® processors, Intel® HD Graphics 630 / 610 Intel® Celeron® processors, Intel® HD Graphics 610 Chipset: Intel® H110 Express Chipset | | | |
| Memory^{1, 3, 4} | 16 GB / 8 GB / 4 GB / 2 GB DDR4 2400 MHz UDIMM • Up to 32GB of Dual-channel DDR4 2400 MHz | | | |
| Storage^{1, 5} | Hard disk drive • 256 GB / 128 GB 2.5-inch Solid State Drive • 2 TB / 1 TB 3.5-inch 7200 RPM | | | |
| Optical media drive | 8X DVD-RW drive, 9.0 mm slim, tray-load, M-DISC Ready™ | | | |
| Graphics⁶ | AMD Radeon™ R7 430, 2 GB GDDR5 NVIDIA® GeForce® GT 710, 1 GB DDR3 | | | |
| Audio | Integrated high-definition, 5.1-channel surround sound | | | |
| Communication | LAN: Gigabit Ethernet | | | |
| Expansion slot(s) | 1 PCIe x16 slot | | | |
| Software⁷ | • Acer Office Manager • Cyberlink® PowerDVD™ • Acer control center • Acer ProShield | | | |
| Commercial features | Kensington lock slot 2-in-1 cable and padlock slot Hard drive password protection (via BIOS) | | PXE (Preboot eXecution Environment) WOL (Wake On Lan) | |
| Commercial selected options⁸ | Internal speaker Dual-channel memory support TPM v2.0 (Trusted Platform Module) | | | |
| Dimensions | 165 (W) x 320 (D) x 340 (H) mm (6.5 x 12.6 x 13.39 inches) | | | |
| Power adapter and battery | Power supply • 300 W single-rail 12 V PFC (EuP), auto-sensing, 80PLUS Bronze • 220 W single-rail 12 V PFC (EuP), auto-sensing, 80PLUS Bronze, ATX form factor | | | |
| System compliance | DMI, ENERGY STAR®, GS, PC2001, RoHS | | | |
| Options and accessories | USB keyboard and mouse DVI-to-VGA adapter | | | |
| Certification | BSMI, CB, CE, FCC, VCCI | | | |

1. Specifications vary depending on model.
 2. 64-bit software is required to enjoy the advantages of 64-bit processing.
 3. A 64-bit operating system is required to enjoy the ultimate performance of 4 GB or higher memory.
 4. Memory speed may vary, depending on the CPU, chipset or memory fitted.
 5. 1 GB is 1 billion bytes. Actual formatted capacity is less and may vary depending on preloaded materials and operating environment. Recovery Management uses a portion of the stated hard disk capacity as dedicated backup space.
 6. Total available graphics memory comprises dedicated video memory, system memory, and shared system memory. This figure will vary depending on system memory, installed drivers, BIOS settings and other factors.
 7. Bundled software may vary depending on hardware configuration, OS and regional availability. For systems with a dual-channel configuration, the two memory modules inserted must be identical, including raw card, size, type, and speed.
 8.

In a continuing effort to improve the quality of our products, information in this document is subject to change without notice. Images shown are only representations of some of the configurations available for this model. Availability may vary depending on region. As a phenomenon known to thin-film transistors (TFTs), liquid crystal displays (LCDs) commonly exhibit a small number of discoloration dots, as so-called "non-conforming pixels." This phenomenon is a limitation of TFT LCD technology, not a product defect, and as such is not covered by Acer's warranty. © 2017. All rights reserved. Microsoft and Windows are registered trademarks of Microsoft Corporation. Intel, Intel Core, Core Inside, Pentium, and Pentium Inside are trademarks of Intel Corporation in the U.S. and other countries.

About Acer

Established in 1976, Acer is a hardware + software + services company dedicated to the research, design, marketing, sale, and support of innovative products that enhance people's lives. Acer's product offerings include PCs, displays, projectors, servers, tablets, smartphones, and wearables. The company is also developing cloud solutions to bring together the Internet of Things. Acer employs 7,000 people and ranks No. 4 for total PCs globally (IDC 2014). Revenues for 2014 reached US\$10.39 billion. Please visit www.acer.com for more information.