

## General Information

Extended Product Type:	OC25G06PNBN00NUH3
Product ID:	1SCA134813R1001
EAN:	6417019635637
Catalog Description:	OC25G06PNBN00NUH3 Cam switch
Long Description:	OC25 Cam switch, Ith=25A, Change-Over, 6-contacts, Snap-on door mounting, Black Basic handle. Black handle and frontplate with standard text are included. Special engraved frontplates to be ordered as separate items.

## Categories

Products » Low Voltage Products and Systems » Switches » Cam Switches

## Ordering

Minimum Order Quantity:	1 piece
Customs Tariff Number:	85365080

## Popular Downloads

Data Sheet, Technical Information:	<a href="#">1SCC302009C0201</a>
Wiring Diagram:	<a href="#">1SCC302014M0201</a>

## Dimensions

Product Net Width:	51 mm
Product Net Height:	51 mm
Product Net Depth:	107 mm
Product Net Weight:	0.14 kg

## Technical

Rated Operational Current AC-22A (I <sub>e</sub> ):	(500 V) 20 A (690 V) 20 A
Rated Operational Current AC-23A (I <sub>e</sub> ):	(690 V) Three Phase 5.9 A (500 V) Three Phase 8.1 A (230 V) Three Phase 15 A (400 V) Three Phase 15 A
Rated Operational Power AC-23A (P <sub>e</sub> ):	(690 V) Three Phase 4.8 kW (500 V) Three Phase 4.8 kW (230 V) Three Phase 2.6 kW (400 V) Three Phase 7.5 kW
Conventional Free-air Thermal Current (I <sub>th</sub> ):	q = 40 °C; C 25 A
Conventional Thermal Current (I <sub>the</sub> ):	Fully Enclosed 25 A
Rated Continuous Thermal Current:	25 A
Rated Impulse Withstand Voltage (U <sub>imp</sub> ):	4 kV
Rated Insulation Voltage (U <sub>i</sub> ):	690 V
Rated Operational Voltage:	690 V
Rated Short-time Withstand Current (I <sub>cw</sub> ):	for 1 s 0.3 kiloampere rms
Power Loss:	1.8 W
Pollution Degree:	3
Handle Type:	Basic handle
Special Functions:	Change-over switch: With 0-position: 12 o'clock, step angle 60°, front plate HAND-OFF-AUTO
Color:	Black
Mounting Type:	Snap-on door mounting
Number of Contacts:	6
Number of Poles:	3
Terminal Type:	Screw Terminals

## Technical UL/CSA

Ampere Rating UL/CSA:	600 V AC 25 A
-----------------------	---------------

## Certificates and Declarations (Document Number)

Declaration of Conformity - CE:	<a href="#">1SCC302005D0201</a>
---------------------------------	---------------------------------

### Container Information

Package Level 1 Units:	1 piece
Package Level 1 Width:	70 mm
Package Level 1 Length:	122 mm
Package Level 1 Height:	70 mm
Package Level 1 Gross Weight:	0.14 kg
Package Level 1 EAN:	6417019635637

### Classifications

Object Classification Code:	Q
ETIM 5:	EC002611 - Control switch
ETIM 6:	EC002611 - Control switch

