

OC25G16PNBN00NST44

General Information

Extended Product Type:	OC25G16PNBN00NST44
Product ID:	1SCA138368R1001
EAN:	6417019667379
Catalog Description:	OC25G16PNBN00NST44 Cam switch
Long Description:	OC25 Cam switch, I _{th} =25A, Multi-Step, 16-contacts, Snap-on door mounting, Black Basic handle, Black handle and frontplate with standard text are included. Special engraved frontplates to be ordered as separate items.

Categories

Products » Low Voltage Products and Systems » Switches » Cam Switches

Ordering

Minimum Order Quantity:	1 piece
Customs Tariff Number:	85365080

Popular Downloads

Data Sheet, Technical Information:	1SCC302009C0201
Wiring Diagram:	1SCC302014M0201

Dimensions

Product Net Width:	51 mm
Product Net Height:	51 mm
Product Net Depth:	167 mm
Product Net Weight:	0.25 kg

Technical

Rated Operational Current AC-22A (I_e):	(500 V) 20 A (690 V) 20 A
Conventional Free-air Thermal Current (I_{th}):	q = 40 °C 25 A
Conventional Thermal Current (I_{the}):	Fully Enclosed 25 A
Rated Continuous Thermal Current:	25 A
Rated Impulse Withstand Voltage (U_{imp}):	4 kV
Rated Insulation Voltage (U_i):	690 V
Rated Operational Voltage:	690 V
Rated Short-time Withstand Current (I_{cw}):	for 1 s 0.3 kiloampere rms
Power Loss:	1.8 W
Pollution Degree:	3
Handle Type:	Basic handle
Special Functions:	

Multistep switch: 4-step, without 0-position, step angle 30°, front plate 1-2-3-4

Color:	Black
Mounting Type:	Snap-on door mounting
Number of Contacts:	16
Number of Poles:	4
Terminal Type:	Screw Terminals

Technical UL/CSA

Ampere Rating UL/CSA: 600 V AC 25 A

Certificates and Declarations (Document Number)

Declaration of Conformity - CE: 1SCC302005D0201

Instructions and Manuals: 1SCC302013F0006

Container Information

Package Level 1 Units:	1 piece
Package Level 1 Width:	70 mm
Package Level 1 Length:	230 mm
Package Level 1 Height:	70 mm
Package Level 1 Gross Weight:	0.25 kg
Package Level 1 EAN:	6417019667379

Classifications

Object Classification Code:	Q
ETIM 5:	EC002611 - Control switch
ETIM 6:	EC002611 - Control switch

