

TECHNICAL DATA SHEET



Coaxial Cable Model: CB13949

RoHS
Compliant

Design of cable:	
Inner conductor	Single steel copper 1.02mm dia ± 0.01 mm
Insulation	Air space PE
Insulation Dia	4.7mm dia ± 0.1 mm
Screening	Aluminate outside
Braiding	16 x 4/0.12 ± 0.003 mm AL/MG
Jacket	PVC
Colour	White
Size	6.5mm dia ± 0.2 mm
Wall thickness	≈ 0.7 mm
Printing	RG6U Twin Coaxial Cable meter marking
Electric data at 20°C	
Conductor resistance	$< 117 \Omega/\text{km}$
Insulation resistance	$> 5000 \text{M}\Omega/\text{km}$
Testing voltage	50Hz 1min wire/wire 50Hz 1min=1.5KV
Impedance	$75 \pm 3 \Omega @ 200 \text{MHz}$
Packing	100meters on non returnable reel
Temperature range	$-10^\circ\text{C} \sim 60^\circ\text{C}$

Frequency	50	100	200	800	1000
ATT dB/100m	11.0	18.0	20.5	30.5	33.8

Important Notice : This data sheet and its contents (the "Information") belong to pro-POWER. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but pro-POWER assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where pro-POWER was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict pro-POWER's liability for death or personal injury resulting from its negligence.

