

WD Passport®

Portable Hard Drives

USB Powered
Sync & Encrypt Software
Ultra-portable Design



Interface

USB 2.0 and 1.1

Software

WD Sync
Google

Capacities

60 to 160 GB

Order Numbers

WDXMS600Tx
WDXMS800Tx
WDXMS1200Tx
WDXMS1600Tx

Note: Not all products may be available in all regions of the world.

High-performance portable storage for your Mac® and PC. Light and rugged, it's easy to carry and no external power adapter is needed. Comes with sync & encryption and Google™ software.

Product Features

Easy – Installation is a snap because you don't really "install" this drive; you just plug it in and it's ready to use. There is no CD to install; the included software loads from the drive the first time you plug it in.

Smart – Powered by the USB bus. No separate power supply is needed.*

Ultra-portable – This ultra-portable drive fits easily in your pocket or purse, weighs only a few ounces and holds tons of valuable data.

Synchronized and Secure – WD Sync™ synchronization and encryption software lets you save your critical data, and take it with you. Plug your drive into any PC, edit files, read e-mail, and view photos. Then sync all of your changes back to your home or office computer (*Windows only*).

Includes Google software – Search your drive, manage your photos, and simplify Web searches with included Google software (*Windows only*).

Fast – 5400 RPM hard drive - almost 24% faster than 4200 RPM drives.

Compatible – Use with Windows® and Macintosh® computers.

*An optional cable is available for the few systems that limit bus power.

Applications

- Carry important files and e-mail between work and home or on the road
- Share large files between office and home, between PC and Mac
- Back up your existing notebook hard drive for extra data safety

Compatibility

Windows

- Available USB port
- Windows 2000/XP

Macintosh

- Available USB port
- Mac OS X 10.1.5 or later

Note: Compatibility may vary depending on user's hardware configuration and operating system.

Kit Contents

- WD Passport Portable hard drive
- USB 2.0 certified cable
- Quick Install Guide

WD Passport

Portable Hard Drives

External Portable

Performance Specifications

Data transfer rate ¹	Up to 480 Mb/sec
Rotational speed	5400 RPM
Read seek time	12.0 ms (average)

Environmental Specifications

Operating temperature	5°C to 40°C
Non-operating temperature	-20°C to 65°C

Product Dimensions

Height	0.59 in. (15.0 mm) ± 0.10
Length	5.11 in. (129.78 mm) ± 0.10
Width	3.14 in. (79.78 mm) ± 0.10
Weight	0.2310 lb. (0.1048 kg)



Packaging Specifications

Clamshell

	English	Metric
Retail package size	7.45 in. x 6.67 in. x 3.00 in.	189.2 mm x 169.4 mm x 76.2 mm
Retail package weight	0.60 lb.	0.27 kg
Master carton size	12.44 in. x 7.81 in. x 7.31 in.	316.0 mm x 198.4 mm x 185.7 mm
Master carton weight	2.89 lb.	1.31 kg
Packages per master carton	4	4
Master cartons per pallet	108	108



Retail UPC Codes

Capacity ²	PAN AMERICA		ASIA		EUROPE/MIDDLE EAST/AFRICA	
	Order Number	UPC Code	Order Number	UPC Code	Order Number	UPC Code
60 GB	WDXMS600TN	7 18037 11866 6	WDXMS600TA	7 18037 11892 5	WDXMS600TE	7 18037 11869 7
80 GB	WDXMS800TN	7 18037 11867 3	WDXMS800TA	7 18037 11893 2	WDXMS800TE	7 18037 11870 3
120 GB	WDXMS1200TN	7 18037 11868 0	WDXMS1200TA	7 18037 11895 6	WDXMS1200TE	7 18037 11871 0
160 GB	WDXMS1600TN	7 18037 11905 2	WDXMS1600TA	7 18037 11907 6	WDXMS1600TE	7 18037 11906 9



For service and literature:

support.wdc.com
www.westerndigital.com

800.ASK.4WDC North America
 949.672.7199 Spanish
 +800.6008.6008 Asia Pacific
 +31.20.4467651 EMEA

Western Digital, WD, the WD logo, and WD Passport are registered trademarks; and WD Sync is a trademark of Western Digital Technologies, Inc. Other marks may be mentioned herein that belong to other companies. Product specifications subject to change without notice.

© 2007 Western Digital Technologies, Inc. All rights reserved.

Western Digital
 20511 Lake Forest Drive
 Lake Forest, California 92630
 U.S.A.

2879-701191-A02 Feb 2007

¹A USB 2.0 host and USB 2.0 certified cable are required to obtain Hi-Speed USB performance.

²One gigabyte (GB) = one billion bytes. One terabyte (TB) = one trillion bytes. Total accessible capacity varies depending on operating environment.

